

## Datasheet

### RNF133 polyclonal antibody (A01)

**Catalog Number:** H00168433-A01

**Regulation Status:** For research use only (RUO)

**Product Description:** Mouse polyclonal antibody raised against a partial recombinant RNF133.

**Immunogen:** RNF133 (NP\_631914, 277 a.a. ~ 376 a.a) partial recombinant protein with GST tag.

**Sequence:**

FFHKNCIDPWILPHGTCPICKCDILKVLGIQVVVENGTE  
PLQVLMSNELPETLSPSEEETNNEVSPAGTSDKVIHVE  
ENPTSQNNDIQPHSVVEDVHPSP

**Host:** Mouse

**Reactivity:** Human

**Applications:** ELISA, WB-Ce, WB-Re

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Storage Buffer:** 50 % glycerol

**Storage Instruction:** Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 168433

**Gene Symbol:** RNF133

**Gene Alias:** MGC27072

**Gene Summary:** The protein encoded by this gene contains a RING finger domain, a motif present in a variety of functionally distinct proteins and known to be involved in protein-protein and protein-DNA interactions. This gene has no intron. [provided by RefSeq]