TCI AMERICA

SAFETY DATA SHEET

Revision number: 2
Revision date: 10/06/2014

1. IDENTIFICATION

Product name: 2,3-Dibromo-1-propanol
Product code: D0204

Product use: For laboratory research purposes.
Restrictions on use: Not for drug or household use.

Company:
TCI America
9211 N. Harborgate Street
Portland, OR 97203 U.S.A.
Telephone:
+1-800-423-8616 / +1-503-283-1681
Fax:
+1-888-520-1075 / +1-503-283-1987
e-mail:
sales-US@TCIchemicals.com
www.TCIchemicals.com

Emergency telephone number:
Chemical Emergencies:
TCI America (8:00am - 5:00pm) PST
+1-503-286-7624
Transportation Emergencies:
Chemtrec 24-Hour
+1-800-424-9300 (U.S.A.)
+1-703-527-3887 (International)
Responsible department:
TCI America
Environmental Health Safety and Security
+1- 503-286-7624

2. HAZARD(S) IDENTIFICATION

OSHA Haz Com: CFR 1910.1200:
Acute Toxicity - Oral [Category 4]
Acute Toxicity - Dermal [Category 3]
Acute Toxicity - Inhalation [Category 4]
Eye Damage/Irritation [Category 1]
Carcinogenicity [Category 2]
Toxic to Reproduction [Category 2]
Aquatic Hazard (Acute) [Category 3]
Aquatic Hazard (Long-Term) [Category 3]

Signal word: Danger!

Hazard Statement(s):
Causes serious eye damage
Harmful if swallowed
Harmful if inhaled
Suspected of causing cancer
Suspected of damaging fertility or the unborn child
Toxic in contact with skin
Harmful to aquatic life
Harmful to aquatic life with long lasting effects

Pictogram(s) or Symbol(s):



Precautionary Statement(s):

[Prevention] Do not eat, drink or smoke when using this product. Wash hands and face thoroughly after handling. Wear protective gloves and protective clothing. Avoid breathing fume, mist, vapors or spray. Use only outdoors or in a well-ventilated area. Wear eye protection. Wear face protection (full length face shield). Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Wear protective gloves, protective clothing, eye protection and face protection.

[Response] If swallowed: Immediately call a poison center or doctor. Rinse mouth. If on skin: Wash with plenty of water. Call a poison center or doctor if you feel unwell. Take off immediately all contaminated clothing and wash it before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a poison center or doctor. If exposed or concerned: Get medical advice or attention. If exposed: Call a poison center or doctor.

[Storage] Store locked up.

2. HAZARD(S) IDENTIFICATION

[Disposal] Dispose of contents and container in accordance with US EPA guidelines for the classification and determination of hazardous waste listed in 40 CFR 261.3. (See Section 13)

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance/Mixture: Substance
Components: 2,3-Dibromo-1-propanol
Percent: >95.0%(GC)
CAS Number: 96-13-9
Molecular Weight: 217.89
Chemical Formula: $C_3H_6Br_2O$
Synonyms: α,β-Dibromohydrin , Glycerol α,β-Dibromohydrin

4. FIRST-AID MEASURES

Inhalation: Immediately call a poison center or doctor. Effects of exposure (inhalation) to substance may be delayed. Inhalation of vapors or contact with substance will result in contamination and potential harmful effects. Move victim to fresh air. Give artificial respiration if victim is not breathing. Administer oxygen if breathing is difficult. Keep victim warm and quiet. Treat symptomatically and supportively. Ensure that medical personnel are aware of the material(s) involved and take precautions to protect themselves.

Skin contact: Immediately call a poison center or doctor. Effects of exposure (skin contact) to substance may be delayed. Remove and wash contaminated clothing before re-use. Remove and isolate contaminated clothing and shoes. In case of contact with substance, immediately flush skin with running water for at least 20 minutes. Treat symptomatically and supportively. Ensure that medical personnel are aware of the material(s) involved and take precautions to protect themselves.

Eye contact: IMMEDIATELY flush eyes with running water for at least 15 minutes, keeping eyelids open. Eye contact with vapors or substance may cause severe injury, burns, or death. Call emergency medical service. Move victim to fresh air. Check for and remove any contact lenses. Keep victim warm and quiet. Treat symptomatically and supportively. Effects of exposure to substance may be delayed. Ensure that medical personnel are aware of the material(s) involved and take precautions to protect themselves.

Ingestion: Harmful if swallowed. Do not induce vomiting with out medical advice. Effects of exposure (ingestion) to substance may be delayed. Call a physician or Poison Control Center immediately. Do not use mouth-to-mouth method if victim ingested the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Loosen tight clothing such as a collar, tie, belt or waistband. If a person vomits place them in the recovery position so that vomit will not reenter the mouth and throat. Rinse mouth. Keep victim warm and quiet. Treat symptomatically and supportively. Ensure that medical personnel are aware of the material(s) involved and take precautions to protect themselves.

Symptoms/effects:

Acute: Pain. Redness.
Delayed: Possibly carcinogenic to humans.

Immediate medical attention: WARNING: It might be dangerous to the person providing aid to give mouth-to-mouth respiration, because the inhaled material is toxic. WARNING: It might be hazardous to the person providing aid to give mouth-to-mouth respiration, because the inhaled material is corrosive. CAUTION: Victim may be a source of contamination. For severe burns, immediate medical attention is required. If breathing has stopped, perform artificial respiration. Use first aid treatment according to the nature of the injury. Ensure that medical personnel are aware of the material(s) involved and take precautions to protect themselves.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media: Dry chemical, CO_2 or water spray. Consult with local fire authorities before attempting large scale fire fighting operations.

Specific hazards arising from the chemical
Hazardous combustion products: These products include: Carbon oxides Halogenated compounds
Other specific hazards: Closed containers may explode from heat of a fire.

Special precautions for fire-fighters:
Use water spray or fog; do not use straight streams. Dike fire-control water for later disposal; do not scatter the material. Containers may explode when heated. Move containers from fire area if you can do it without risk.

5. FIRE-FIGHTING MEASURES

Special protective equipment for fire-fighters:
Wear positive pressure self-contained breathing apparatus (SCBA). Structural fire fighters' protective clothing provides limited protection in fire situations ONLY; it may not be effective in spill situations. Wear chemical protective clothing which is specifically recommended by the manufacturer. It may provide little or no thermal protection.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions:	Avoid contact with skin, eyes, and clothing. Keep people away from and upwind of spill/leak. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing (Section 8). Warn unnecessary personnel to move away. Stop leak if you can do it without risk. Ensure adequate ventilation. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.
Personal protective equipment:	Wear eye protection (splash goggles) and face protection (full length face shield). Wear protective clothing (chemical resistant suit and chemical resistant boots). Vapor respirator. Be sure to use a MSHA/NIOSH approved respirator or equivalent. Wear protective gloves (nitrile).
Emergency procedures:	Do not clean-up or dispose except under supervision of a specialist. In case of a spill and/or a leak, always shut off any sources of ignition, ventilate the area, and excercise caution. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Warn personnel to move away. Prevent entry into sewers, basements or confined areas; dike if needed.

Methods and materials for containment and cleaning up:
ELIMINATE all ignition sources (no smoking, flares, sparks, or flames in immediate area). Stop leak if without risk. Absorb with an inert material and put the spilled material in an appropriate waste disposal container. Use clean non-sparking tools to collect absorbed material. Dike far ahead of spill; use dry sand to contain the flow of material. Ventilate the area.
Environmental precautions:
Keep away from living quarters. Environmental hazard. Do not let product enter drains. Prevent further leakage or spillage if safe to do so. Water runoff can cause environmental damage. Prevent entry into sewers, basements or confined areas; dike if needed.

7. HANDLING AND STORAGE

Precautions for safe handling:	Do NOT breath gas, fumes, vapor, or spray. Manipulate under an adequate fume hood. Do not ingest. Avoid contact with skin and eyes. Avoid contact with skin. Avoid exposure - obtain special instructions before use. Avoid prolonged or repeated exposure. Normal measures for preventive fire protection. Avoid contact - obtain special instructions before use. Good general ventilation should be sufficient to control airborne levels. Keep container dry. Handle and open container with care. Wear suitable protective clothing, gloves and eye/face protection. When using do not eat, drink, or smoke. Keep away from sources of ignition.
Conditions for safe storage:	Store locked up. Keep containers tightly closed in a cool, well-ventilated place. Keep away from incompatibles. Containers which are opened must be carefully resealed and kept upright to prevent leakage. Avoid prolonged storage periods.
Storage incompatibilities:	Combustible substances, Store away from oxidizing agents

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure limits: No data available

Appropriate engineering controls:
Handle only in a fully enclosed system and equipment. Good general ventilation should be sufficient to control airborne levels. Ventilation is normally required when handling or using this product. Eyewash fountains should be provided in areas where there is any possibility that workers could be exposed to the substance. Follow safe industrial engineering/laboratory practices when handling any chemical.

Personal protective equipment

Respiratory protection:	Vapor respirator. Be sure to use a MSHA/NIOSH approved respirator or equivalent.
Hand protection:	Wear protective gloves.
Eye protection:	Splash goggles.
Skin and body protection:	Wear protective clothing (chemical resistant suit and chemical resistant boots).

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state (20°C):	Liquid
Form:	Clear
Color:	Colorless - Slightly pale yellow
Odor:	No data available
Odor threshold:	No data available

9. PHYSICAL AND CHEMICAL PROPERTIES

Melting point/freezing point:	9°C (48°F)	**pH:**	No data available
Boiling point/range:	99°C (210°F)/1.3kPa	**Vapor pressure:**	12Pa/25°C
Decomposition temperature:	No data available	**Vapor density:**	No data available
Relative density:	2.14	**Dynamic Viscosity:**	No data available
Kinematic Viscosity:	No data available		
Partition coefficient: n-octanol/water (log P_{ow})	0.96	**Evaporation rate:** (Butyl Acetate = 1)	No data available
Flash point:	110°C (230°F)	**Autoignition temperature:**	No data available
Flammability (solid, gas):	No data available	**Flammability or explosive limits:**	
		Lower:	No data available
		Upper:	No data available

Solubility(ies):
Water: Soluble (52g/L, 25°C)
Soluble: Ether, Alcohols, Benzene, Acetone

10. STABILITY AND REACTIVITY

Reactivity:	Not Available.
Chemical Stability:	Moisture sensitive. Light sensitive.
Possibility of Hazardous Reactions:	No hazardous reactivity has been reported.
Conditions to avoid:	Exposure to light. Exposure to moisture. Moisture sensitive.
Incompatible materials:	Oxidizing agents
Hazardous Decomposition Products:	No data available

11. TOXICOLOGICAL INFORMATION

RTECS Number: UB0175000

Acute Toxicity:
orl-rat LD50:681 mg/kg

skn-rbt LD50:316 mg/kg

ihl-rat LC50:9920 mg/m^3/4H

Skin corrosion/irritation:
No data available

Serious eye damage/irritation:
eye-rbt 100 uL/24H SEV

Respiratory or skin sensitization:
No data available

Germ cell mutagenicity:
mmo-sat 3300 ng/plate (-S9)

mmo-sat 203 ug/plate (+S9)

Carcinogenicity:

skn-rat TDLo:45120 mg/kg/48W-I

IARC: Group 2B (Possibly carcinogenic to humans) .

NTP: No data available

OSHA: No data available

Reproductive toxicity:
No data available

Routes of Exposure: Inhalation, Eye contact, Ingestion, Skin contact.
Symptoms related to exposure:
Overexposure may result in serious illness or death. Eye contact can result in corneal damage or blindness.
Potential Health Effects:
No specific information available; skin and eye contact may result in irriatation. May be harmful if inhaled or ingested.
Target organ(s): No data available

12. ECOLOGICAL INFORMATION

Ecotoxicity

Fish:	No data available
Crustacea:	No data available
Algae:	No data available

Persistence and degradability:	No data available
Bioaccumulative potential (BCF):	3
Mobillity in soil:	No data available
Partition coefficient: n-octanol/water (log P_{ow})	0.96
Soil adsorption (Koc):	4
Henry's Law: constant (PaM^3/mol)	6.4×10^{-3}

13. DISPOSAL CONSIDERATIONS

Disposal of product:	Recycle to process if possible. It is the generator's responsibility to comply with Federal, State and Local rules and regulations. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. This section is intended to provide assistance but does not replace these laws, nor does compliance in accordance with this section ensure regulatory compliance according to the law. US EPA guidelines for Identification and Listing of Hazardous Waste are listed in 40 CFR Parts 261. The product should not be allowed to enter the environment, drains, water ways, or the soil.
Disposal of container:	Dispose of as unused product. Do not re-use empty containers.
Other considerations:	Observe all federal, state and local regulations when disposing of the substance.

14. TRANSPORT INFORMATION

DOT (US)

UN number:	Proper Shipping Name:	Class or Division:	Packing Group:
UN2810	Toxic liquids, organic, n.o.s.	6.1 Toxic material.	III

IATA

UN number:	Proper Shipping Name:	Class or Division:	Packing Group:
UN2810	Toxic liquid, organic, n.o.s.	6.1 Toxic material.	III

IMDG

UN number:	Proper Shipping Name:	Class or Division:	Packing Group:
UN2810	Toxic liquid, organic, n.o.s.	6.1 Toxic material.	III

EmS number: F-A, S-A

15. REGULATORY INFORMATION

Toxic Substance Control Act (TSCA 8b.):
This product is ON the EPA Toxic Substances Control Act (TSCA) inventory.

US Federal Regulations

CERCLA Hazardous substance and Reportable Quantity:

SARA 313:	Not Listed
SARA 302:	Not Listed

State Regulations

State Right-to-Know

Massachusetts	Not Listed
New Jersey	Listed
Pennsylvania	Not Listed
California Proposition 65:	Listed

Other Information

15. REGULATORY INFORMATION

NFPA Rating:

Health:	2
Flammability:	1
Instability:	0

HMIS Classification:

Health:	2
Flammability:	1
Physical:	0

International Inventories

WHMIS hazard class: E: Corrosive material.
D1B: Materials causing immediate and serious toxic effects. (Toxic)
D2A: Materials causing other toxic effects. (Very Toxic)

EC-No: 202-480-9

16. OTHER INFORMATION

Revision date: 10/06/2014
Revision number: 2

TCI chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its affiliates or subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our SDS are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated SDS for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, face mask, fume hood). For proper handling and disposal, always comply with federal, state and local regulations.