

## Datasheet

### CKS1B polyclonal antibody (A01)

**Catalog Number:** H00001163-A01

**Regulation Status:** For research use only (RUO)

**Product Description:** Mouse polyclonal antibody raised against a partial recombinant CKS1B.

**Immunogen:** CKS1B (NP\_001817, 1 a.a. ~ 79 a.a)  
partial recombinant protein with GST tag.

**Sequence:**

MSHKQIYYSDKYDDEEFYRHVMLPKDIAKLVPKTHLM  
SESEWRNLGVQSQGWVHYMIHEPEPHILLFRRPLPK  
KPKK

**Host:** Mouse

**Reactivity:** Human

**Applications:** ELISA, WB-Re

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Storage Buffer:** 50 % glycerol

**Storage Instruction:** Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 1163

**Gene Symbol:** CKS1B

**Gene Alias:** CKS1, PNAS-16, PNAS-18, ckshs1

**Gene Summary:** CKS1B protein binds to the catalytic subunit of the cyclin dependent kinases and is essential for their biological function. The CKS1B mRNA is found to be expressed in different patterns through the cell cycle in HeLa cells, which reflects a specialized role for the encoded protein. At least two transcript variants have been identified for this gene, and it appears that only one of them encodes a protein. [provided by RefSeq]