

Datasheet

ARHGEF17 polyclonal antibody

Catalog Number: PAB13013

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against synthetic peptide of ARHGEF17.

Immunogen: A synthetic peptide corresponding to internal region 18 amino acids of human ARHGEF17.

Host: Rabbit

Reactivity: Human

Applications: IHC-P, WB-Ce

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Recommend Usage: Western Blot (1-2 ug/mL)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS (0.02% sodium azide)

Storage Instruction: Store at 4°C for three months. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 9828

Gene Symbol: ARHGEF17

Gene Alias: FLJ90019, KIAA0337, P164RHOGF, TEM4, p164-RhoGEF

References:

1. A phase I and pharmacokinetic study of irinotecan given as a 7-day continuous infusion in metastatic colorectal cancer patients pretreated with 5-fluorouracil or raltitrexed. Masi G, Falcone A, Di Paolo A, Allegrini G, Danesi R, Barbara C, Cupini S, Del Tacca M. Clin Cancer Res. 2004 Mar 1;10(5):1657-63.

2. Tumor endothelial markers: new targets for cancer therapy. Nanda A, St Croix B. Curr Opin Oncol. 2004 Jan;16(1):44-9.

3. Cell surface tumor endothelial markers are conserved in mice and humans. Carson-Walter EB, Watkins DN, Nanda A, Vogelstein B, Kinzler KW, St Croix B. Cancer Res. 2001 Sep 15;61(18):6649-55.