

SAFETY DATA SHEET

1. Identification

Product identifier: HYDROCHLORIC ACID

Other means of identification

Synonyms: Muriatic Acid, Hydrogen Chloride, Aqueous

Product No.: 9538, 9165, V226, V187, V078, V001, 6900, 2624, 2515, H999, H987, H616, 5861, 2062, 5814, 2626, 2612, 5800, 9625, 5587, 9551, 9544, 9539, 9535, 9530, 9529, 5367, H613, 37825, 25496, 20620

Recommended use and restriction on use

Recommended use: Not available.

Restrictions on use: Not known.

Manufacturer/Importer/Supplier/Distributor information

Manufacturer

Company Name: Avantor Performance Materials, Inc.
Address: 3477 Corporate Parkway, Suite 200
Center Valley, PA 18034

Telephone: Customer Service: 855-282-6867

Fax:
Contact Person: Environmental Health & Safety
e-mail: info@avantormaterials.com

Emergency telephone number:

24 Hour Emergency: 908-859-2151

Chemtrec: 800-424-9300

2. Hazard(s) identification

Hazard classification

Physical hazards

Corrosive to metals Category 1

Health hazards

Acute toxicity (Oral)	Category 4
Skin corrosion/irritation	Category 1
Serious eye damage/eye irritation	Category 1
Specific target organ toxicity - single exposure (Inhalation - vapor)	Category 3
Acute toxicity (Oral)	Category 4
Skin corrosion/irritation	Category 1A
Serious eye damage/eye irritation	Category 1

Label elements

Hazard symbol:



Signal word:

Danger

Hazard statement: May be corrosive to metals.
Harmful if swallowed.
Causes severe skin burns and eye damage.
May cause respiratory irritation.

Precautionary statement

Prevention: Keep only in original container. Wash thoroughly after handling. Do not breathe dust/fume/gas/mist/vapors/spray. Use only outdoors or in a well-ventilated area. Wear protective gloves/protective clothing/eye protection/face protection. Do not eat, drink or smoke when using this product.

Response: Absorb spillage to prevent material damage. IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Remove/take off immediately all contaminated clothing. Rinse skin with water/shower. Wash contaminated clothing before reuse. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Immediately call a POISON CENTER or doctor/physician.

Storage: Store locked up. Store in a well-ventilated place. Keep container tightly closed. Store in corrosive resistant container with a resistant inner liner.

Disposal: Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

Other hazards which do not result in GHS classification: None.

3. Composition/information on ingredients

Mixtures

Chemical identity	Common name and synonyms	CAS number	Content in percent (%)*
HYDROCHLORIC ACID		7647-01-0	20 - 40%

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

4. First-aid measures

General information: Get medical advice/attention if you feel unwell. Show this safety data sheet to the doctor in attendance.

Ingestion: Call a physician or poison control center immediately. Do not induce vomiting without advice from poison control center. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.

Inhalation: Move to fresh air. Call a physician or poison control center immediately. Apply artificial respiration if victim is not breathing. If breathing is difficult, give oxygen.

Skin contact: Immediately flush with plenty of water for at least 15 minutes while removing contaminated clothing and shoes. Call a physician or poison control center immediately. Wash contaminated clothing before reuse. Destroy or thoroughly clean contaminated shoes.

Eye contact: Immediately flush with plenty of water for at least 15 minutes. If easy to do, remove contact lenses. Call a physician or poison control center immediately. In case of irritation from airborne exposure, move to fresh air. Get medical attention immediately.

Most important symptoms/effects, acute and delayed

Symptoms: Causes severe skin and eye burns. Harmful if swallowed.

Indication of immediate medical attention and special treatment needed

Treatment: Treat symptomatically. Symptoms may be delayed.

5. Fire-fighting measures

General fire hazards: No data available.

Suitable (and unsuitable) extinguishing media

Suitable extinguishing media: The product is non-combustible. Use fire-extinguishing media appropriate for surrounding materials.

Unsuitable extinguishing media: None known.

Specific hazards arising from the chemical: Fire or excessive heat may produce hazardous decomposition products.

Special protective equipment and precautions for firefighters

Special fire fighting procedures: Move containers from fire area if you can do so without risk. Use water spray to keep fire-exposed containers cool.

Special protective equipment for fire-fighters: Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures: Ventilate closed spaces before entering them. Keep unauthorized personnel away. Evacuate area. Keep upwind. See Section 8 of the MSDS for Personal Protective Equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing.

Methods and material for containment and cleaning up: Neutralize with lime or soda ash. Absorb spill with vermiculite or other inert material, then place in a container for chemical waste. Dike far ahead of larger spill for later recovery and disposal.

Notification Procedures: Inform authorities if large amounts are involved.

Environmental precautions: Do not contaminate water sources or sewer. Prevent further leakage or spillage if safe to do so.

7. Handling and storage

Precautions for safe handling: Do not eat, drink or smoke when using the product. Do not get in eyes, on skin, on clothing. Wash hands thoroughly after handling. Do not breathe dust/fume/gas/mist/vapors/spray. Use caution when adding this material to water.

Conditions for safe storage, including any incompatibilities:

Keep container tightly closed. Store in a well-ventilated place. Unsuitable containers: metals.

8. Exposure controls/personal protection

Control parameters

Occupational exposure limits

Chemical identity	Type	Exposure Limit values	Source
HYDROCHLORIC ACID	Ceiling	2 ppm	US. ACGIH Threshold Limit Values (2011)
	Ceil_Time	5 ppm 7 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2010)
	Ceiling	5 ppm 7 mg/m3	US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000) (02 2006)
	Ceiling	5 ppm 7 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)

Appropriate engineering controls

No data available.

Individual protection measures, such as personal protective equipment

General information: Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. An eye wash and safety shower must be available in the immediate work area.

Eye/face protection: Wear safety glasses with side shields (or goggles) and a face shield.

Skin protection

Hand protection: Chemical resistant gloves

Other: Wear suitable protective clothing and gloves.

Respiratory protection: If engineering controls do not maintain airborne concentrations below recommended exposure limits (where applicable) or to an acceptable level (in countries where exposure limits have not been established), an approved respirator must be worn. Air-purifying respirator with an appropriate, government approved (where applicable), air-purifying filter, cartridge or canister. Contact health and safety professional or manufacturer for specific information.

Hygiene measures: Provide eyewash station and safety shower. Observe good industrial hygiene practices. Wash hands before breaks and immediately after handling the product. Do not get in eyes. Wash contaminated clothing before reuse. Do not get this material in contact with skin.

9. Physical and chemical properties

Appearance

Physical state: Liquid

Form: Liquid

Color: Colorless

Odor: Pungent

Odor threshold: No data available.

pH: 0.1 (1 N aqueous solution)

Melting point/freezing point: -35 °C

Initial boiling point and boiling range:	48 °C
Flash Point:	Not applicable
Evaporation rate:	No data available.
Flammability (solid, gas):	No data available.
Upper/lower limit on flammability or explosive limits	
Flammability limit - upper (%):	No data available.
Flammability limit - lower (%):	No data available.
Explosive limit - upper (%):	No data available.
Explosive limit - lower (%):	No data available.
Vapor pressure:	14.1 kPa
Vapor density:	No data available.
Relative density:	1.18 (20 °C)
Solubility(ies)	
Solubility in water:	Soluble
Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	No data available.
Auto-ignition temperature:	No data available.
Decomposition temperature:	No data available.
Viscosity:	No data available.

10. Stability and reactivity

Reactivity:	Reacts violently with strong alkaline substances.
Chemical stability:	Material is stable under normal conditions.
Possibility of hazardous reactions:	Hazardous polymerization does not occur.
Conditions to avoid:	Avoid contact with strong reducing agents. Strong oxidizing agents. Contact with alkalis.
Incompatible materials:	Acids. Amines. Alkalies. Metals. Reducing agents. Oxidizing agents.
Hazardous decomposition products:	Chlorine. hydrogen chloride By heating and fire, corrosive vapors/gases may be formed.

11. Toxicological information

Information on likely routes of exposure

Ingestion:	Harmful if swallowed.
Inhalation:	Causes severe burns.
Skin contact:	Causes severe skin burns.
Eye contact:	Causes serious eye damage.

Information on toxicological effects

Acute toxicity (list all possible routes of exposure)

Oral	
Product:	ATEmix (Rat): 581 mg/kg
Dermal	
Product:	No data available.

Inhalation

Product: No data available.

Specified substance(s):

HYDROCHLORIC ACID LC 50 (Mouse, 1 h): 1,108 mg/l

Repeated dose toxicity

Product: No data available.

Skin corrosion/irritation

Product: Causes severe skin burns.

Serious eye damage/eye irritation

Product: Causes serious eye damage.

Respiratory or skin sensitization

Product: Not a skin sensitizer.

Carcinogenicity

Product: This substance has no evidence of carcinogenic properties.

IARC Monographs on the Evaluation of Carcinogenic Risks to Humans:

No carcinogenic components identified

US. National Toxicology Program (NTP) Report on Carcinogens:

No carcinogenic components identified

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050):

No carcinogenic components identified

Germ cell mutagenicity

In vitro

Product: No mutagenic components identified

In vivo

Product: No mutagenic components identified

Reproductive toxicity

Product: No components toxic to reproduction

Specific target organ toxicity - single exposure

Product: Respiratory tract irritation.

Specific target organ toxicity - repeated exposure

Product: None known.

Aspiration hazard

Product: Not classified

Other effects:

None known.

12. Ecological information

Ecotoxicity:

Acute hazards to the aquatic environment:

Fish

Product: No data available.

Specified substance(s):

HYDROCHLORIC ACID LC 50 (Western mosquitofish (*Gambusia affinis*), 96 h): 282 mg/l Mortality

Aquatic invertebrates

Product: No data available.

Specified substance(s):

HYDROCHLORIC ACID LC 50 (Green or European shore crab (*Carcinus maenas*), 48 h): 240 mg/l Mortality
LC 50 (Common shrimp, sand shrimp (*Crangon crangon*), 48 h): 260 mg/l Mortality

Chronic hazards to the aquatic environment:
Fish

Product: No data available.

Aquatic invertebrates

Product: No data available.

Toxicity to Aquatic Plants

Product: No data available.

Persistence and degradability
Biodegradation

Product: Expected to be readily biodegradable.

BOD/COD ratio

Product: No data available.

Bioaccumulative potential
Bioconcentration factor (BCF)

Product: No data available on bioaccumulation.

Partition coefficient n-octanol / water (log Kow)

Product: No data available.

Mobility in soil:

The product is water soluble and may spread in water systems.

Other adverse effects:

Large amounts of the product may affect the acidity (pH-factor) in water with possible risk of harmful effects to aquatic organisms.

13. Disposal considerations
Disposal instructions:

Discharge, treatment, or disposal may be subject to national, state, or local laws. Since emptied containers retain product residue, follow label warnings even after container is emptied.

Contaminated packaging:

No data available.

14. Transport information
DOT

UN number:	UN 1789
UN proper shipping name:	Hydrochloric acid
Transport hazard class(es)	
Class(es):	8
Label(s):	8
Packing group:	II
Marine Pollutant:	No

IMDG

UN number:	UN 1789
UN proper shipping name:	HYDROCHLORIC ACID
Transport hazard class(es)	
Class(es):	8
Label(s):	8
EmS No.:	F-A, S-B
Packing group:	II
Marine Pollutant:	No

IATA

UN number:	UN 1789
Proper Shipping Name:	Hydrochloric acid
Transport hazard class(es):	
Class(es):	8
Label(s):	8
Marine Pollutant:	No
Packing group:	II

15. Regulatory information
US federal regulations
TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)
US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

None present or none present in regulated quantities.

CERCLA Hazardous Substance List (40 CFR 302.4):

HYDROCHLORIC ACID Reportable quantity: 5000 lbs.

Superfund amendments and reauthorization act of 1986 (SARA)
Hazard categories

<input checked="" type="checkbox"/> Acute (Immediate)	<input type="checkbox"/> Chronic (Delayed)	<input type="checkbox"/> Fire	<input type="checkbox"/> Reactive	<input type="checkbox"/> Pressure Generating
---	--	-------------------------------	-----------------------------------	--

SARA 302 Extremely hazardous substance

Chemical identity	RQ	Threshold Planning Quantity
HYDROCHLORIC ACID	5000 lbs.	500 lbs.

SARA 304 Emergency release notification

Chemical identity	RQ
HYDROCHLORIC ACID	5000 lbs.

SARA 311/312 Hazardous chemical

Chemical identity	Threshold Planning Quantity
HYDROCHLORIC ACID	500lbs

SARA 313 (TRI reporting)

Chemical identity	Reporting threshold for other users	Reporting threshold for manufacturing and processing
HYDROCHLORIC ACID	10000 lbs	25000 lbs.

Clean Water Act Section 311 Hazardous Substances (40 CFR 117.3)

HYDROCHLORIC ACID Reportable quantity: 5000 lbs.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130):

HYDROCHLORIC ACID Threshold quantity: 15000 lbs

HYDROCHLORIC ACID

Threshold quantity: 5000 lbs

US state regulations

US. California Proposition 65

No ingredient regulated by CA Prop 65 present.

US. New Jersey Worker and Community Right-to-Know Act

HYDROCHLORIC ACID Listed

US. Massachusetts RTK - Substance List

HYDROCHLORIC ACID Listed

US. Pennsylvania RTK - Hazardous Substances

HYDROCHLORIC ACID Listed

US. Rhode Island RTK


HYDROCHLORIC ACID Listed

Inventory Status:

Australia AICS:	On or in compliance with the inventory
Canada DSL Inventory List:	On or in compliance with the inventory
EU EINECS List:	On or in compliance with the inventory
EU ELINCS List:	Not in compliance with the inventory.
Japan (ENCS) List:	On or in compliance with the inventory
EU No Longer Polymers List:	Not in compliance with the inventory.
China Inv. Existing Chemical Substances:	On or in compliance with the inventory
Korea Existing Chemicals Inv. (KECI):	On or in compliance with the inventory
Canada NDSL Inventory:	Not in compliance with the inventory.
Philippines PICCS:	On or in compliance with the inventory
US TSCA Inventory:	On or in compliance with the inventory
New Zealand Inventory of Chemicals:	On or in compliance with the inventory
Switzerland Consolidated Inventory:	Not in compliance with the inventory.
Japan ISHL Listing:	Not in compliance with the inventory.
Japan Pharmacopoeia Listing:	Not in compliance with the inventory.

16. Other information, including date of preparation or last revision

NFPA Hazard ID



	Flammability
	Health
	Reactivity
	Special hazard.

Hazard rating: 0 - Minimal; 1 - Slight; 2 - Moderate; 3 - Serious; 4 - Severe

COR: Corrosive

Issue date: 06-23-2014

Revision date: No data available.

Version #: 2.0

Further information: No data available.

SDS_US - SDSMIX000520

Disclaimer:

THE INFORMATION PRESENTED IN THIS MATERIAL SAFETY DATA SHEET (MSDS/SDS) WAS PREPARED BY TECHNICAL PERSONNEL BASED ON DATA THAT THEY BELIEVE IN THEIR GOOD FAITH JUDGMENT IS ACCURATE. HOWEVER, THE INFORMATION PROVIDED HEREIN IS PROVIDED "AS IS," AND AVANTOR PERFORMANCE MATERIALS MAKES AND GIVES NO REPRESENTATIONS OR WARRANTIES WHATSOEVER, AND EXPRESSLY DISCLAIMS ALL WARRANTIES REGARDING SUCH INFORMATION AND THE PRODUCT TO WHICH IT RELATES, WHETHER EXPRESS, IMPLIED, OR STATUTORY, INCLUDING WITHOUT LIMITATION<(>,<)> WARRANTIES OF ACCURACY, COMPLETENESS, MERCHANTABILITY, NON-INFRINGEMENT, PERFORMANCE, SAFETY, SUITABILITY, STABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, AND ANY WARRANTIES ARISING FROM COURSE OF DEALING, COURSE OF PERFORMANCE, OR USAGE OF TRADE. THIS MSDS/SDS IS INTENDED ONLY AS A GUIDE TO THE APPROPRIATE PRECAUTIONARY HANDLING OF THE MATERIAL BY A PROPERLY TRAINED PERSON USING THIS PRODUCT, AND IS NOT INTENDED TO BE COMPREHENSIVE AS TO THE MANNER AND CONDITIONS OF USE, HANDLING, STORAGE, OR DISPOSAL OF THE PRODUCT. INDIVIDUALS RECEIVING THIS MSDS/SDS MUST ALWAYS EXERCISE THEIR OWN INDEPENDENT JUDGMENT IN DETERMINING THE APPROPRIATENESS OF SUCH ISSUES. ACCORDINGLY, AVANTOR PERFORMANCE MATERIALS ASSUMES NO LIABILITY WHATSOEVER FOR THE USE OF OR RELIANCE UPON THIS INFORMATION. NO SUGGESTIONS FOR USE ARE INTENDED AS, AND NOTHING HEREIN SHALL BE CONSTRUED AS, A RECOMMENDATION TO INFRINGE ANY EXISTING PATENTS OR TO VIOLATE ANY FEDERAL, STATE, LOCAL, OR FOREIGN LAWS. AVANTOR PERFORMANCE MATERIALS REMINDS YOU THAT IT IS YOUR LEGAL DUTY TO MAKE ALL INFORMATION IN THIS MSDS/SDS AVAILABLE TO YOUR EMPLOYEES.