



SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 09/25/2014

Version 1.1

SECTION 1. Identification

Product identifier

Product number	DX0685
Product name	1,2-Dichlorobenzene
CAS-No.	95-50-1

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis
-----------------	----------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 4, H227
Acute toxicity, Category 4, Oral, H302
Acute toxicity, Category 3, Inhalation, H331
Skin irritation, Category 2, H315
Eye irritation, Category 2A, H319
Specific target organ systemic toxicity - single exposure, Category 3, Respiratory system, H335
For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX0685
Product name 1,2-Dichlorobenzene

Version 1.1

Hazard Statements

H227 Combustible liquid.
H302 Harmful if swallowed.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H331 Toxic if inhaled.
H335 May cause respiratory irritation.

Precautionary Statements

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P261 Avoid breathing dust/ fume/ gas/ mist/ vapors/ spray.
P264 Wash skin thoroughly after handling.
P270 Do not eat, drink or smoke when using this product.
P271 Use only outdoors or in a well-ventilated area.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
P304 + P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P311 Call a POISON CENTER or doctor/ physician.
P321 Specific treatment (see supplemental first aid instructions on this label).
P330 Rinse mouth.
P332 + P313 If skin irritation occurs: Get medical advice/ attention.
P337 + P313 If eye irritation persists: Get medical advice/ attention.
P362 Take off contaminated clothing and wash before reuse.
P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.
P403 + P233 Store in a well-ventilated place. Keep container tightly closed.
P403 + P235 Store in a well-ventilated place. Keep cool.
P405 Store locked up.
P501 Dispose of contents/ container to an approved waste disposal plant.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	1,2-(Cl) ₂ C ₆ H ₄	C ₆ H ₄ Cl ₂ (Hill)
Molar mass	147 g/mol	

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

1,2-Dichlorobenzene (>= 90 % - <= 100 %)

95-50-1

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX0685
Product name 1,2-Dichlorobenzene

Version 1.1

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water. Call in ophthalmologist.

Ingestion

After swallowing: make victim drink water (two glasses at most), avoid vomiting (risk of aspiration!). Pulmonary failure possible after aspiration of vomit. Call a physician immediately.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects, Cough, Shortness of breath, Dizziness, narcosis, Headache, CNS disorders

Indication of any immediate medical attention and special treatment needed

Sodium sulfate (1 tablespoon/1/4 l water).

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Water, Carbon dioxide (CO₂), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air on intense heating.

Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:

Hydrogen chloride gas, Phosgene, dioxin

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX0685
Product name 1,2-Dichlorobenzene

Version 1.1

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers

Do not use light-weight-metal containers.

Tightly closed. Keep in a well-ventilated place. Keep locked up or in an area accessible only to qualified or authorized persons.

Store at room temperature.

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Ingredients

Basis	Value	Threshold limits	Remarks
<i>1,2-Dichlorobenzene 95-50-1</i>			
ACGIH	Time Weighted Average (TWA):	25 ppm	
	Short Term Exposure Limit (STEL):	50 ppm	
NIOSH/GUIDE	Ceiling Limit Value and Time Period (if specified):	50 ppm 300 mg/m ³	
	Ceiling Limit Value:	50 ppm 300 mg/m ³	
OSHA_TRANS	Ceiling Limit Value:	50 ppm 300 mg/m ³	
Z1A	Ceiling Limit Value:	50 ppm 300 mg/m ³	

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

DX0685

Version 1.1

Product name

1,2-Dichlorobenzene

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	characteristic
Odor Threshold	No information available.
pH	No information available.
Melting point	-17 °C
Boiling point/boiling range	356 °F (180 °C) at 1,013 hPa
Flash point	151 °F (66 °C) Method: DIN 51758
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	2.2 %(V)
Upper explosion limit	12 %(V)
Vapor pressure	1.33 hPa at 68 °F (20 °C)
Relative vapor density	5.1
Density	1.31 g/cm ³ at 68 °F (20 °C)

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number
Product name

DX0685
1,2-Dichlorobenzene

Version 1.1

Relative density	No information available.
Water solubility	0.13 g/l at 68 °F (20 °C)
Partition coefficient: n-octanol/water	log Pow: 3.43 Bioaccumulation is not expected. (Lit.)
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	1.32 mPa.s at 68 °F (20 °C)
Explosive properties	Not classified as explosive.
Oxidizing properties	none
Ignition temperature	1184 °F (640 °C)

SECTION 10. Stability and reactivity

Reactivity

Forms explosive mixtures with air on intense heating.
A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Violent reactions possible with:
Strong oxidizing agents, Alkali metals, Alkaline earth metals
Aluminum, Light metals, in the presence of:
Water, Acids

Conditions to avoid

Strong heating.

Incompatible materials

Aluminum, rubber, various plastics

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure
Inhalation, Eye contact, Skin contact

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX0685
Product name 1,2-Dichlorobenzene

Version 1.1

Target Organs

Eyes
Skin
Respiratory system
Liver
Kidneys

Acute oral toxicity

LD50 Rat: 500 mg/kg (RTECS)

absorption

Symptoms: Irritations of mucous membranes in the mouth, pharynx, oesophagus and gastrointestinal tract., Risk of aspiration upon vomiting., Aspiration may cause pulmonary edema and pneumonitis.

Acute inhalation toxicity

LC50 Rat: 8.15 mg/l; 4 h (IUCLID)

Irritating to respiratory system.

Symptoms: mucosal irritations, Cough, Shortness of breath, Possible damages:, damage of respiratory tract

Acute dermal toxicity

LD50 Rabbit: > 10,000 mg/kg
(RTECS)

absorption

Skin irritation

Rabbit
Result: Irritations
OECD Test Guideline 404

Repeated or prolonged exposure may cause skin irritation and dermatitis, due to degreasing properties of the product.

Causes skin irritation.

Eye irritation

Rabbit
Result: Eye irritation
OECD Test Guideline 405
Causes serious eye irritation.

Genotoxicity in vitro

Ames test
Result: negative
(IUCLID)

Specific target organ systemic toxicity - single exposure

May cause respiratory irritation.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number
Product name

DX0685
1,2-Dichlorobenzene

Version 1.1

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

After absorption of large quantities:

CNS disorders, psychoses, Headache, Dizziness, narcosis

After long-term exposure to the chemical:

Toxic effect on:

Liver, Kidney

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish

LC50 Danio rerio (zebra fish): 5.2 mg/l; 96 h

OECD Test Guideline 203

Toxicity to daphnia and other aquatic invertebrates

EC50 Daphnia magna (Water flea): 1.7 mg/l; 24 h (IUCLID)

Toxicity to algae

IC50 Desmodesmus subspicatus (green algae): 14 mg/l; 48 h (IUCLID)

Toxicity to bacteria

EC5 Pseudomonas putida: 15 mg/l; 16 h (IUCLID) (maximum permissible toxic concentration)

Persistence and degradability

Biodegradability

58 %; 20 d

OECD Test Guideline 301D

Not readily biodegradable.

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: 3.43

Bioaccumulation is not expected. (Lit.)

Mobility in soil

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX0685
Product name 1,2-Dichlorobenzene

Version 1.1

Distribution among environmental compartments

Adsorption/Soil

log K_{oc}: 2.58

(experimental)

Moderately mobile in soils

(Lit.)

Other adverse effects

Henry constant

194 Pa·m³/mol

Method: (experimental)

Distribution preferentially in air. (Lit.)

Additional ecological information

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 1591
Proper shipping name	O-DICHLOROBENZENE
Class	6.1
Packing group	III
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 1591
Proper shipping name	O-DICHLOROBENZENE
Class	6.1
Packing group	III
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

UN number	UN 1591
Proper shipping name	O-DICHLOROBENZENE
Class	6.1
Packing group	III
Environmentally hazardous	--

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX0685
Product name 1,2-Dichlorobenzene

Version 1.1

Special precautions for user yes
EmS F-A S-A

SECTION 15. Regulatory information

United States of America

SARA 313

The following components are subject to reporting levels established by SARA Title III, Section 313:

Ingredients

1,2-Dichlorobenzene	95-50-1	100 %
---------------------	---------	-------

SARA 302

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

The following Hazardous Substances are listed under the U.S. CleanWater Act, Section 311, Table 116.4A:

Ingredients

1,2-Dichlorobenzene

The following Hazardous Chemicals are listed under the U.S. CleanWater Act, Section 311, Table 117.3:

Ingredients

1,2-Dichlorobenzene

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Ingredients

1,2-Dichlorobenzene

Pennsylvania Right To Know

Ingredients

1,2-Dichlorobenzene

New Jersey Right To Know

Ingredients

1,2-Dichlorobenzene

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

DX0685

Version 1.1

Product name

1,2-Dichlorobenzene

Notification status

TSCA: All components of the product are listed in the TSCA-inventory.

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H227	Combustible liquid.
H302	Harmful if swallowed.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H331	Toxic if inhaled.
H335	May cause respiratory irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 09/25/2014

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.