

Datasheet

Human immunodeficiency virus type 1 P24 (core protein) monoclonal antibody, clone 340

Catalog Number: MAB6348

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against recombinant human immunodeficiency virus type 1 P24 (core protein).

Clone Name: 340

Immunogen: Recombinant protein corresponding to human immunodeficiency virus type 1 P24 core protein.

Host: Mouse

Reactivity: Human

Applications: Cap Ab, S-ELISA, WB
(See our web site product page for detailed applications information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Specificity: This antibody reacts with HIV-1 P24 (core protein).

Form: Lyophilized

Isotype: IgG1, kappa

Recommend Usage: Sandwich ELISA (Capture coating dose: 4 ug/mL)
Western Blot (0.1 ug/mL)
The optimal working dilution should be determined by the end user.

Storage Buffer: Lyophilized from 10 mM PBS, pH 7.2

Storage Instruction: Store at -20°C.
Aliquot after reconstitution to avoid repeated freezing and thawing.