

Datasheet

JUN (phospho T91/T93) monoclonal antibody, clone C-J 4C4

Catalog Number: MAB7251

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against phosphorylated JUN.

Clone Name: C-J 4C4

Immunogen: Human/Rat JUN phosphorylated at T91 and T93.

Host: Mouse

Reactivity: Human, Rat

Applications: WB

(See our web site product page for detailed applications information)

Protocols: See our web site at <http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Specificity: This recognizes c-Jun phosphorylated at T91 and T93, or just at T91 but not at T93 alone. Not yet tested in other species. Predicted molecular weight: 36 KDa. Not tested in other applications.

Form: Liquid

Isotype: IgG1

Recommend Usage: The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS

Storage Instruction: Store at 4°C for short term. For long term storage store at -20°C. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 3725|24516

Gene Symbol: JUN

Gene Alias: AP-1, AP1, c-Jun

References:

1. The ubiquitin ligase SCFFbw7 antagonizes apoptotic JNK signaling. Nateri AS, Riera-Sans L, Da Costa C, Behrens A. Science. 2004 Feb 27;303(5662):1374-8. Epub 2004 Jan 22.