

Datasheet

Apom polyclonal antibody

Catalog Number: PAB18690

Regulation Status: For research use only (RUO)

Product Description: Goat polyclonal antibody raised against synthetic peptide of Apom.

Immunogen: A synthetic peptide corresponding to amino acids at internal region of mouse Apom.

Sequence: C-KGNMELRTEGRPD

Host: Goat

Theoretical MW (kDa): 26

Reactivity: Human

Applications: ELISA, WB-Ti

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Concentration: 0.5 mg/mL

Recommend Usage: ELISA (1:8000)

Western Blot (0.5-1.5 ug/mL)

The optimal working dilution should be determined by the end user.

Storage Buffer: In Tris saline, pH 7.3 (0.02% sodium azide, 0.5% BSA)

Storage Instruction: Store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 55938

Gene Symbol: Apom

Gene Alias: 1190010O19Rik, G3a, NG20