

The Cooling Bath are water baths with air-cooled refrigerating unit. Housing and tank of stainless steel. The refrigerating unit works continuously.

\* Together with the immersion thermostats can the cooling baths be used up to 200 °C.

### Technical data according to DIN 12876

Operating temperature range	-30...200 °C
Cooling power	
at 20°C	0,4 kW
at 0°C	0,35 kW
at -10°C	0,27 kW
at -20°C	0,16 kW
at -30°C	0,065 kW
Refrigeration machine	air-cooled, natural refrigerant
Refrigerant	R290
Refrigerant quantity	0,072 kg
Bath volume	20 l
Width bath opening WxD/ bath depth	290x500/ 150 mm
Overall dimensions WxDxH **	350x555x448 mm
Net weight	35 kg
Power supply requirement	115V 1~ 60Hz
max. current	5,5 A
Fuse (1 phase)	10 A
min. ambient temperature	5 °C
max. ambient temperature	40 °C



**Order-No.: 2011.0003.99**

### from Serial-No.:

**1.0/10**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions.

Accessories and periphery: Drain valve with cap #6839, adjustable base #19655, trolley #6334, test tube racks Typ 1-4, Bath covers in various versions: see catalogue.

\* standard equipment

Output data valid for: Room temperature 20° C

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5%voltage and -2% frequency -> allowed.

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)