

Datasheet

NCK1 monoclonal antibody (M01), clone 1A1

Catalog Number: H00004690-M01

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against a partial recombinant NCK1.

Clone Name: 1A1

Immunogen: NCK1 (AAH06403, 185 a.a. ~ 294 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.

Sequence:

NLNTGQVLHVVQALYPFSSSNDEELNFEKGDVMDVIE
KPENDEWWKCRKINGMVGLVPKNYVTVMQNNPLTS
GLEPSPQCDDYIRPSLTGKFAGNPWYYGKVTRHQA
E M

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA, WB-Ce, WB-Re, WB-Tr
(See our web site product page for detailed applications information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Isotype: IgG1 Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 4690

Gene Symbol: NCK1

Gene Alias: MGC12668, NCK, NCKalpha

Gene Summary: The protein encoded by this gene is one of the signaling and transforming proteins containing Src homology 2 and 3 (SH2 and SH3) domains. It is

located in the cytoplasm and is an adaptor protein involved in transducing signals from receptor tyrosine kinases to downstream signal recipients such as RAS. [provided by RefSeq]