

Datasheet

OPRK1 polyclonal antibody

Catalog Number: PAB18980

Regulation Status: For research use only (RUO)

Product Description: Goat polyclonal antibody raised against synthetic peptide of OPRK1.

Immunogen: A synthetic peptide corresponding to amino acids at C-terminus of human OPRK1.

Sequence: C-PAYLRDIDGMNKP

Host: Goat

Theoretical MW (kDa): 45

Reactivity: Human

Applications: ELISA, WB-Ti

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Concentration: 0.5 mg/mL

Recommend Usage: ELISA (1:16000)

Western Blot (1-3 ug/mL)

The optimal working dilution should be determined by the end user.

Storage Buffer: In 0.5 mg/mL in Tris saline, pH7.3
(0.5% BSA, 0.02% sodium azide)

Storage Instruction: Store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 4986

Gene Symbol: OPRK1

Gene Alias: KOR, OPRK