

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/26/2014

1 Identification

- **Product identifier**
- **Trade name:** 3-Amino-4-methylpyridine
- **Article number:** 138460
- **CAS Number:**
3430-27-1
- **Application of the substance / the mixture** Laboratory chemicals for research and development
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
BeanTown Chemical
9 Sagamore Park Road
Hudson, NH 03051
USA
- Phone: (603) 402-2234
Fax: (603) 402-9713
Email: technical@beantownchem.com
www.beantownchem.com
- **Information department:** Technical Support Department
- **Emergency telephone number:**
During normal operating hours, please call (603) 402-2234
After hours, please call Chemtrec at (800) 424-9300

2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS06 Skull and crossbones

Acute Tox. 3 H301 Toxic if swallowed.

Acute Tox. 3 H311 Toxic in contact with skin.



GHS07

Skin Irrit. 2 H315 Causes skin irritation.

Eye Irrit. 2A H319 Causes serious eye irritation.

STOT SE 3 H335 May cause respiratory irritation.

-
- **Label elements**
 - **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
 - **Hazard pictograms**



GHS06

- **Signal word** Danger
- **Hazard-determining components of labeling:**
3-Amino-4-methylpyridine

(Contd. on page 2)

USA

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/26/2014

Trade name: 3-Amino-4-methylpyridine

(Contd. of page 1)

· Hazard statements*Toxic if swallowed or in contact with skin.**Causes skin irritation.**Causes serious eye irritation.**May cause respiratory irritation.***· Precautionary statements***If medical advice is needed, have product container or label at hand.**Keep out of reach of children.**Read label before use.**Avoid breathing dust/fume/gas/mist/vapors/spray**If swallowed: Immediately call a poison center/doctor.**If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.**Continue rinsing.**Specific treatment (see on this label).**Store locked up.**Dispose of contents/container in accordance with local/regional/national/international regulations.***· Other hazards****· Results of PBT and vPvB assessment****· PBT:** Not applicable.**· vPvB:** Not applicable.

3 Composition/information on ingredients

· Chemical characterization: Substances**· CAS No. Description**

3430-27-1 3-Amino-4-methylpyridine

4 First-aid measures

· Description of first aid measures**· General information:***Immediately remove any clothing soiled by the product.**In case of irregular breathing or respiratory arrest provide artificial respiration.***· After inhalation:** *In case of unconsciousness place patient stably in side position for transportation.***· After skin contact:** *Immediately wash with water and soap and rinse thoroughly.***· After eye contact:***Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.***· After swallowing:** *Do not induce vomiting; immediately call for medical help.***· Information for doctor:****· Most important symptoms and effects, both acute and delayed** *No further relevant information available.***· Indication of any immediate medical attention and special treatment needed***No further relevant information available.*

5 Fire-fighting measures

· Extinguishing media**· Suitable extinguishing agents:***CO₂, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.***· Special hazards arising from the substance or mixture** *No further relevant information available.*

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/26/2014

Trade name: 3-Amino-4-methylpyridine

(Contd. of page 2)

- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:**
 - Do not allow product to reach sewage system or any water course.
 - Inform respective authorities in case of seepage into water course or sewage system.
- **Methods and material for containment and cleaning up:**
 - Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
 - Dispose contaminated material as waste according to item 13.
 - Ensure adequate ventilation.
- **Reference to other sections**
 - See Section 7 for information on safe handling.
 - See Section 8 for information on personal protection equipment.
 - See Section 13 for disposal information.

7 Handling and storage

- **Handling:**
- **Precautions for safe handling**
 - Ensure good ventilation/exhaustion at the workplace.
 - Prevent formation of aerosols.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:**
 - Properly operating chemical fume hood designed for hazardous chemicals and having an average face velocity of at least 100 feet per minute
- **Control parameters**
- **Components with limit values that require monitoring at the workplace:** Not required.
- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
 - Keep away from foodstuffs, beverages and feed.
 - Immediately remove all soiled and contaminated clothing.
 - Wash hands before breaks and at the end of work.
 - Store protective clothing separately.
 - Avoid contact with the eyes and skin.

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/26/2014

Trade name: 3-Amino-4-methylpyridine

(Contd. of page 3)

· **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

· **Protection of hands:**

Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:** *Tightly sealed goggles*

9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form:	Powder
Color:	Not determined.
Odor:	Characteristic
Odour threshold:	Not determined.

· **pH-value:** Not determined.

· **Change in condition**

Melting point/Melting range:	102-107 °C (216-225 °F)
Boiling point/Boiling range:	Undetermined

· **Flash point:** Not applicable.

· **Flammability (solid, gaseous):** Not applicable.

· **Ignition temperature:**

Decomposition temperature: Not determined.

· **Auto igniting:** Not determined.

· **Danger of explosion:** Product does not present an explosion hazard.

· **Explosion limits:**

Lower:	Not determined.
Upper:	Not determined.

· **Vapor pressure:** Not determined.

· **Density:** Not determined.

· **Relative density** Not determined.

· **Vapour density** Not determined.

· **Evaporation rate** Not determined.

· **Solubility in / Miscibility with**

Water: Not miscible or difficult to mix.

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/26/2014

Trade name: 3-Amino-4-methylpyridine

(Contd. of page 4)

- **Partition coefficient (n-octanol/water):** Not determined.
- **Viscosity:**
 - Dynamic:** Not determined.
 - Kinematic:** Not determined.
 - Organic solvents:** 0.0 %
- **Other information** No further relevant information available.

10 Stability and reactivity

- **Reactivity**
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
 - on the skin:** Irritant to skin and mucous membranes.
 - on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)**

Substance is not listed.

- **NTP (National Toxicology Program)**

Substance is not listed.

- **OSHA-Ca (Occupational Safety & Health Administration)**

Substance is not listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:** Not known to be hazardous to water.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/26/2014

Trade name: 3-Amino-4-methylpyridine

(Contd. of page 5)

· **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

- | | |
|---|---|
| · UN-Number | |
| · DOT, IMDG, IATA | UN2811 |
| · UN proper shipping name | |
| · DOT | Toxic solids, organic, n.o.s. |
| · IMDG, IATA | TOXIC SOLID, ORGANIC, N.O.S. |
| · Transport hazard class(es) | |
| · DOT, IMDG, IATA | |
| · Class | 6.1 Toxic substances |
| · Packing group | |
| · DOT, IMDG, IATA | III |
| · Environmental hazards: | |
| · Marine pollutant: | No |
| · Special precautions for user | Warning: Toxic substances |
| · Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code | Not applicable. |
| · UN "Model Regulation": | UN2811, Toxic solids, organic, n.o.s., 6.1, III |

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**
- **Section 355 (extremely hazardous substances):**
Substance is not listed.
- **Section 313 (Specific toxic chemical listings):**
Substance is not listed.
- **TSCA (Toxic Substances Control Act):**
Substance is not listed.
- **Proposition 65**
- **Chemicals known to cause cancer:**
Substance is not listed.

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/26/2014

Trade name: 3-Amino-4-methylpyridine

(Contd. of page 6)

· Chemicals known to cause reproductive toxicity for females:

Substance is not listed.

· Chemicals known to cause reproductive toxicity for males:

Substance is not listed.

· Chemicals known to cause developmental toxicity:

Substance is not listed.

· Carcinogenic categories**· EPA (Environmental Protection Agency)**

Substance is not listed.

· TLV (Threshold Limit Value established by ACGIH)

Substance is not listed.

· NIOSH-Ca (National Institute for Occupational Safety and Health)

Substance is not listed.

· RTECS

Substance is not listed.

· Chemical safety assessment: A Chemical Safety Assessment has not been carried out.**16 Other information**

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· NFPA ratings (scale 0-4)

Health = 3

Fire = 0

Reactivity = 0

· HMIS ratings (scale 0-4)

Health = 3

Fire = 0

Reactivity = 0

· Department issuing SDS: Technical Support Department**· Contact: Technical Support Department****· Date of preparation / last revision 03/04/2015 / -****· Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

CAS: Chemical Abstracts Service (division of the American Chemical Society)

Acute Tox. 3: Acute toxicity, Hazard Category 3

Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2

Eye Irrit. 2A: Serious eye damage/eye irritation, Hazard Category 2A

STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3