

## Datasheet

### CCNY polyclonal antibody

**Catalog Number:** PAB22709

**Regulation Status:** For research use only (RUO)

**Product Description:** Rabbit polyclonal antibody raised against recombinant CCNY.

**Immunogen:** Recombinant protein corresponding to amino acids of human CCNY.

**Sequence:**

GNTTSCCVSSSPKLRRNAHSRLESYRPDTDLSDREDTG  
CNLQHISDRENIDDLNMEFNPS

**Host:** Rabbit

**Reactivity:** Human

**Applications:** IHC-P

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Form:** Liquid

**Purification:** Antigen affinity purification

**Isotype:** IgG

**Recommend Usage:** Immunohistochemistry

(1:50-1:200)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

**Storage Instruction:** Store at 4°C. For long term storage store at -20°C.  
Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 219771

**Gene Symbol:** CCNY

**Gene Alias:** C10orf9, CBCP1, CFP1, FLJ95513

**Gene Summary:** Cyclins, such as CCNY, control cell division cycles and regulate cyclin-dependent kinases (e.g., CDC2; MIM 116940) (Li et al., 2009 [PubMed 18060517]).[supplied by OMIM]