

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 03/11/2013 Version 1.0

SECTION 1. Identification

Product identifier

Product number 816144

Product name Oxalic acid anhydrous for synthesis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses Chemical for synthesis

Details of the supplier of the safety data sheet

Company EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821,

United States of America | SDS Phone Support: +1-978-715-1335 | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to

4:00 PM Eastern Time (GMT-5)

e-mail: mm_sds@merckgroup.com

Emergency telephone 800-424-9300 CHEMTREC (USA)

+1-703-527-3887 CHEMTREC (International)

24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Acute toxicity, Category 4, Oral, H302 Acute toxicity, Category 4, Dermal, H312

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word Warning

Hazard Statements

H302 + H312 Harmful if swallowed or in contact with skin.

Precautionary Statements

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816144 Version 1.0

Product name Oxalic acid anhydrous for synthesis

P262 Do not get in eyes, on skin, or on clothing.

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula HOOCCOOH C₂H₂O₄ (Hill)

CAS-No. 144-62-7 Molar mass 90.03 g/mol

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

Oxalic acid (>= 90 % - <= 100 %)

144-62-7

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing. Consult a

physician.

Eye contact

After eye contact: rinse out with plenty of water with the eyelid held wide open. Call in ophthalmologist if necessary.

Ingestion

After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Irritation and corrosion, agitation, spasms, Nausea, Vomiting, cardiovascular disorders, collapse The following applies to oxalates in general: nausea and vomiting after swallowing. Mucosal irritations, coughing, and dyspnoea after inhalation. Systemic effect: drop in the blood calcium level, toxic effect on kidneys, cardiovascular disorders.

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816144 Version 1.0

Product name Oxalic acid anhydrous for synthesis

Suitable extinguishing media

Water, Carbon dioxide (CO2), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.

Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Avoid inhalation of dusts. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry.

Store at +15°C to +25°C (+59°F to +77°F).

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816144 Version 1.0

Product name Oxalic acid anhydrous for synthesis

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

,		
Inc	redie	ntc

rrigicalcins			
Basis	Value	Threshold limits	Remarks
Oxalic acid 14	<i>4-62-7</i>		
ACGIH	Short Term Exposure Limit (STEL):	2 mg/m³	
	Time Weighted Average (TWA):	1 mg/m³	
NIOSH/GUIDE	Recommended exposure limit (REL):	1 mg/m³	
	Short Term Exposure Limit (STEL):	2 mg/m³	
OSHA_TRANS	PEL:	1 mg/m³	
Z1A	Short Term Exposure Limit (STEL):	2 mg/m³	
	Time Weighted Average (TWA):	1 mg/m³	

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when dusts are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state solid

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number Version 1.0 Product name Oxalic acid anhydrous for synthesis

Color white

Odor odorless

Odor Threshold not applicable

рΗ ca. 1

> at 100 g/l 68 °F (20 °C)

189 °C Melting point

(decomposition)

Boiling point No information available.

Flash point not applicable, (decomposition)

Evaporation rate No information available.

Flammability (solid, gas) No information available.

Lower explosion limit No information available.

Upper explosion limit No information available.

Vapor pressure 21.5 hPa

at 122 °F (50 °C)

No information available. Relative vapor density

1.9 g/cm³ Relative density

at 68 °F (20 °C)

Water solubility 220 g/l

> at 77 °F (25 °C) (experimental)

Partition coefficient: n-

log Pow: -0.81 (30 °C)

octanol/water (IUCLID) Bioaccumulation is not expected (log Pow <1).

Autoignition temperature No information available.

Decomposition temperature > 315 °F (> 157 °C)

Viscosity, dynamic No information available.

Explosive properties No information available.

Bulk density ca. 750 kg/m3

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816144 Version 1.0

Product name Oxalic acid anhydrous for synthesis

SECTION 10. Stability and reactivity

Reactivity

The following applies in general to flammable organic substances and mixtures: in correspondingly fine distribution, when whirled up a dust explosion potential may generally be assumed.

Chemical stability

sensitive to moisture

Possibility of hazardous reactions

Risk of explosion with:

chlorates, sodium hypochlorite, Strong oxidizing agents, silver, salts of oxyhalogenic acids

Exothermic reaction with:

bases, Ammonia, Mercury

Conditions to avoid

Strong heating (decomposition).

Incompatible materials

no information available

Hazardous decomposition products

no information available

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact, Ingestion

Target Organs

Eyes

Skin

Respiratory system

. Kidneys

Acute oral toxicity

LD50 rat: 375 mg/kg (IUCLID)

absorption

Symptoms: Irritations of mucous membranes in the mouth, pharynx, oesophagus and gastrointestinal tract.

Acute dermal toxicity

absorption

Skin irritation slight irritation

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816144 Version 1.0

Product name Oxalic acid anhydrous for synthesis

Eye irritation

rabbit

Result: Severe irritations

(IUCLID) (Regulation (EC) No 1272/2008, Annex VI)

Genotoxicity in vitro

Ames test Result: negative

(Lit.)

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC No ingredient of this product present at levels greater than or

equal to 0.1% is identified as probable, possible or confirmed

human carcinogen by IARC.

OSHA No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

NTP No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a known or anticipated carcinogen

by NTP.

ACGIH No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by ACGIH.

Further information

Systemic effects:

After absorption:

agitation, spasms, Nausea, Vomiting, cardiovascular disorders, collapse, disturbed electrolyte balance.

Secondary products cause:

Damage to:

Kidney

The following applies to oxalates in general: nausea and vomiting after swallowing. Mucosal irritations, coughing, and dyspnoea after inhalation. Systemic effect: drop in the blood calcium level, toxic effect on kidneys, cardiovascular disorders.

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816144 Version 1.0

Product name Oxalic acid anhydrous for synthesis

Toxicity to fish

LC50 Leuciscus idus (Golden orfe): 160 mg/l; 48 h (IUCLID)

Toxicity to daphnia and other aquatic invertebrates

EC50 Daphnia magna (Water flea): 137 mg/l; 48 h (IUCLID)

Persistence and degradability

Biodegradability 40 %; 5 d (IUCLID)

Biochemical Oxygen Demand (BOD)

160 mg/g (5 d)

(IUCLID)

Chemical Oxygen Demand (COD)

180 mg/g (IUCLID)

Theoretical oxygen demand (ThOD)

180 mg/g

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: -0.81 (30 °C)

(IUCLID) Bioaccumulation is not expected (log Pow <1).

Mobility in soil

No information available.

Other adverse effects

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number UN 3261

Proper shipping name CORROSIVE SOLID, ACIDIC, ORGANIC, N.O.S. (OXALIC

ACID)

Class 8
Packing group II
Environmentally hazardous --

Air transport (IATA)

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number Version 1.0

Product name Oxalic acid anhydrous for synthesis

UN number UN 3261

Proper shipping name CORROSIVE SOLID, ACIDIC, ORGANIC, N.O.S. (OXALIC

ACID)

Class 8 Packing group Ш **Environmentally hazardous** Special precautions for user no

Sea transport (IMDG)

UN number UN 3261

Proper shipping name CORROSIVE SOLID, ACIDIC, ORGANIC, N.O.S. (OXALIC

ACID)

Class 8 Packing group Ш **Environmentally hazardous** Special precautions for user ves **EmS**

F-A S-B

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Toxic by ingestion

Target organ effects

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Acute Health Hazard Chronic Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816144 Version 1.0

Product name Oxalic acid anhydrous for synthesis

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311,

Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311,

Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

TSCA 12b

Ingredients

Oxalic acid 144-62-7

Massachusetts Right To Know

Ingredients

Oxalic acid

Pennsylvania Right To Know

Ingredients

Oxalic acid

New Jersey Right To Know

Ingredients

Oxalic acid

Notification status

TSCA: On TSCA Inventory

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H302 Harmful if swallowed.
H312 Harmful in contact with skin.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

MATERIAL SAFETY DATA SHEET according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816144 Version 1.0

Product name Oxalic acid anhydrous for synthesis

Date of issue:03/11/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.