



# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 03/11/2013

Version 1.0

## SECTION 1. Identification

### Product identifier

Product number	820032
Product code	820032
Product name	2-Ethyl-1,3-hexanediol (mixture of DL-and meso-form) for synthesis

### Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Chemical for synthesis
-----------------	------------------------

### Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation   290 Concord Road, Billerica, MA 01821, United States of America   SDS Phone Support: +1-978-715-1335   General Inquiries: +1-978-715-4321   Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)  e-mail: mm_sds@merckgroup.com
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

## SECTION 2. Hazards identification

### GHS Classification

Serious eye damage, Category 1, H318

For the full text of the H-Statements mentioned in this Section, see Section 16.

### GHS-Labeling

*Hazard pictograms*



*Signal Word*

Danger

*Hazard Statements*

H318 Causes serious eye damage.

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 820032 Version 1.0  
Product name 2-Ethyl-1,3-hexanediol (mixture of DL-and meso-form) for synthesis

---

## *Precautionary Statements*

P280 Wear eye protection.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

## **OSHA Hazards**

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

## **Other hazards**

None known.

---

## **SECTION 3. Composition/information on ingredients**

Formula	$\text{CH}_3\text{CH}_2\text{CH}_2\text{CH}(\text{OH})\text{CH}(\text{C}_2\text{H}_5)\text{CH}_2\text{OH}$	$\text{C}_8\text{H}_{18}\text{O}_2$ (Hill)
CAS-No.	94-96-2	
Molar mass	146.23 g/mol	

## **Hazardous ingredients**

*Chemical Name ( Concentration)*

CAS-No.

*2-Ethylhexane-1,3-diol ( >= 90 % - <= 100 % )*

94-96-2

---

## **SECTION 4. First aid measures**

### **Description of first-aid measures**

#### *Inhalation*

After inhalation: fresh air.

#### *Skin contact*

After skin contact: wash off with plenty of water. Remove contaminated clothing.

#### *Eye contact*

After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

#### *Ingestion*

After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

### **Most important symptoms and effects, both acute and delayed**

irritant effects, Dizziness, Nausea, Vomiting

Risk of serious damage to eyes.

### **Indication of any immediate medical attention and special treatment needed**

No information available.

---

## **SECTION 5. Fire-fighting measures**

### **Extinguishing media**

*Suitable extinguishing media*

Carbon dioxide (CO<sub>2</sub>), Foam, Dry powder

---

## MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

820032

Version 1.0

Product name

2-Ethyl-1,3-hexanediol (mixture of DL-and meso-form) for synthesis

---

### *Unsuitable extinguishing media*

For this substance/mixture no limitations of extinguishing agents are given.

### **Special hazards arising from the substance or mixture**

Combustible.

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air on intense heating.

Development of hazardous combustion gases or vapors possible in the event of fire.

### **Advice for firefighters**

*Special protective equipment for fire-fighters*

In the event of fire, wear self-contained breathing apparatus.

*Further information*

Prevent fire extinguishing water from contaminating surface water or the ground water system.

---

## **SECTION 6. Accidental release measures**

### **Personal precautions, protective equipment and emergency procedures**

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

### **Environmental precautions**

Do not empty into drains.

### **Methods and materials for containment and cleaning up**

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent material (e.g. Chemisorb®). Dispose of properly. Clean up affected area.

---

## **SECTION 7. Handling and storage**

### **Precautions for safe handling**

Observe label precautions.

### **Conditions for safe storage, including any incompatibilities**

Tightly closed.

Store at +15°C to +25°C (+59°F to +77°F).

---

## **SECTION 8. Exposure controls/personal protection**

### **Exposure limit(s)**

Contains no substances with occupational exposure limit values.

### **Engineering measures**

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

---

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

820032

Version 1.0

Product name

2-Ethyl-1,3-hexanediol (mixture of DL-and meso-form) for synthesis

---

## Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

### *Hygiene measures*

Change contaminated clothing. Application of skin- protective barrier cream recommended.  
Wash hands after working with substance.

### *Eye/face protection*

Tightly fitting safety goggles

### *Hand protection*

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

### *Other protective equipment:*

protective clothing

### *Respiratory protection*

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

---

## SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	odorless
Odor Threshold	No information available.
pH	No information available.
Melting point	-40 °C
Boiling point/boiling range	466 - 480 °F ( 241 - 249 °C) at 1,013 hPa
Flash point	277 °F ( 136 °C) Method: c.c.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.

---

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 820032 Version 1.0  
Product name 2-Ethyl-1,3-hexanediol (mixture of DL-and meso-form) for synthesis

---

Vapor pressure	< 0.01 hPa at 68 °F ( 20 °C)
Relative vapor density	5.03
Relative density	0.94 g/cm <sup>3</sup> at 68 °F ( 20 °C)
Water solubility	42 g/l at 68 °F ( 20 °C)
Partition coefficient: n-octanol/water	log Pow: 1.6 (calculated) (Lit.) Bioaccumulation is not expected (log Pow <1).
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	323 mPa.s at 68 °F ( 20 °C)
Explosive properties	Not classified as explosive.
Ignition temperature	644 °F ( 340 °C) DIN 51794
Refractive index	1.4530 ( 589 nm) at 72 °F ( 22 °C)

---

## SECTION 10. Stability and reactivity

### Reactivity

Forms explosive mixtures with air on intense heating.

### Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

### Possibility of hazardous reactions

Violent reactions possible with:

Oxidizing agents, acids

### Conditions to avoid

Strong heating.

A range from approx. 15 Kelvin below the flash point is to be rated as critical.

### Incompatible materials

no information available

### Hazardous decomposition products

no information available

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

820032

Version 1.0

Product name

2-Ethyl-1,3-hexanediol (mixture of DL-and meso-form) for synthesis

---

## SECTION 11. Toxicological information

### Information on toxicological effects

#### *Likely route of exposure*

Eye contact, Skin contact

#### *Acute oral toxicity*

LD50 rat: 5,170 mg/kg (External MSDS)

Symptoms: Nausea, Vomiting

#### *Acute inhalation toxicity*

Symptoms: Possible damages:, mucosal irritations

#### *Acute dermal toxicity*

LD50 rabbit: 2,000 mg/kg  
(RTECS)

absorption

#### *Skin irritation*

rabbit

Result: slight irritation  
(Lit.)

#### *Eye irritation*

rabbit

Result: Severe irritations  
(RTECS)

Causes serious eye damage.

#### *Sensitization*

In animal experiments:

Result: negative  
(Lit.)

#### *Genotoxicity in vitro*

Ames test

Result: negative  
(External MSDS)

#### *Specific target organ systemic toxicity - single exposure*

The substance or mixture is not classified as specific target organ toxicant, single exposure.

#### *Specific target organ systemic toxicity - repeated exposure*

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

#### *Aspiration hazard*

Regarding the available data the classification criteria are not fulfilled.

### Carcinogenicity

IARC

No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

## MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	820032	Version 1.0
Product name	2-Ethyl-1,3-hexanediol (mixture of DL-and meso-form) for synthesis	

---

OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

### Further information

After absorption of large quantities:

Dizziness

Further data:

Handle in accordance with good industrial hygiene and safety practice.

---

## SECTION 12. Ecological information

### Ecotoxicity

#### *Toxicity to fish*

LC0 *Leuciscus idus* (Golden orfe): > 1,000 mg/l; 48 h (External MSDS)

#### *Toxicity to daphnia and other aquatic invertebrates*

EC50 *Daphnia magna* (Water flea): 811 mg/l; 24 h (External MSDS)

#### *Toxicity to bacteria*

EC10 *Pseudomonas putida*: 1,300 mg/l; 18 h (External MSDS)

### Persistence and degradability

No information available.

### Bioaccumulative potential

#### *Partition coefficient: n-octanol/water*

log Pow: 1.6

(calculated)

(Lit.) Bioaccumulation is not expected (log Pow <1).

### Mobility in soil

No information available.

### Other adverse effects

---

## SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

820032

Version 1.0

Product name

2-Ethyl-1,3-hexanediol (mixture of DL-and meso-form) for synthesis

---

## SECTION 14. Transport information

### Land transport (DOT)

Not classified as dangerous in the meaning of transport regulations.

### Air transport (IATA)

Not classified as dangerous in the meaning of transport regulations.

### Sea transport (IMDG)

Not classified as dangerous in the meaning of transport regulations.

---

## SECTION 15. Regulatory information

### United States of America

#### OSHA Hazards

Harmful by skin absorption.

Corrosive to eyes

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

#### SARA 311/312 Hazards

Acute Health Hazard

#### SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

#### SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

#### Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

#### DEA List I

Not listed

#### DEA List II

Not listed

#### Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

#### Pennsylvania Right To Know

*Ingredients*

2-Ethylhexane-1,3-diol

---



# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 820032 Version 1.0  
Product name 2-Ethyl-1,3-hexanediol (mixture of DL-and meso-form) for synthesis

---

## New Jersey Right To Know

### *Ingredients*

2-Ethylhexane-1,3-diol

### Notification status

TSCA: On TSCA Inventory

DSL: All components of this product are on the Canadian DSL.

---

## SECTION 16. Other information

### Training advice

Provide adequate information, instruction and training for operators.

### Full text of H-Statements referred to under sections 2 and 3.

H318 Causes serious eye damage.

### Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at [www.wikipedia.org](http://www.wikipedia.org).

Date of issue:03/11/2013

---

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

*All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.*