



MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 03/10/2013

Version 1.0

SECTION 1. Identification

Product identifier

Product number	821131
Product name	4-Methylbenzoyl chloride for synthesis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Chemical for synthesis
-----------------	------------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America SDS Phone Support: +1-978-715-1335 General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Skin corrosion, Category 1B, H314
Specific target organ systemic toxicity - single exposure, Category 3, H335
For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

Hazard Statements

H314 Causes severe skin burns and eye damage.
H335 May cause respiratory irritation.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 821131
Product name 4-Methylbenzoyl chloride for synthesis

Version 1.0

Precautionary Statements

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P301 + P330 + P331 IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P309 + P310 IF exposed or if you feel unwell: Immediately call a POISON CENTER or doctor/physician.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	4-(CH ₃)C ₆ H ₄ COCl	C ₈ H ₇ ClO (Hill)
CAS-No.	874-60-2	
Molar mass	154.6 g/mol	

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

p-Toluoyl chloride (>= 90 % - <= 100 %)
874-60-2

SECTION 4. First aid measures

Description of first-aid measures

General advice

First aider needs to protect himself.

Inhalation

After inhalation: fresh air. Call in physician.

Skin contact

After skin contact: wash off with plenty of water. Immediately remove contaminated clothing. If available swab with polyethylene glycol 400. Call a physician immediately.

Eye contact

After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

Ingestion

After swallowing: make victim drink water (two glasses at most), avoid vomiting (risk of perforation!). Call a physician immediately. Do not attempt to neutralize.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Irritation and corrosion, Cough, Shortness of breath
Risk of blindness!

Indication of any immediate medical attention and special treatment needed

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 821131
Product name 4-Methylbenzoyl chloride for synthesis

Version 1.0

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂), Dry powder

Unsuitable extinguishing media

Water, Foam

Special hazards arising from the substance or mixture

Combustible.

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air on intense heating.

Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:

Hydrogen chloride gas, Phosgene

May not get in touch with:

Water

Caution! in contact with water product releases:

Hydrogen chloride gas

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent material (e.g. Chemisorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 821131
Product name 4-Methylbenzoyl chloride for synthesis

Version 1.0

Keep workplace dry. Do not allow product to come into contact with water.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Tightly fitting safety goggles

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	stinging
Odor Threshold	No information available.
pH	1 at 68 °F (20 °C)
Melting point	-2 °C

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	821131	Version 1.0
Product name	4-Methylbenzoyl chloride for synthesis	

Boiling point/boiling range	437 - 441 °F (225 - 227 °C) at 1,013 hPa
Flash point	180 °F (82 °C) Method: c.c.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	1.6 %(V)
Upper explosion limit	No information available.
Vapor pressure	0.1 hPa at 68 °F (20 °C)
Relative vapor density	No information available.
Relative density	1.17 g/cm ³ at 68 °F (20 °C)
Water solubility	at 68 °F (20 °C) (decomposition)
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.

SECTION 10. Stability and reactivity

Reactivity

Forms explosive mixtures with air on intense heating.

Chemical stability

sensitive to moisture

Possibility of hazardous reactions

Violent reactions possible with:

Water, Alcohols, Amines, alkalines

Conditions to avoid

Strong heating.

A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Exposure to moisture.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 821131
Product name 4-Methylbenzoyl chloride for synthesis

Version 1.0

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Inhalation, Eye contact, Skin contact

Acute oral toxicity

Symptoms: If ingested, severe burns of the mouth and throat, as well as a danger of perforation of the esophagus and the stomach.

Acute inhalation toxicity

Symptoms: mucosal irritations, Cough, Shortness of breath, Possible damages:., damage of respiratory tract

Irritating to respiratory system.

Skin irritation

Causes burns.

Eye irritation

Causes serious eye damage.

Risk of blindness!

Specific target organ systemic toxicity - single exposure

May cause respiratory irritation.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 821131
Product name 4-Methylbenzoyl chloride for synthesis

Version 1.0

Further information

Decomposition of the substance with tissue moisture.
Other dangerous properties can not be excluded.
Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Other adverse effects

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 3265
Proper shipping name	CORROSIVE LIQUID, ACIDIC, ORGANIC, N.O.S. (4-METHYLBENZOYL CHLORIDE)
Class	8
Packing group	II
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 3265
Proper shipping name	CORROSIVE LIQUID, ACIDIC, ORGANIC, N.O.S. (4-METHYLBENZOYL CHLORIDE)
Class	8
Packing group	II
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 821131
Product name 4-Methylbenzoyl chloride for synthesis

Version 1.0

UN number	UN 3265
Proper shipping name	CORROSIVE LIQUID, ACIDIC, ORGANIC, N.O.S. (4-METHYLBENZOYL CHLORIDE)
Class	8
Packing group	II
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-A S-B

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Combustible Liquid
Corrosive to skin
Corrosive to eyes
Respiratory irritant

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Fire Hazard
Acute Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Ingredients

p-Toluoyl chloride

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 821131

Version 1.0

Product name 4-Methylbenzoyl chloride for synthesis

New Jersey Right To Know

Ingredients

p-Toluoyl chloride

Notification status

TSCA: On TSCA Inventory

DSL: This product contains one or several components listed in the Canadian NDSL.

Ingredients

p-Toluoyl chloride

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H314 Causes severe skin burns and eye damage.

H335 May cause respiratory irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Date of issue:03/10/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.