



MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 03/11/2013

Version 1.0

SECTION 1. Identification

Product identifier

| | |
|----------------|-----------------------------|
| Product number | 807333 |
| Product name | n-Pentylamine for synthesis |

Relevant identified uses of the substance or mixture and uses advised against

| | |
|-----------------|------------------------|
| Identified uses | Chemical for synthesis |
|-----------------|------------------------|

Details of the supplier of the safety data sheet

| | |
|---------|--|
| Company | EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America SDS Phone Support: +1-978-715-1335 General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com |
|---------|--|

| | |
|---------------------|--|
| Emergency telephone | 800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week |
|---------------------|--|

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 2, H225
Acute toxicity, Category 4, Dermal, H312
Acute toxicity, Category 4, Oral, H302
Skin corrosion, Category 1B, H314

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

Hazard Statements

H225 Highly flammable liquid and vapor.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807333
Product name n-Pentylamine for synthesis

Version 1.0

H302 + H312 Harmful if swallowed or in contact with skin.
H314 Causes severe skin burns and eye damage.

Precautionary Statements

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P233 Keep container tightly closed.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P301 + P330 + P331 IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P309 + P310 IF exposed or if you feel unwell: Immediately call a POISON CENTER or doctor/physician.
P403 + P235 Store in a well-ventilated place. Keep cool.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

| | | |
|------------|---|--|
| Formula | $\text{CH}_3(\text{CH}_2)_4\text{NH}_2$ | $\text{C}_5\text{H}_{13}\text{N}$ (Hill) |
| CAS-No. | 110-58-7 | |
| Molar mass | 87.16 g/mol | |

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

n-pentylamine (>= 90 % - <= 100 %)
110-58-7

SECTION 4. First aid measures

Description of first-aid measures

General advice

First aider needs to protect himself.

Inhalation

After inhalation: fresh air. Call in physician.

Skin contact

After skin contact: wash off with plenty of water. Immediately remove contaminated clothing. If available swab with polyethylene glycol 400. Call a physician immediately.

Eye contact

After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

Ingestion

After swallowing: make victim drink water (two glasses at most), avoid vomiting (risk of perforation!). Call a physician immediately. Do not attempt to neutralize.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807333
Product name n-Pentylamine for synthesis

Version 1.0

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Irritation and corrosion, Cough, Shortness of breath, Unconsciousness, Vomiting, Risk of corneal clouding.
Risk of blindness!

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air at ambient temperatures.

Pay attention to flashback.

Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:

nitrogen oxides

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Cool closed containers exposed to fire with water spray. Prevent fire extinguishing water from contaminating surface water or the ground water system. Suppress (knock down) gases/vapors/mists with a water spray jet.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Keep away from heat and sources of ignition. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains. Risk of explosion.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807333
Product name n-Pentylamine for synthesis

Version 1.0

Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Advice on protection against fire and explosion

Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

Conditions for safe storage, including any incompatibilities

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat and sources of ignition.

Requirements for storage areas and containers

Do not use light-weight-metal containers.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Tightly fitting safety goggles

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

Flame retardant antistatic protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807333
Product name n-Pentylamine for synthesis

Version 1.0

SECTION 9. Physical and chemical properties

| | |
|--|---|
| Physical state | liquid |
| Color | colorless |
| Odor | amine-like |
| Odor Threshold | No information available. |
| pH | No information available. |
| Melting point | -50 °C |
| Boiling point/boiling range | 217 °F (103 °C) at 1,013 hPa |
| Flash point | 45 °F (7 °C) |
| Evaporation rate | No information available. |
| Flammability (solid, gas) | No information available. |
| Lower explosion limit | 2.2 %(V) |
| Upper explosion limit | 22 %(V) |
| Vapor pressure | 34.4 hPa at 72 °F (22 °C) 120.9 hPa at 117 °F (47 °C) |
| Relative vapor density | 3.0 |
| Relative density | 0.75 g/cm ³ at 68 °F (20 °C) |
| Water solubility | at 68 °F (20 °C) soluble |
| Partition coefficient: n-octanol/water | log Pow: 1.49 (experimental) (Lit.) Bioaccumulation is not expected (log Pow <1). |
| Autoignition temperature | No information available. |
| Decomposition temperature | No information available. |

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

| | | |
|----------------|-----------------------------|-------------|
| Product number | 807333 | Version 1.0 |
| Product name | n-Pentylamine for synthesis | |

| | |
|----------------------|---------------------------------------|
| Viscosity, dynamic | 1.2 mPa.s at 68 °F (20 °C) |
| Explosive properties | Not classified as explosive. |
| Ignition temperature | 581 °F (305 °C) Method: DIN 51794 |

SECTION 10. Stability and reactivity

Reactivity

Vapors may form explosive mixture with air.

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Caution! In contact with nitrites, nitrates, nitrous acid possible liberation of nitosamines!

Violent reactions possible with:

Strong oxidizing agents, acid halides, Acid anhydrides, Light metals, Nitriles, phenols, acids

Conditions to avoid

Warming.

A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Incompatible materials

various plastics, Copper, Copper alloys

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Inhalation, Eye contact, Skin contact

Acute oral toxicity

LD50 rat: 470 mg/kg (External MSDS)

Symptoms: If ingested, severe burns of the mouth and throat, as well as a danger of perforation of the esophagus and the stomach.

absorption

Acute inhalation toxicity

Symptoms: mucosal irritations, Cough, Shortness of breath, Lung edema, Possible damages:, damage of respiratory tract

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807333
Product name n-Pentylamine for synthesis

Version 1.0

Acute dermal toxicity

LD50 rabbit: 1,120 mg/kg
(External MSDS)

absorption

Skin irritation

Causes burns.

Eye irritation

Causes serious eye damage. Risk of corneal clouding. Risk of blindness!

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

| | |
|-------|--|
| IARC | No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC. |
| OSHA | No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA. |
| NTP | No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP. |
| ACGIH | No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH. |

Further information

After absorption:

Vomiting, Unconsciousness

Under given conditions, contact with nitrites or nitric acid can lead to the formation of nitrosamines, which have shown themselves to be carcinogenic in animal experiments.

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish

LC50 Pimephales promelas (fathead minnow): 177 mg/l; 96 h (ECOTOX Database)

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807333
Product name n-Pentylamine for synthesis

Version 1.0

Toxicity to daphnia and other aquatic invertebrates

EC50 Daphnia magna (Water flea): 27 - 170 mg/l; 48 h (ECOTOX Database)

Persistence and degradability

No information available.

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: 1.49

(experimental)

(Lit.) Bioaccumulation is not expected (log Pow <1).

Mobility in soil

No information available.

Other adverse effects

Additional ecological information

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

| | |
|---------------------------|------------|
| UN number | UN 1106 |
| Proper shipping name | AMYLAMINES |
| Class | 3 (8) |
| Packing group | II |
| Environmentally hazardous | -- |

Air transport (IATA)

| | |
|------------------------------|-----------|
| UN number | UN 1106 |
| Proper shipping name | AMYLAMINE |
| Class | 3 (8) |
| Packing group | II |
| Environmentally hazardous | -- |
| Special precautions for user | no |

Sea transport (IMDG)

| | |
|------------------------------|------------|
| UN number | UN 1106 |
| Proper shipping name | AMYLAMINES |
| Class | 3 (8) |
| Packing group | II |
| Environmentally hazardous | -- |
| Special precautions for user | yes |

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807333
Product name n-Pentylamine for synthesis

Version 1.0

EmS

F-E S-C

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Flammable Liquid
Toxic by ingestion
Harmful by skin absorption.
Corrosive to skin

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Fire Hazard
Acute Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

Massachusetts Right To Know

Ingredients
n-pentylamine

Pennsylvania Right To Know

Ingredients
n-pentylamine

New Jersey Right To Know

Ingredients
n-pentylamine

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807333
Product name n-Pentylamine for synthesis

Version 1.0

Notification status

TSCA: On TSCA Inventory

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

| | |
|------|--|
| H225 | Highly flammable liquid and vapor. |
| H302 | Harmful if swallowed. |
| H312 | Harmful in contact with skin. |
| H314 | Causes severe skin burns and eye damage. |

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Date of issue:03/11/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.