

# Safety Data Sheet

**acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)**

Printing date 03/03/2015

Reviewed on 11/21/2014

## 1 Identification

- **Product identifier**
- **Trade name:** 2-Cyclopenten-1-one
- **Article number:** 212505
- **CAS Number:**  
930-30-3
- **EC number:**  
213-213-0
- **Application of the substance / the mixture** Laboratory chemicals for research and development
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
BeanTown Chemical  
9 Sagamore Park Road  
Hudson, NH 03051  
USA
- 
- Phone: (603) 402-2234  
Fax: (603) 402-9713  
Email: [technical@beantownchem.com](mailto:technical@beantownchem.com)  
[www.beantownchem.com](http://www.beantownchem.com)
- **Information department:** Technical Support Department
- **Emergency telephone number:**  
During normal operating hours, please call (603) 402-2234  
After hours, please call Chemtrec at (800) 424-9300

## 2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS02 Flame

Flam. Liq. 3 H226 Flammable liquid and vapour.



GHS07

STOT SE 3 H335 May cause respiratory irritation.

- **Label elements**
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS02



GHS07

- **Signal word** Warning
- **Hazard-determining components of labeling:**  
2-Cyclopenten-1-one
- **Hazard statements**  
Flammable liquid and vapour.  
May cause respiratory irritation.

(Contd. on page 2)

# Safety Data Sheet

## acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/03/2015

Reviewed on 11/21/2014

**Trade name: 2-Cyclopenten-1-one**

(Contd. of page 1)

- **Precautionary statements**

*If medical advice is needed, have product container or label at hand.*

*Keep out of reach of children.*

*Read label before use.*

*Keep away from heat/sparks/open flames/hot surfaces. - No smoking.*

*Use explosion-proof electrical/ventilating/lighting/equipment.*

*Avoid breathing dust/fume/gas/mist/vapors/spray*

*IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower.*

*Store locked up.*

*Dispose of contents/container in accordance with local/regional/national/international regulations.*

- **Other hazards**

- **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.

- **vPvB:** Not applicable.

### 3 Composition/information on ingredients

- **Chemical characterization: Substances**

- **CAS No. Description**

930-30-3 2-Cyclopenten-1-one

- **Identification number(s)**

- **EC number:** 213-213-0

### 4 First-aid measures

- **Description of first aid measures**

- **After inhalation:** Supply fresh air; consult doctor in case of complaints.

- **After skin contact:** Generally the product does not irritate the skin.

- **After eye contact:** Rinse opened eye for several minutes under running water.

- **After swallowing:** If symptoms persist consult doctor.

- **Information for doctor:**

- **Most important symptoms and effects, both acute and delayed** No further relevant information available.

- **Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

### 5 Fire-fighting measures

- **Extinguishing media**

- **Suitable extinguishing agents:** CO<sub>2</sub>, sand, extinguishing powder. Do not use water.

- **For safety reasons unsuitable extinguishing agents:** Water with full jet

- **Special hazards arising from the substance or mixture** No further relevant information available.

- **Advice for firefighters**

- **Protective equipment:** No special measures required.

### 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**

*Wear protective equipment. Keep unprotected persons away.*

- **Environmental precautions:** No special measures required.

- **Methods and material for containment and cleaning up:**

*Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).*

(Contd. on page 3)

# Safety Data Sheet

## acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/03/2015

Reviewed on 11/21/2014

**Trade name: 2-Cyclopenten-1-one**

(Contd. of page 2)

- Ensure adequate ventilation.
- Do not flush with water or aqueous cleansing agents
- **Reference to other sections**
- See Section 7 for information on safe handling.
- See Section 8 for information on personal protection equipment.
- See Section 13 for disposal information.

### 7 Handling and storage

- **Handling:**
- **Precautions for safe handling**
- Ensure good ventilation/exhaustion at the workplace.
- Prevent formation of aerosols.
- **Information about protection against explosions and fires:**
- Keep ignition sources away - Do not smoke.
- Protect against electrostatic charges.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Specific end use(s)** No further relevant information available.

### 8 Exposure controls/personal protection

- **Additional information about design of technical systems:**
- Properly operating chemical fume hood designed for hazardous chemicals and having an average face velocity of at least 100 feet per minute
- **Control parameters**
- **Components with limit values that require monitoring at the workplace:** Not required.
- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
- Keep away from foodstuffs, beverages and feed.
- Immediately remove all soiled and contaminated clothing.
- Wash hands before breaks and at the end of work.
- **Breathing equipment:**
- In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.
- **Protection of hands:**
- The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
- Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.
- Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**
- The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

(Contd. on page 4)

# Safety Data Sheet

*acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)*

Printing date 03/03/2015

Reviewed on 11/21/2014

Trade name: 2-Cyclopenten-1-one

(Contd. of page 3)

- **Penetration time of glove material**  
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Tightly sealed goggles

## 9 Physical and chemical properties

- **Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**
  - Form:** Liquid
  - Color:** Not determined.
- **Odor:** Characteristic
- **Odour threshold:** Not determined.
- **pH-value:** Not determined.
- **Change in condition**
  - Melting point/Melting range:** Undetermined
  - Boiling point/Boiling range:** 64-65 °C (147-149 °F) (19mm)
- **Flash point:** 42 °C (108 °F)
- **Flammability (solid, gaseous):** Not applicable.
- **Ignition temperature:**
- **Decomposition temperature:** Not determined.
- **Auto igniting:** Not determined.
- **Danger of explosion:** Product is not explosive. However, formation of explosive air/vapor mixtures are possible.
- **Explosion limits:**
  - Lower:** Not determined.
  - Upper:** Not determined.
- **Vapor pressure:** Not determined.
- **Density at 20 °C (68 °F):** 0.98 g/cm<sup>3</sup> (8.178 lbs/gal)
- **Relative density** Not determined.
- **Vapour density** Not determined.
- **Evaporation rate** Not determined.
- **Solubility in / Miscibility with Water:** Not miscible or difficult to mix.
- **Partition coefficient (n-octanol/water):** Not determined.
- **Viscosity:**
  - Dynamic:** Not determined.
  - Kinematic:** Not determined.
  - Organic solvents:** 0.0 %
- **Other information** No further relevant information available.

-USA-

(Contd. on page 5)

# Safety Data Sheet

## acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/03/2015

Reviewed on 11/21/2014

Trade name: 2-Cyclopenten-1-one

(Contd. of page 4)

### 10 Stability and reactivity

- **Reactivity**
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

### 11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)**

Substance is not listed.

- **NTP (National Toxicology Program)**

Substance is not listed.

- **OSHA-Ca (Occupational Safety & Health Administration)**

Substance is not listed.

### 12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:** Not known to be hazardous to water.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

### 13 Disposal considerations

- **Waste treatment methods**
  - **Recommendation:**
- Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

(Contd. on page 6)

# Safety Data Sheet

**acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)**

Printing date 03/03/2015

Reviewed on 11/21/2014

Trade name: 2-Cyclopenten-1-one

(Contd. of page 5)

- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

## 14 Transport information

· <b>UN-Number</b>	
· <b>DOT, IMDG, IATA</b>	UN1224
· <b>UN proper shipping name</b>	
· <b>DOT</b>	Ketones, liquid, n.o.s.
· <b>IMDG, IATA</b>	KETONES, LIQUID, N.O.S.
· <b>Transport hazard class(es)</b>	
· <b>DOT, IMDG, IATA</b>	
· <b>Class</b>	3 Flammable liquids
· <b>Packing group</b>	
· <b>DOT, IMDG, IATA</b>	III
· <b>Environmental hazards:</b>	
· <b>Marine pollutant:</b>	No
· <b>Special precautions for user</b>	Warning: Flammable liquids
· <b>Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code</b>	Not applicable.
· <b>UN "Model Regulation":</b>	UN1224, Ketones, liquid, n.o.s., 3, III

## 15 Regulatory information

· <b>Safety, health and environmental regulations/legislation specific for the substance or mixture</b>
· <b>Sara</b>
· <b>Section 355 (extremely hazardous substances):</b>
Substance is not listed.
· <b>Section 313 (Specific toxic chemical listings):</b>
Substance is not listed.
· <b>TSCA (Toxic Substances Control Act):</b>
Substance is not listed.
· <b>Proposition 65</b>
· <b>Chemicals known to cause cancer:</b>
Substance is not listed.
· <b>Chemicals known to cause reproductive toxicity for females:</b>
Substance is not listed.
· <b>Chemicals known to cause reproductive toxicity for males:</b>
Substance is not listed.
· <b>Chemicals known to cause developmental toxicity:</b>
Substance is not listed.

(Contd. on page 7)

# Safety Data Sheet

**acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)**

Printing date 03/03/2015

Reviewed on 11/21/2014

**Trade name: 2-Cyclopenten-1-one**

(Contd. of page 6)

**· Carcinogenic categories**
**· EPA (Environmental Protection Agency)**

Substance is not listed.

**· TLV (Threshold Limit Value established by ACGIH)**

Substance is not listed.

**· NIOSH-Ca (National Institute for Occupational Safety and Health)**

Substance is not listed.

**· RTECS**

Substance is not listed.

**· Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## 16 Other information

*This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.*

**· NFPA ratings (scale 0-4)**

Health = 1

Fire = 2

Reactivity = 0

**· HMIS ratings (scale 0-4)**

Health = 1

Fire = 2

Reactivity = 0

**· Department issuing SDS:** Technical Support Department

**· Contact:** Technical Support Department

**· Date of preparation / last revision** 03/03/2015 / -

**· Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

Flam. Liq. 3: Flammable liquids, Hazard Category 3

STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3