

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/24/2014

1 Identification

- **Product identifier**
- **Trade name:** Sodium cyanide
- **Article number:** 212960
- **CAS Number:**
143-33-9
- **EC number:**
205-599-4
- **Index number:**
006-007-00-5
- **Application of the substance / the mixture** Laboratory chemicals for research and development
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
BeanTown Chemical
9 Sagamore Park Road
Hudson, NH 03051
USA

Phone: (603) 402-2234
Fax: (603) 402-9713
Email: technical@beantownchem.com
www.beantownchem.com
- **Information department:** Technical Support Department
- **Emergency telephone number:**
During normal operating hours, please call (603) 402-2234
After hours, please call Chemtrec at (800) 424-9300

2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS06 Skull and crossbones

Acute Tox. 1 H300 Fatal if swallowed.

Acute Tox. 1 H310 Fatal in contact with skin.

Acute Tox. 1 H330 Fatal if inhaled.

- **Label elements**
- **GHS label elements** The substance is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS06

- **Signal word** Danger
- **Hazard-determining components of labeling:**
sodium cyanide
- **Hazard statements**
Fatal if swallowed, in contact with skin or if inhaled.

(Contd. on page 2)

USA

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/24/2014

Trade name: Sodium cyanide

(Contd. of page 1)

- **Precautionary statements**

If medical advice is needed, have product container or label at hand.

Keep out of reach of children.

Read label before use.

Do not breathe dust/fume/gas/mist/vapors/spray.

Wear respiratory protection.

If swallowed: Immediately call a poison center/doctor.

Specific treatment is urgent (see on this label).

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

- **Other hazards**

- **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.

- **vPvB:** Not applicable.

3 Composition/information on ingredients

- **Chemical characterization: Substances**

- **CAS No. Description**

143-33-9 sodium cyanide

- **Identification number(s)**

- **EC number:** 205-599-4

- **Index number:** 006-007-00-5

4 First-aid measures

- **Description of first aid measures**

- **General information:**

Immediately remove any clothing soiled by the product.

Remove breathing apparatus only after contaminated clothing have been completely removed.

In case of irregular breathing or respiratory arrest provide artificial respiration.

- **After inhalation:**

Supply fresh air or oxygen; call for doctor.

In case of unconsciousness place patient stably in side position for transportation.

- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.

- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.

- **After swallowing:** Do not induce vomiting; immediately call for medical help.

- **Information for doctor:**

- **Most important symptoms and effects, both acute and delayed** No further relevant information available.

- **Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**

- **Suitable extinguishing agents:**

CO₂, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

- **Special hazards arising from the substance or mixture** No further relevant information available.

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/24/2014

Trade name: Sodium cyanide

(Contd. of page 2)

- **Advice for firefighters**
- **Protective equipment:** Mouth respiratory protective device.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:**
Do not allow product to reach sewage system or any water course.
Inform respective authorities in case of seepage into water course or sewage system.
- **Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

7 Handling and storage

- **Handling:**
- **Precautions for safe handling**
Thorough dedusting.
Ensure good ventilation/exhaustion at the workplace.
Open and handle receptacle with care.
- **Information about protection against explosions and fires:** Keep respiratory protective device available.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:**
Properly operating chemical fume hood designed for hazardous chemicals and having an average face velocity of at least 100 feet per minute
- **Control parameters**

- **Components with limit values that require monitoring at the workplace:**

143-33-9 sodium cyanide

PEL	Long-term value: 5 mg/m ³ as CN; Skin
REL	Ceiling limit value: 5* mg/m ³ , 4.7* ppm as CN; *10-min
TLV	Ceiling limit value: 5 mg/m ³ , 4.7 ppm as CN; Skin

- **Additional information:** The lists that were valid during the creation were used as basis.

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/24/2014

Trade name: Sodium cyanide

(Contd. of page 3)

- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
 Keep away from foodstuffs, beverages and feed.
 Immediately remove all soiled and contaminated clothing.
 Wash hands before breaks and at the end of work.
 Store protective clothing separately.
 Avoid contact with the eyes and skin.
- **Breathing equipment:**
 In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.
- **Protection of hands:**
 Protective gloves
 The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
 Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.
 Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**
 The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.
- **Penetration time of glove material**
 The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Not required.

9 Physical and chemical properties

- **Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**

Form:	Crystalline
Color:	White
Odor:	Characteristic
Odour threshold:	Not determined.
- **pH-value:** Not applicable.
- **Change in condition**

Melting point/Melting range:	564 °C (1047 °F)
Boiling point/Boiling range:	1500 °C (2732 °F)
- **Flash point:** Not applicable.
- **Flammability (solid, gaseous):** Product is not flammable.
- **Ignition temperature:**
- **Decomposition temperature:** Not determined.
- **Auto igniting:** Not determined.
- **Danger of explosion:** Product does not present an explosion hazard.
- **Explosion limits:**

Lower:	Not determined.
Upper:	Not determined.

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/24/2014

Trade name: Sodium cyanide

(Contd. of page 4)

- | | |
|---------------------------------------------------|--------------------------------------------|
| · Vapor pressure at 817 °C (1503 °F): | 1 hPa (1 mm Hg) |
| · Density at 20 °C (68 °F): | 1.61 g/cm ³ (13.435 lbs/gal) |
| · Relative density | Not determined. |
| · Vapour density | Not applicable. |
| · Evaporation rate | Not applicable. |
| · Solubility in / Miscibility with Water: | Insoluble. |
| · Partition coefficient (n-octanol/water): | Not determined. |
| · Viscosity: | |
| · Dynamic: | Not applicable. |
| · Kinematic: | Not applicable. |
| · Organic solvents: | 0.0 % |
| · Solids content: | 100.0 % |
| · Other information | No further relevant information available. |

10 Stability and reactivity

- **Reactivity**
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

- **LD/LC50 values that are relevant for classification:**

143-33-9 sodium cyanide

Oral LD50 6440 mg/kg (rat)

- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:** Danger through skin absorption.

- **Carcinogenic categories**

- **IARC (International Agency for Research on Cancer)**

Substance is not listed.

- **NTP (National Toxicology Program)**

Substance is not listed.

(Contd. on page 6)

USA

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/24/2014

Trade name: Sodium cyanide

(Contd. of page 5)

· **OSHA-Ca (Occupational Safety & Health Administration)**

Substance is not listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** Very toxic for fish
- **Additional ecological information:**
- **General notes:**
Also poisonous for fish and plankton in water bodies.
Very toxic for aquatic organisms
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

- | | |
|---------------------------------------|---------------------------|
| · UN-Number | UN1689 |
| · DOT, IMDG, IATA | |
| · UN proper shipping name | Sodium cyanide, solid |
| · DOT | SODIUM CYANIDE, SOLID |
| · IMDG, IATA | |
| · Transport hazard class(es) | |
| · DOT, IMDG, IATA | 6.1 Toxic substances |
| · Class | |
| · Packing group | I |
| · DOT, IMDG, IATA | |
| · Environmental hazards: | |
| · Marine pollutant: | No |
| · Special precautions for user | Warning: Toxic substances |

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/24/2014

Trade name: Sodium cyanide

(Contd. of page 6)

- | | |
|-----------------------------------------------------------------------------------|------------------------------------------------------------------|
| · Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code | Not applicable. |
| · UN "Model Regulation": | UN1689, Sodium cyanide, solid, ENVIRONMENTALLY HAZARDOUS, 6.1, I |

15 Regulatory information

- Safety, health and environmental regulations/legislation specific for the substance or mixture
- Sara

· Section 355 (extremely hazardous substances):

Substance is listed.

· Section 313 (Specific toxic chemical listings):

Substance is listed.

· TSCA (Toxic Substances Control Act):

Substance is listed.

· Proposition 65

· Chemicals known to cause cancer:

Substance is not listed.

· Chemicals known to cause reproductive toxicity for females:

Substance is not listed.

· Chemicals known to cause reproductive toxicity for males:

Substance is listed.

· Chemicals known to cause developmental toxicity:

Substance is not listed.

· Carcinogenic categories

· EPA (Environmental Protection Agency)

143-33-9 sodium cyanide	II
-------------------------	----

· TLV (Threshold Limit Value established by ACGIH)

Substance is not listed.

· NIOSH-Ca (National Institute for Occupational Safety and Health)

Substance is not listed.

· RTECS

Substance is not listed.

· Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· NFPA ratings (scale 0-4)

Health = 4

Fire = 0

Reactivity = 0

(Contd. on page 8)

Safety Data Sheet
acc. to OSHA Hazard Communication Standard (29 CFR 1910.1200)

Printing date 03/04/2015

Reviewed on 11/24/2014

Trade name: Sodium cyanide

(Contd. of page 7)

· HMIS ratings (scale 0-4)

Health = 4

Fire = 0

Reactivity = 0

· Department issuing SDS: Technical Support Department**· Contact:** Technical Support Department**· Date of preparation / last revision** 03/04/2015 / -**· Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

Acute Tox. 1: Acute toxicity, Hazard Category 1

USA