## **BioVision**

## Interferon-y (IFN-y), human recombinant

CATALOG #:	4116-20 4116-100 4116-1000	20 µg 100 µg 1 mg
SOURCE:	E. coli	
PURITY:	>98% by SDS-PAGE and HPLC analysis Endotoxin level is <0.1 ng per μg of IFN-γ.	
MOL. WEIGHT:	16.9 kDa	
FORMULATION:	Lyophilized powder with no additive	


**RECONSTITUTION:** Centrifuge the vial prior to opening. Reconstitute in sterile water to a concentration of 0.1-1 mg/ml.

**STORAGE CONDITIONS:** The lyophilized IFN- $\gamma$  should be stored desiccated below 0°C. Reconstituted IFN- $\gamma$  should be stored at working aliquots at -20°C. For long term storage, it's recommend to add a carrier protein (0.1% HAS or BSA).

**DESCRIPTION**: IFN- $\gamma$  is a lymphoid factor that possesses potent anti-viral activity. Interferon-gamma (IFN- $\gamma$ /IFNG) is a dimerized soluble cytokine that is the only member of the type II class of interferon. This interferon was originally called macrophage-activating factor, a term now used to describe a larger family of proteins to which IFN- $\gamma$  belongs. IFN-gamma has been used in a wide variety of clinical indications. Interferon-gamma (IFN gamma) is a central regulator of the immune response and signals via the Janus Activated Kinase (JAK)-Signal Transducer and Activator of Transcription (STAT) pathway. Interferon gamma has broader roles in activation of innate and adaptive immune responses to viruses and tumors, in part through upregulating transcription of genes involved in cell cycle regulation, apoptosis, and antigen processing/presentation. Despite this, rodent and human trophoblast cells show dampened responses to IFNG that reflect the resistance of these cells to IFNG-mediated activation of major histocompatibility complex (MHC) class II transplantation antigen expression. Recombinant human IFN- $\gamma$  is a 16.9 kDa protein containing 144 amino acid residues.

## **BIOLOGICAL ACTIVITY:**

The ED<sub>50</sub> as determined in a viral resistance assay is  $\leq$  0.05 ng/ml, corresponding to a specific activity of  $\geq$  2 x 10<sup>7</sup> units/mg.



Lane 1 : Markers Lane 2: hr IFN-gamma (3.5 µg) Lane 3: hr IFN-gamma (7 µg) Lane 4: hr IFN-gamma (14 µg)

Human Recombinant IFN-gamma

## **RELATED PRODUCTS:**

- Human CellExp<sup>™</sup> Human Recombinant IFN-gamma (Cat # 7271-10)
- IFN-λ2, human recombinant (Cat # 7163-10, -50)
- Human CellExp<sup>™</sup> Human Recombinant IFN-alpha 2b (Cat # 6459-10, -50)
- IFN-alpha 2a, human recombinant (Cat # 4594-20, -100, -1000)
- IFN-alpha 2b, human recombinant (Cat # 4595-20, -100, -1000)
- IFN-alpha 1, human recombinant (Cat # 4596-10, -100, -1000)
- IFN-beta 1b, human recombinant (Cat # 4860-10, -50, -1000)
- IFN-gamma, human recombinant (Cat # 4116-20, -100, -1000)
- IFN-gamma, murine recombinant (Cat # 4117-20, -100, -1000)
- IFN-gamma, rat recombinant (Cat # 4118-50, -100, -1000)
- IFN-gamma Antibody (Cat # 5116-200)
- IFN-gamma Antibody (Cat # 5117-100)
- IFN-alpha Antibody (Cat # 5596-100)
- IFN-alpha Antibody (Cat # 5595R-100)
- IFN-alpha 2b Antibody (Cat # 5595-100)

FOR RESEARCH USE ONLY! Not to be used on humans.