

## Recombinant Murine Interleukin-5 (m-IL-5)

**CATALOG #:** 4141-10 10 µg  
4141-1000 1 mg

**LOT #:** \_\_\_\_\_

**SOURCE:** *E. coli*

**PURITY:** > 97 % by SDS-PAGE and RP-HPLC analysis  
Endotoxin level is < 0.01 ng per µg of rm- IL-5.

**MOL. WEIGHT:** 26.2 kDa

**FORM:** Lyophilized from 20 mM Sodium phosphate buffer, pH 7.5

### RECONSTITUTION:

It is recommended to reconstitute the lyophilized product with sterile water at a concentration of 0.1 mg/ml, which can be further diluted into other aqueous solutions.

### STORAGE CONDITIONS:

The lyophilized product is very stable at -20 °C. Upon reconstitution the material should be aliquoted and frozen at -20 °C. It is recommended to add a carrier protein (0.1% HSA or BSA) for long term storage.

### DESCRIPTION:

Mouse Interleukin-5 (mIL-5) is a glycoprotein also known as EDF and TRF. It is involved in B-cell growth and eosinophil activation. IL-5 has been shown to be expressed in Th2, mast cells and eosinophils and is regulated by GATA-3, in addition to other transcription factors. IL-5 signals its biological effect through interaction with the IL-5 receptor (IL-5R). Recombinant mIL-5 is produced in E.Coli, comprised of two 113 amino acid chains forming a disulfide-linked homodimer with a molecular weight of 26.2 kDa.

### BIOLOGICAL ACTIVITY:

Mouse IL-5 is fully biologically active as compared to standard. The ED<sub>50</sub>, as calculated by the dose-dependent induction of TF-1 cell proliferation, is 1.7ng/ml.

### AA SEQUENCE:

MEIPMSTVVK ETLTQLSAHR ALLTSNETMR LPVPTHKNHQ LCIGEIFQGL DILKNQTVRG  
GTVEMLFQNL SLIKKYIDRQ KEKCGEERRR TRQFLDYLQE FLGVMSTEWA MEG

**FOR RESEARCH USE ONLY! Not to be used in humans.**

### RELATED PRODUCTS:

#### Apoptosis Detection Kits & Reagents

- Annexin V Kits & Bulk Reagents
- Caspase Assay Kits & Reagents
- Mitochondrial Apoptosis Kits & Reagents
- Nuclear Apoptosis Kits & Reagents
- Apoptosis Inducers and Set
- Apoptosis siRNA Vectors

#### Cell Fractionation System

- Mitochondria/Cytosol Fractionation Kit
- Nuclear/Cytosol Fractionation Kit
- Membrane Protein Extraction Kit
- Cytosol/Particulate Rapid Separation Kit
- Mammalian Cell Extraction Kit
- FractionPREP Fractionation System

#### Cell Proliferation & Senescence

- Quick Cell Proliferation Assay Kit
- Senescence Detection Kit
- High Throughput Apoptosis/Cell Viability Assay Kits
- LDH-Cytotoxicity Assay Kit
- Bioluminescence Cytotoxicity Assay Kit
- Live/Dead Cell Staining Kit

#### Cell Damage & Repair

- HDAC Fluorometric & Colorimetric Assays & Drug Discovery Kits
- HAT Colorimetric Assay Kit & Reagents
- DNA Damage Quantification Kit
- Glutathione & Nitric Oxide Fluorometric & Colorimetric Assay Kits

#### Signal Transduction

- cAMP & cGMP Assay Kits
- Akt & JNK Activity Assay Kits
- Beta-Secretase Activity Assay Kit

#### Adipocyte & Lipid Transfer

- Recombinant Adiponectin, Survivin, & Leptin
- CETP Activity Assay & Drug Discovery Kits
- PLTP Activity Assay & Drug Discovery Kits
- Total Cholesterol Quantification Kit

#### Molecular Biology & Reporter Assays

- siRNA Vectors
- Cloning Insert Quick Screening Kit
- Mitochondrial & Genomic DNA Isolation Kits
- 5 Minutes DNA Ligation Kit
- 20 Minutes Gel Staining/Destaining Kit
- β -Galactosidase Staining Kit & Luciferase Reporter Assay Kit

#### Growth Factors and Cytokines

#### Monoclonal and Polyclonal Antibodies