

Datasheet

BIVM polyclonal antibody

Catalog Number: PAB9949

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against synthetic peptide of BIVM.

Immunogen: A synthetic peptide (conjugated with KLH) corresponding to C-terminus of human BIVM.

Host: Rabbit

Reactivity: Human

Applications: ELISA, WB-Ce

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Recommend Usage: ELISA (1:5000-1:25000)

Western Blot (1:1000)

The optimal working dilution should be determined by the end user.

Storage Buffer: In 20 mM KH_2PO_4 , 150 mM NaCl, pH 7.2 (0.01% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 54841

Gene Symbol: BIVM

Gene Alias: MGC133326

References:

1. BIVM, a novel gene widely distributed among deuterostomes, shares a core sequence with an unusual gene in *Giardia lamblia*. Yoder JA, Hawke NA, Eason DD, Mueller MG, Davids BJ, Gillin FD, Litman GW. Genomics. 2002 Jun;79(6):750-5.