

Rabbit Monoclonal Antibody to Human Calcitonin

Catalog No.:	RMAB 009
Intended Use:	This product is intended for qualitative immunohistochemistry with normal and neoplastic formalin-fixed, paraffin-embedded tissue sections, to be viewed by light microscopy. Clinical interpretation of staining results should be accompanied by histological studies with proper controls. Patients' clinical histories and other relevant diagnostic tests should be utilized by a qualified person(s) when evaluating and interpreting results.
Clone:	SP17
Immunogen:	Synthetic human calcitonin 1-32 amino acid peptide.
Isotype:	IgG
Format:	This antibody is supplied as tissue culture supernatant containing sodium azide as a preservative.
Titer/Working Dilution:	This antibody may be diluted to a titer of 1:100 in an ABC method. The final dilution should be determined by the user based upon the staining conditions employed.
Staining Protocol:	We suggest an incubation period of 30 minutes at room temperature. Optimal incubation conditions should be determined by the user based upon the fixation conditions and staining system employed. <u>Formalin fixed paraffin embedded tissue sections require high temperature antigen unmasking with 10mM citrate buffer, pH 6.0 prior to immunostaining.</u>
Specificity:	This antibody recognizes Calcitonin, a 32 amino acid peptide, which can be demonstrated in C cells of the normal and hyperplastic thyroid. Staining for calcitonin may be used for the identification of a spectrum of C cell proliferative abnormalities ranging from C cell hyperplasia to invasive tumors. Staining for calcitonin in medullary carcinoma of the thyroid produces a fine granular pattern in the cytoplasm. Amyloid deposits within the tumor may also exhibit varying degrees of calcitonin activity. This antibody crossreacts with Human, Monkey, Mouse, Rat, Dog, Horse, Sheep, and Pig.
Positive Control:	Thyroid or Medullary carcinoma
Cellular Localization:	Cytoplasmic
Storage:	Store at 2-8°C. Do not use beyond the expiration date stated on the label.

IVD: For In Vitro Diagnostic Use

DBS will not be held responsible for patent infringement or other violation that may occur with the use of our product

DBS

1020 Serpentine Lane, # 114, Pleasanton, CA 94566 Tel: 925 484 3350, Fax: 925 484 3390

Website: www.dbiosys.com e-mail: customersupport@dbiosys.com