



SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 06/25/2014

Version 1.2

SECTION 1. Identification

Product identifier

Product number	100583
Product name	Tungstophosphoric acid hydrate for analysis EMSURE®
CAS-No.	12501-23-4

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis
-----------------	----------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Skin corrosion, Category 1B, H314

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

Hazard Statements

H314 Causes severe skin burns and eye damage.

Precautionary Statements

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 100583
Product name Tungstophosphoric acid hydrate for analysis EMSURE®

Version 1.2

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P308 + P310 IF exposed or concerned: immediately call a POISON CENTER or doctor/ physician.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200). This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS and may deviate from the GHS information.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	$H_3[P(W_3O_{10})_4] \cdot x H_2O$	$H_3O_{40}PW_{12} \cdot x H_2O$ (Hill)
Molar mass	2,880.17 g/mol (anhydrous)	

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

Phosphotungstic acid hydrate ($\geq 90\%$ - $\leq 100\%$)

12501-23-4

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

General advice

First aider needs to protect himself.

Inhalation

After inhalation: fresh air. Call in physician.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing. Call a physician immediately.

Eye contact

After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

Ingestion

After swallowing: make victim drink water (two glasses at most), avoid vomiting (risk of perforation!). Call a physician immediately. Do not attempt to neutralize.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Irritation and corrosion, Cough, Shortness of breath

Risk of blindness!

Indication of any immediate medical attention and special treatment needed

No information available.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

100583

Version 1.2

Product name

Tungstophosphoric acid hydrate for analysis EMSURE®

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Not combustible.

Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:

Oxides of phosphorus

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Avoid inhalation of dusts.

Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry.

Store at +15°C to +25°C (+59°F to +77°F).

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

100583

Version 1.2

Product name

Tungstophosphoric acid hydrate for analysis EMSURE®

SECTION 8. Exposure controls/personal protection**Exposure limit(s)***Ingredients*

Basis	Value	Threshold limits	Remarks
<i>Phosphotungstic acid hydrate 12501-23-4</i>			
ACGIH	Time Weighted Average (TWA):	1 mg/m ³	Expressed as: as W
	Time Weighted Average (TWA):	5 mg/m ³	Expressed as: as W
	Short Term Exposure Limit (STEL):	3 mg/m ³	Expressed as: as W
	Short Term Exposure Limit (STEL):	10 mg/m ³	Expressed as: as W
	Limit (STEL):		
NIOSH/GUIDE	Recommended exposure limit (REL):	5 mg/m ³	Expressed as: as W
	Short Term Exposure Limit (STEL):	3 mg/m ³	Expressed as: as W
	Short Term Exposure Limit (STEL):	10 mg/m ³	Expressed as: as W
	Limit (STEL):		
	Recommended exposure limit (REL):	1 mg/m ³	Expressed as: as W
Z1A	Time Weighted Average (TWA):	1 mg/m ³	Expressed as: as W
	Time Weighted Average (TWA):	5 mg/m ³	Expressed as: as W
	Short Term Exposure Limit (STEL):	3 mg/m ³	Expressed as: as W
	Short Term Exposure Limit (STEL):	10 mg/m ³	Expressed as: as W
	Limit (STEL):		

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Tightly fitting safety goggles

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

Acid-resistant protective clothing.

Respiratory protection

required when dusts are generated.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

100583

Version 1.2

Product name

Tungstophosphoric acid hydrate for analysis EMSURE®

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	solid
Color	light green
Odor	odorless
Odor Threshold	not applicable
pH	ca. 1.3 at 20 g/l 68 °F (20 °C)
Melting point	107 °C
Boiling point/boiling range	not applicable
Flash point	No information available.
Evaporation rate	No information available.
Flammability (solid, gas)	The product is not flammable.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Density	No information available.
Relative density	No information available.
Water solubility	at 68 °F (20 °C) soluble
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	> 225 °F (> 107 °C)
Viscosity, dynamic	No information available.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	100583	Version 1.2
Product name	Tungstophosphoric acid hydrate for analysis EMSURE®	

Explosive properties	Not classified as explosive.
----------------------	------------------------------

Oxidizing properties	none
----------------------	------

Bulk density	ca. 960 kg/m ³
--------------	---------------------------

SECTION 10. Stability and reactivity

Reactivity

See below

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Exothermic reaction with:

Strong bases

Conditions to avoid

Temperatures above melting point.

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact, Ingestion

Acute oral toxicity

LD50 rat: 3,300 mg/kg (anhydrous substance) (RTECS)

Symptoms: Ingestion causes burns of the upper digestive and respiratory tracts.

Acute inhalation toxicity

Symptoms: Cough, Shortness of breath, mucosal irritations, Possible damages:; damage of respiratory tract

Skin irritation

Causes burns.

Eye irritation

Causes serious eye damage.

Risk of blindness!

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 100583
Product name Tungstophosphoric acid hydrate for analysis EMSURE®

Version 1.2

Sensitization

In animal experiments:

Result: negative

Method: OECD Test Guideline 429

Genotoxicity in vitro

Ames test

Result: negative

Method: OECD Test Guideline 471

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to daphnia and other aquatic invertebrates

EC50 Daphnia magna (Water flea): > 100 mg/l; 48 h

OECD Test Guideline 202 (own results)

Persistence and degradability

Biodegradability

The methods for determining the biological degradability are not applicable to inorganic substances.

SAFETY DATA SHEET
according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 100583
Product name Tungstophosphoric acid hydrate for analysis EMSURE®

Version 1.2

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Additional ecological information

Harmful effect due to pH shift.

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 3260
Proper shipping name	CORROSIVE SOLID, ACIDIC, INORGANIC, N.O.S. (TUNGSTOPHOSPHORIC ACID)
Class	8
Packing group	III
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 3260
Proper shipping name	CORROSIVE SOLID, ACIDIC, INORGANIC, N.O.S. (TUNGSTOPHOSPHORIC ACID)
Class	8
Packing group	III
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

UN number	UN 3260
Proper shipping name	CORROSIVE SOLID, ACIDIC, INORGANIC, N.O.S. (TUNGSTOPHOSPHORIC ACID)
Class	8
Packing group	III
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-A S-B

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

100583

Version 1.2

Product name

Tungstophosphoric acid hydrate for analysis EMSURE®

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Corrosive to skin

Corrosive to eyes

Corrosive by inhalation.

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Acute Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Ingredients

Phosphotungstic acid hydrate

New Jersey Right To Know

Ingredients

Phosphotungstic acid hydrate

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 100583
Product name Tungstophosphoric acid hydrate for analysis EMSURE®

Version 1.2

Notification status

TSCA: All components of the product are listed in the TSCA-inventory.

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H314 Causes severe skin burns and eye damage.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 06/25/2014

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.