MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 12/20/2012 Version 1.0

SECTION 1. Identification

Product identifier

Product number	102333
Product name	Chlorotrimethylsilane for gas chromatography

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821, United States of America | SDS Phone Support: +1-978-715-1335 | General Inquiries: +1-978-751-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 2, H225
Specific target organ systemic toxicity - single exposure, Category 3, Respiratory system, H335
Skin corrosion, Category 1A, H314

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

Hazard Statements
H225 Highly flammable liquid and vapor.
H314 Causes severe skin burns and eye damage.
H335 May cause respiratory irritation.

Precautionary Statements
P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P233 Keep container tightly closed.
P240 Ground/bond container and receiving equipment.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P301 + P330 + P331 IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P309 + P310 IF exposed or if you feel unwell: Immediately call a POISON CENTER or doctor/physician.
P403 + P235 Store in a well-ventilated place. Keep cool.

OSHA Hazards
This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards
None known.

SECTION 3. Composition/information on ingredients

Formula	$(CH_3)_3SiCl$	C_3H_9ClSi (Hill)
CAS-No.	75-77-4	
Molar mass	108.64 g/mol	

Hazardous ingredients
Chemical Name (Concentration)
CAS-No.

chlorotrimethylsilane (>= 90 % - <= 100 %)
75-77-4

SECTION 4. First aid measures

Description of first-aid measures

General advice
First aider needs to protect himself.

Inhalation
After inhalation: fresh air. Call in physician.

Skin contact
After skin contact: wash off with plenty of water. Immediately remove contaminated clothing. If available swab with polyethylene glycol 400. Call a physician immediately.

Eye contact
After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

Ingestion
After swallowing: make victim drink water (two glasses at most), avoid vomiting (risk of perforation!). Do not attempt to neutralize. Pulmonary failure possible after aspiration of vomit. Call a physician immediately.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed
Irritation and corrosion, Cough, Shortness of breath, Risk of blindness!

Indication of any immediate medical attention and special treatment needed
No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media
Carbon dioxide (CO2), Dry powder

Unsuitable extinguishing media
Water, Foam

Special hazards arising from the substance or mixture
Combustible.
Vapors are heavier than air and may spread along floors.
Forms explosive mixtures with air at ambient temperatures.
Pay attention to flashback.
Development of hazardous combustion gases or vapors possible in the event of fire.
Fire may cause evolution of:
Hydrogen chloride gas, silanes
Caution! in contact with water product releases:
Hydrogen chloride gas

Advice for firefighters

Special protective equipment for fire-fighters
Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information
Cool closed containers exposed to fire with water spray. Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures
Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Ensure adequate ventilation. Keep away from heat and sources of ignition. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions
Do not empty into drains. Risk of explosion.

Methods and materials for containment and cleaning up
Cover drains. Collect, bind, and pump off spills.
Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Keep workplace dry. Do not allow product to come into contact with water.

Advice on protection against fire and explosion

Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

Conditions for safe storage, including any incompatibilities

Keep away from heat and sources of ignition. Keep container tightly closed in a dry and well-ventilated place.

Storage temperature: no restrictions.

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Tightly fitting safety goggles

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid

Color	colorless
Odor	characteristic
Odor Threshold	No information available.
pH	No information available.
Melting point	-72 °F (-58 °C)
Boiling point/boiling range	135 °F (57 °C) at 1,013 hPa
Flash point	-4 °F (-20 °C) Method: c.c.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	1.5 %(V)
Upper explosion limit	46 %(V)
Vapor pressure	250 hPa at 68 °F (20 °C)
Relative vapor density	3.8
Relative density	0.86 g/cm³ at 68 °F (20 °C)
Water solubility	at 68 °F (20 °C) (rigorous decomposition)
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	0.4 mPa.s at 68 °F (20 °C)
Explosive properties	Not classified as explosive.
Ignition temperature	788 °F (420 °C) Method: DIN 51794

SECTION 10. Stability and reactivity

Reactivity
Vapors may form explosive mixture with air.

Chemical stability
Sensitive to air.

Possibility of hazardous reactions
Violent reactions possible with:

Generates dangerous gases or fumes in contact with:

Water, Alcohols, Acetone, Esters, Ketones, Aldehydes, Strong acids, Bases, Amines

Conditions to avoid
Warming.
A range from approx. 15 Kelvin below the flash point is to be rated as critical.
Exposure to moisture.

Incompatible materials
no information available

Hazardous decomposition products
in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure
Inhalation, Eye contact, Skin contact

Acute oral toxicity
LD50 rat: 4,868 mg/kg (RTECS)
Symptoms: If ingested, severe burns of the mouth and throat, as well as a danger of perforation of the esophagus and the stomach., Risk of aspiration upon vomiting., Aspiration may cause pulmonary edema and pneumonitis.

Acute inhalation toxicity
LC50 rat: 12.9 mg/l; 1 h
OECD Test Guideline 403
Symptoms: mucosal irritations, Cough, Shortness of breath, Inhalation may lead to the formation of oedemas in the respiratory tract., Possible damages:, damage of respiratory tract

Irritating to respiratory system.

Acute dermal toxicity
LD50 rabbit: 1,530 mg/kg
(RTECS)

Skin irritation
rabbit
Result: Causes burns.
(IUCLID)

Causes severe burns.

Eye irritation
rabbit
Result: Causes burns.
(IUCLID)

Causes serious eye damage.
Risk of blindness!

Genotoxicity in vivo
Mutagenicity (mammal cell test):
Result: negative
(IUCLID)

Genotoxicity in vitro
Ames test
Result: negative
Method: OECD Test Guideline 471

Specific target organ systemic toxicity - single exposure
May cause respiratory irritation.

Specific target organ systemic toxicity - repeated exposure
The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard
Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information
Decomposition of the substance with tissue moisture.
Other dangerous properties can not be excluded.
Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish
LC0 Danio rerio (zebra fish): >= 1,000 mg/l; 96 h (External MSDS)

Toxicity to bacteria
EC50 activated sludge: > 10,000 mg/l (External MSDS)

Persistence and degradability
No information available.

Bioaccumulative potential
No information available.

Mobility in soil
No information available.

Other adverse effects
Additional ecological information
Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 1298
Proper shipping name	TRIMETHYLCHLOROSILANE
Class	3 (8)
Packing group	II
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 1298
Proper shipping name	TRIMETHYLCHLOROSILANE
Class	3 (8)
Packing group	II
Environmentally hazardous	--
Special precautions for user	yes
IATA (Passenger)	**Not permitted for transport**

Sea transport (IMDG)

UN number	UN 1298
Proper shipping name	TRIMETHYLCHLOROSILANE
Class	3 (8)
Packing group	II
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-E S-C

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Flammable Liquid
Harmful by skin absorption.
Corrosive to skin
Corrosive to eyes
Respiratory irritant

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Fire Hazard
Acute Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

US State Regulations

Massachusetts Right To Know

Ingredients
chlorotrimethylsilane

Pennsylvania Right To Know

Ingredients
chlorotrimethylsilane

New Jersey Right To Know

Ingredients
chlorotrimethylsilane

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA:	On TSCA Inventory
DSL:	All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H225	Highly flammable liquid and vapor.
H314	Causes severe skin burns and eye damage.
H335	May cause respiratory irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet
Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Date of issue:12/20/2012

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.
All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.