SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 12/21/2015 Version 1.5

SECTION 1.Identification

Product identifier

Product number	108159
Product name	Holmium perchlorate standard solution for the calibration of spectrophotometers

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Use restricted under TSCA to research and development or as analytical reagent. Uses regulated under FDA or FIFRA are not affected. Reagent for analysis

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821, United States of America | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Oxidizing liquid, Category 2, H272
Skin irritation, Category 2, H315
Eye irritation, Category 2A, H319

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

Hazard Statements
H272 May intensify fire; oxidizer.

H315 Causes skin irritation.
H319 Causes serious eye irritation.

Precautionary Statements
P210 Keep away from heat.
P220 Keep/Store away from clothing/ combustible materials.
P221 Take any precaution to avoid mixing with combustibles.
P264 Wash skin thoroughly after handling.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P321 Specific treatment (see supplemental first aid instructions on this label).
P332 + P313 If skin irritation occurs: Get medical advice/ attention.
P337 + P313 If eye irritation persists: Get medical advice/ attention.
P362 Take off contaminated clothing and wash before reuse.
P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.
P501 Dispose of contents/ container to an approved waste disposal plant.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Chemical nature Strong acid aqueous solution.

Hazardous ingredients

Chemical Name (Concentration)
CAS-No.
Holmium(3+) perchlorate (>= 10 % - < 30 %)
14017-54-0

Exact percentages are being withheld as a trade secret.
Perchloric acid (>= 5 % - < 10 %)
7601-90-3

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation
After inhalation: fresh air.

Skin contact
In case of skin contact: Take off immediately all contaminated clothing. Rinse skin with water/ shower.

Eye contact
After eye contact: rinse out with plenty of water. Call in ophthalmologist.

Ingestion
After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed
irritant effects

Indication of any immediate medical attention and special treatment needed
No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media
Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media
For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture
Not combustible.
Ambient fire may liberate hazardous vapors.
Fire may cause evolution of:
Hydrogen chloride gas

Advice for firefighters

Special protective equipment for fire-fighters
Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information
Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures
Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders:

Protective equipment see section 8.

Environmental precautions
Do not let product enter drains.

Methods and materials for containment and cleaning up
Cover drains. Collect, bind, and pump off spills. Observe possible material restrictions (see sections 7 and 10).
Take up with liquid-absorbent and neutralizing material (e.g. Chemizorb® H^+, Art. No. 101595).
Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Do not store near combustible materials.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when vapors/aerosols are generated.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	light pink
Odor	odorless
Odor Threshold	Not applicable

pH	ca. 0 at 20 °C (20 °C)
Melting point	No information available.
Boiling point	No information available.
Flash point	No information available.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Density	1.136 g/cm3 at 20 °C (20 °C)
Relative density	No information available.
Water solubility	at 20 °C (20 °C) soluble
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.
Oxidizing properties	The substance or mixture is classified as oxidizing with the category 2.

SECTION 10. Stability and reactivity

Reactivity

See below

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

no information available

Conditions to avoid
no information available

Incompatible materials
Metals

Hazardous decomposition products
in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure
Eye contact, Skin contact

Acute oral toxicity
Symptoms: Irritations of mucous membranes in the mouth, pharynx, oesophagus and gastrointestinal tract.

Acute inhalation toxicity

Symptoms: Possible damages:, mucosal irritations

Skin irritation

Mixture causes skin irritation.

Eye irritation

Mixture causes serious eye irritation.

Specific target organ systemic toxicity - single exposure
The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure
The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard
Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Quantitative data on the toxicity of this product are not available.
Further data:
Other dangerous properties can not be excluded.
Handle in accordance with good industrial hygiene and safety practice.

Ingredients

Holmium(3+) perchlorate
No information available.

Perchloric acid
No information available.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Additional ecological information
Biological effects:
Harmful effect due to pH shift.
Further information on ecology
Discharge into the environment must be avoided.

Ingredients

Holmium(3+) perchlorate
No information available.

Perchloric acid
No information available.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 1802
Proper shipping name	PERCHLORIC ACID
Class	8 (5.1)
Packing group	II
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 1802
Proper shipping name	PERCHLORIC ACID
Class	8 (5.1)
Packing group	II
Environmentally hazardous	--
Special precautions for user	yes
IATA (Passenger)	**Not permitted for transport**

Sea transport (IMDG)

UN number	UN 1802
Proper shipping name	PERCHLORIC ACID
Class	8 (5.1)
Packing group	II
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-H S-Q

SECTION 15. Regulatory information

United States of America

SARA 313

This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

This product does not contain any toxic pollutants listed under the U.S. Clean Water Act Section 307

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Ingredients

Perchloric acid

Pennsylvania Right To Know

Ingredients

Perchloric acid

New Jersey Right To Know

Ingredients

Perchloric acid

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA:	Not Listed on TSCA inventory. For Research and Development Use only. Not For Manufacturing or Commercial Purposes.
DSL:	This product contains one or several components that are not on the Canadian DSL nor NDSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Labeling

Hazard pictograms



Signal Word
Danger

Hazard Statements
H272 May intensify fire; oxidizer.
H315 Causes skin irritation.
H319 Causes serious eye irritation.

Precautionary Statements
Prevention
P221 Take any precaution to avoid mixing with combustibles, heavy-metal compounds, acids and alkalis.
Response
P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P313 Get medical advice/ attention.

Full text of H-Statements referred to under sections 2 and 3.

H272	May intensify fire; oxidizer.
H315	Causes skin irritation.
H319	Causes serious eye irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet
Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date12/21/2015

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.