

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 04/04/2014 Version 1. 0

SECTION 1.Identification

Product identifier

Product number DX2091

Product name p-Dioxane For HPLC, Spectrophotometry
 spr/>and Gas

Chromatography OmniSolv®

CAS-No. 123-91-1

Relevant identified uses of the substance or mixture and uses advised against

Identified uses Reagent for analysis

Details of the supplier of the safety data sheet

Company EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821,

United States of America | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)

Emergency telephone 800-424-9300 CHEMTREC (USA)

+1-703-527-3887 CHEMTREC (International)

24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 2, H225 Eye irritation, Category 2, H319

Carcinogenicity, Category 2, H351

Specific target organ systemic toxicity - single exposure, Category 3, Respiratory system, H335

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms







Signal Word
Danger

Hazard Statements

H225 Highly flammable liquid and vapor.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX2091 Version 1.0

Product name p-Dioxane For HPLC, Spectrophotometry
 spr/>and Gas Chromatography

OmniSolv®

H319 Causes serious eve irritation.

H335 May cause respiratory irritation.

H351 Suspected of causing cancer.

Precautionary Statements

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P281 Use personal protective equipment as required.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact

lenses, if present and easy to do. Continue rinsing.

P308 + P313 IF exposed or concerned: Get medical advice/ attention.

P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200). This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS and may deviate from the GHS information.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula $C_4H_8O_2$ (Hill) Molar mass 88.11 g/mol

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

1,4-Dioxane (>= 90 % - <= 100 %)

123-91-1

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air. Consult a physician.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing. Consult a

physician.

Eye contact

After eye contact: rinse out with plenty of water. Call in ophthalmologist.

Ingestion

After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX2091 Version 1.0

Product name p-Dioxane For HPLC, Spectrophotometry

sand Gas Chromatography

OmniSolv®

irritant effects, Cough, Shortness of breath, Dizziness, Nausea, Vomiting, Headache Drying-out effect resulting in rough and chapped skin.

Indication of any immediate medical attention and special treatment needed

Laxative: Sodium sulfate (1 tablespoon/1/4 I water).

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Water, Carbon dioxide (CO2), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air at ambient temperatures.

Pay attention to flashback.

Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Cool closed containers exposed to fire with water spray. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains. Risk of explosion.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Work under hood. Do not inhale substance/mixture. Avoid generation of vapors/aerosols.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX2091 Version 1.0

Product name p-Dioxane For HPLC, Spectrophotometry
 spr/>and Gas Chromatography

OmniSolv®

Observe label precautions.

Advice on protection against fire and explosion

Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

Conditions for safe storage, including any incompatibilities

Keep away from heat and sources of ignition. Keep container tightly closed in a dry and well-ventilated place.

No declaration

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Ingredients

Basis Value Threshold Remarks

limits

1,4-Dioxane 123-91-1

ACGIH Time Weighted Average

(TWA):

Skin designation:

NIOSH/GUIDE Ceiling Limit Value and

Time Period (if

1 ppm 3.6 mg/m³

20 ppm

specified):

OSHA_TRANS PEL:

100 ppm

360 mg/m³

Skin designation: Can be absorbed through the skin.

Z1A Time Weighted Average

(TWA):

25 ppm 90 mg/m³

Skin designation (Final

90 mg/m

Rule Limit applies):

Can be absorbed through the skin.

Can be absorbed through the skin.

Ceiling Limit Value 30-min

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection Safety glasses

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX2091 Version 1.0

Product name p-Dioxane For HPLC, Spectrophotometry

sand Gas Chromatography

OmniSolv®

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

Flame retardant antistatic protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state liquid

Color colorless

Odor ether-like

Odor Threshold No information available.

pH 6-8

at 500 g/l 68 °F (20 °C)

Melting point 12 °C

Boiling point/boiling range 214.7 °F (101.5 °C)

at 1,013 hPa

Flash point 52 °F (11 °C)

Method: c.c.

Evaporation rate No information available.

Flammability (solid, gas) No information available.

Lower explosion limit 1.7 %(V)

Upper explosion limit 25.2 %(V)

Vapor pressure 41 hPa

at 68 °F (20 °C)

Relative vapor density 3.03

Density 1.03 g/cm³

at 68 °F (20 °C)

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX2091 Version 1.0

Product name p-Dioxane For HPLC, Spectrophotometry
 and Gas Chromatography

OmniSolv®

Relative density No information available.

Water solubility at 68 °F (20 °C)

soluble

Partition coefficient: n-

octanol/water

log Pow: -0.27 (experimental)

(Lit.) Bioaccumulation is not expected.

Autoignition temperature No information available.

Decomposition temperature No information available.

Viscosity, dynamic 1.32 mPa.s

at 68 °F (20 °C)

Explosive properties Not classified as explosive.

Oxidizing properties none

Ignition temperature 572 °F (300 °C)

Method: DIN 51794

SECTION 10. Stability and reactivity

Reactivity

Vapors may form explosive mixture with air.

Formation of peroxides possible.

Chemical stability

Sensitive to air.

Possibility of hazardous reactions

Risk of ignition or formation of inflammable gases or vapors with:

fire-promoting substances

Raney-nickel, with, Hydrogen

Exothermic reaction with:

Oxidizing agents, Sulfur trioxide, acids

Risk of explosion with:

triethylaluminum, perchlorates, lithium aluminum hydride, Triethylamine

Nitric acid, with, perchloric acid

Conditions to avoid

Distillation (Risk of explosion).

Warming.

Incompatible materials

various plastics, copper compounds

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX2091 Version 1.0

Product name p-Dioxane For HPLC, Spectrophotometry
 and Gas Chromatography

OmniSolv®

Hazardous decomposition products

Peroxides

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Inhalation, Eye contact, Skin contact

Target Organs

Eyes Skin

Respiratory system

Liver Kidneys

Acute oral toxicity
LD50 rat: 5,200 mg/kg
OECD Test Guideline 401

Acute inhalation toxicity LC50 rat: 48.5 - 54.3 mg/l; 4 h OECD Test Guideline 403

Symptoms: mucosal irritations, Cough, Shortness of breath, Possible damages:, damage of respiratory tract

Irritating to respiratory system.

Acute dermal toxicity LD50 rabbit: 7,600 mg/kg

(IUCLID)

absorption

Skin irritation

rabbit

Result: No irritation

(IUCLID)

Repeated exposure may cause skin dryness or cracking.

Eye irritation

rabbit

Result: Eye irritation

(IUCLID)

Causes serious eye irritation.

Sensitization

Sensitization test: guinea pig

Result: negative

(IUCLID)

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX2091 Version 1.0

Product name p-Dioxane For HPLC, Spectrophotometry

sand Gas Chromatography

OmniSolv®

Genotoxicity in vitro

Ames test Result: negative (IUCLID)

Mutagenicity (mammal cell test):

Result: negative

Method: OECD Test Guideline 476

CMR effects
Carcinogenicity:

Suspected of causing cancer.

Specific target organ systemic toxicity - single exposure

May cause respiratory irritation.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC Group 2B: Possibly carcinogenic to humans

1,4-Dioxane 123-91-1

OSHA No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

NTP Anticipated carcinogen.

1,4-Dioxane 123-91-1

ACGIH Confirmed animal carcinogen with unknown relevance to

humans.

1,4-Dioxane 123-91-1

Further information

The substance has delayed effects.

Systemic effects: After absorption:

Headache, Dizziness, Nausea, Vomiting Absorption can result in damage to:

Liver, Kidney

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish

LC50 Pimephales promelas (fathead minnow): 9,850 mg/l; 96 h (ECOTOX Database)

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX2091 Version 1.0

Product name p-Dioxane For HPLC, Spectrophotometry
 spr/>and Gas Chromatography

OmniSolv®

Toxicity to daphnia and other aquatic invertebrates

EC50 Daphnia: 8,450 mg/l; 24 h (IUCLID)

EC5 E.sulcatum: 5,340 mg/l; 72 h (IUCLID) (maximum permissible toxic concentration)

Toxicity to algae

IC5 Scenedesmus quadricauda (Green algae): 5,600 mg/l; 8 d (IUCLID) (maximum permissible

toxic concentration)

Toxicity to bacteria

EC50 Pseudomonas putida: 2,700 mg/l; 16 h

OECD Test Guideline 209

Persistence and degradability

Biodegradability < 5 %; 28 d

OECD Test Guideline 301E

Not readily biodegradable.

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: -0.27 (experimental)

(Lit.) Bioaccumulation is not expected.

Mobility in soil

No information available.

Additional ecological information

Forms toxic mixtures in water, dilution measures notwithstanding.

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN 1165
Proper shipping name DIOXANE

Class 3
Packing group II
Environmentally hazardous ---

Air transport (IATA)

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX2091 Version 1.0

Product name p-Dioxane For HPLC, Spectrophotometry
 and Gas Chromatography

OmniSolv®

UN 1165 Proper shipping nameDIOXANE

Class 3
Packing group II
Environmentally hazardous -Special precautions for user no

Sea transport (IMDG)

UN 1165 Proper shipping nameUN 1165
DIOXANE

Class 3
Packing group II
Environmentally hazardous -Special precautions for user
EmS yes
F-E S-D

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Flammable Liquid

Eye irritant

Respiratory irritant

Carcinogen

Target organ effects

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Fire Hazard

Acute Health Hazard

Chronic Health Hazard

SARA 313

The following components are subject to reporting levels established by SARA Title III, Section 313:

Ingredients

1,4-Dioxane 123-91-1 100 %

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX2091 Version 1.0

Product name p-Dioxane For HPLC, Spectrophotometry

sand Gas Chromatography

OmniSolv®

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311,

Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311,

Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Ingredients 1,4-Dioxane

Pennsylvania Right To Know

Ingredients 1,4-Dioxane

New Jersey Right To Know

Ingredients 1,4-Dioxane

California Prop 65 Components

WARNING: this product contains a chemical known in the State of California to cause cancer.

Ingredients 1,4-Dioxane

Notification status

TSCA: All components of the product are listed in the TSCA-inventory.

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H225 Highly flammable liquid and vapor.
 H319 Causes serious eye irritation.
 H335 May cause respiratory irritation.
 H351 Suspected of causing cancer.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number DX2091 Version 1.0

Product name p-Dioxane For HPLC, Spectrophotometry
 and Gas Chromatography

OmniSolv®

Date of issue: 04/04/2014

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.