

SAFETY DATA SHEET

Creation Date 22-Feb-2010 Revision Date 30-Mar-2015 Revision Number 1

1. Identification

Product Name Protocol™ 10% Neutral Buffered Formalin

Cat No.: 2300527, 2300528, 2300530, 2300532, 2300545, 2300546, 23005500,

23011120, 23032060, 23245684, 23245685, 23253998, 23305510,

23316154,23316155, 23426796, 23426797, 23427098

Synonyms No information available

Recommended Use In vitro diagnostic.

Uses advised against No Information available

Details of the supplier of the safety data sheet

Company
Fisher Diagnostics
A Division of Fisher Scientific Company, LLC
A Part of Thermo Fisher Scientific. Inc.

Emergency Telephone Number
Chemtrec US: (800) 424-9300
Chemtrec EU: 001 (202) 483-7616
A Part of Thermo Fisher Scientific. Inc.

8365 Valley Pike

Middletown, VA 22645-1905

Tel: (800) 528-0494

2. Hazard(s) identification

Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin Corrosion/irritation

Serious Eye Damage/Eye Irritation

Skin Sensitization

Category 1

Carcinogenicity

Category 1

Category 1

Category 1

Category 1

Category 1

Category 1

Target Organs - Central nervous system (CNS).

Specific target organ toxicity - (repeated exposure)

Target Organs - Kidney, Liver, spleen, Blood.

Label Elements

Signal Word

Danger

Hazard Statements

Causes skin irritation

Category 2

May cause an allergic skin reaction Causes serious eye damage May cause drowsiness or dizziness May cause cancer Causes damage to organs

May cause damage to organs through prolonged or repeated exposure



Precautionary Statements

Prevention

Obtain special instructions before use

Do not handle until all safety precautions have been read and understood

Use personal protective equipment as required

Wash face, hands and any exposed skin thoroughly after handling

Contaminated work clothing should not be allowed out of the workplace

Wear protective gloves

Do not breathe dust/fume/gas/mist/vapors/spray

Do not eat, drink or smoke when using this product

Use only outdoors or in a well-ventilated area

Response

IF exposed: Call a POISON CENTER or doctor/physician

Inhalation

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell

Skin

IF ON SKIN: Wash with plenty of soap and water

Take off contaminated clothing and wash before reuse

If skin irritation or rash occurs: Get medical advice/attention

Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing Immediately call a POISON CENTER or doctor/physician

Storage

Store locked up

Store in a well-ventilated place. Keep container tightly closed

Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Other hazards

WARNING! This product contains a chemical known in the State of California to cause birth defects or other reproductive harm.

Unknown Acute Toxicity

<2 % of the mixture consists of ingredients of unknown toxicity.

3. Composition / information on ingredients

| Component | CAS-No | Weight % |
|-----------------------------|-----------|-----------|
| Water | 7732-18-5 | > 90 |
| Sodium phosphate, monobasic | 7558-80-7 | < 1.0 |
| Sodium phosphate dibasic | 7558-79-4 | < 1.0 |
| Formaldehyde | 50-00-0 | 3.5 - 4.0 |
| Methyl alcohol | 67-56-1 | 1.0 - 2.0 |

4. First-aid measures

Eye Contact Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Obtain medical attention.

Skin Contact Wash off immediately with plenty of water for at least 15 minutes. Obtain medical attention.

Inhalation Move to fresh air. If breathing is difficult, give oxygen. Get medical attention immediately if

symptoms occur.

Ingestion Do not induce vomiting. Obtain medical attention.

include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness,

lightheadedness, chest pain, muscle pain or flushing

Notes to Physician Treat symptomatically

5. Fire-fighting measures

Suitable Extinguishing Media Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

Unsuitable Extinguishing Media No information available

Flash Point > 93.3 °C / 199.9 °F
Method - No information available

Autoignition Temperature

Explosion Limits

No information available

Upper No data available
Lower No data available
Sensitivity to Mechanical Impact No information available
Sensitivity to Static Discharge No information available

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors. Keep product and empty container away from heat and sources of ignition.

Hazardous Combustion Products

Thermal decomposition can lead to release of irritating gases and vapors

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

NFPA

| Health | Flammability | Instability | Physical hazards |
|--------|--------------|-------------|------------------|
| 3 | 1 | 0 | N/A |

6. Accidental release measures

Personal Precautions Use personal protective equipment. Ensure adequate ventilation. Remove all sources of

ignition. Avoid contact with skin, eyes and clothing.

Environmental Precautions Should not be released into the environment. See Section 12 for additional ecological

information.

Methods for Containment and Clean Remove all sources of ignition. Soak up with inert absorbent material. Keep in suitable, **Up** closed containers for disposal.

7. Handling and storage

Handling Use only under a chemical fume hood. Wear personal protective equipment. Keep away

from open flames, hot surfaces and sources of ignition. Do not breathe vapors or spray

mist. Do not get in eyes, on skin, or on clothing.

Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat Storage

and sources of ignition.

8. Exposure controls / personal protection

Exposure Guidelines

| Component | ACGIH TLV | OSHA PEL | NIOSH IDLH |
|----------------|------------------|---------------------------------------|-----------------------------|
| Formaldehyde | Ceiling: 0.3 ppm | (Vacated) TWA: 3 ppm | IDLH: 20 ppm |
| | | (Vacated) STEL: 10 ppm | TWA: 0.016 ppm |
| | | (Vacated) Ceiling: 5 ppm | Ceiling: 0.1 ppm |
| | | TWA: 0.75 ppm | |
| | | STEL: 2 ppm | |
| Methyl alcohol | TWA: 200 ppm | (Vacated) TWA: 200 ppm | IDLH: 6000 ppm |
| | STEL: 250 ppm | (Vacated) TWA: 260 mg/m ³ | TWA: 200 ppm |
| | Skin | (Vacated) STEL: 250 ppm | TWA: 260 mg/m ³ |
| | | (Vacated) STEL: 325 mg/m ³ | STEL: 250 ppm |
| | | Skin | STEL: 325 mg/m ³ |
| | | TWA: 200 ppm | - |
| | | TWA: 260 mg/m ³ | |

| Component | Quebec | Mexico OEL (TWA) | Ontario TWAEV |
|----------------|--|--|---------------------------------------|
| Formaldehyde | Ceiling: 2 ppm Ceiling: 3 mg/m³ | Ceiling: 2 ppm Ceiling: 3 mg/m ³ | STEL: 1.0 ppm CEV: 1.5 ppm |
| Methyl alcohol | TWA: 200 ppm TWA: 262 mg/m³ STEL: 250 ppm STEL: 328 mg/m³ Skin | TWA: 200 ppm TWA: 260 mg/m³ STEL: 250 ppm STEL: 310 mg/m³ | TWA: 200 ppm STEL: 250 ppm Skin |

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH IDLH: The National Institute for Occupational Safety and Health Immediately Dangerous to Life or Health

Use only under a chemical fume hood. Ensure adequate ventilation, especially in confined **Engineering Measures**

areas. Ensure that eyewash stations and safety showers are close to the workstation

location.

Personal Protective Equipment

Wear appropriate protective eyeglasses or chemical safety goggles as described by **Eye/face Protection**

OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard

EN166.

Wear appropriate protective gloves and clothing to prevent skin exposure. Skin and body protection

Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard **Respiratory Protection**

EN 149. Use a NIOSH/MSHA or European Standard EN 149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

Handle in accordance with good industrial hygiene and safety practice. **Hygiene Measures**

9. Physical and chemical properties

Physical State Liquid **Appearance** Colorless

Odor Characteristic formaldehyde No information available **Odor Threshold**

Ha 6.9 - 7.1

Melting Point/Range No data available

Boiling Point/Range 102 °C / 215.6 °F > 93.3 °C / 199.9 °F **Flash Point Evaporation Rate** No information available Flammability (solid,gas) No information available

Flammability or explosive limits

No data available Upper Lower No data available

Vapor Pressure No information available **Vapor Density** No information available

Relative Density

Solubility No information available Partition coefficient; n-octanol/water No data available **Autoignition Temperature** No information available

Decomposition Temperature No information available **Viscosity** No information available

10. Stability and reactivity

Reactive Hazard None known, based on information available

Stable under normal conditions. Stability

Conditions to Avoid Incompatible products. Heat, flames and sparks.

Incompatible Materials Strong oxidizing agents

Hazardous Decomposition Products Thermal decomposition can lead to release of irritating gases and vapors

Hazardous Polymerization Hazardous polymerization does not occur.

Hazardous Reactions None under normal processing.

11. Toxicological information

Acute Toxicity

Product Information No acute toxicity information is available for this product

Oral LD50 Based on ATE data, the classification criteria are not met. ATE > 2000 mg/kg. Based on ATE data, the classification criteria are not met. ATE > 2000 mg/kg. **Dermal LD50** Based on ATE data, the classification criteria are not met. ATE > 20 mg/l. Vapor LC50

Component Information

| Component | LD50 Oral | LD50 Dermal | LC50 Inhalation |
|-----------------------------|------------------|------------------------|-----------------------|
| Sodium phosphate, monobasic | 8290 mg/kg (Rat) | 7940 mg/kg (Rabbit) | Not listed |
| Sodium phosphate dibasic | 17 g/kg (Rat) | Not listed | Not listed |
| Formaldehyde | 500 mg/kg (Rat) | 270 mg/kg (Rabbit) | 0.578 mg/L (Rat) 4 h |
| Methyl alcohol | 6200 mg/kg (Rat) | 15800 mg/kg (Rabbit) | 64000 ppm (Rat) 4 h |
| | | | 83.2 mg/L (Rat) 4 h |

Toxicologically Synergistic

Products

No information available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Irritation No information available

Sensitization May cause sensitization by skin contact

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

| Component | CAS-No | IARC | NTP | ACGIH | OSHA | Mexico |
|-----------------------------|-----------|------------|------------|------------|------------|------------|
| Water | 7732-18-5 | Not listed |
| Sodium phosphate, monobasic | 7558-80-7 | Not listed |

NTP: (National Toxicity Program)

Revision Date 30-Mar-2015

| Sodium phosphate dibasic | 7558-79-4 | Not listed | |
|--------------------------|-----------|------------|------------|------------|------------|------------|--|
| Formaldehyde | 50-00-0 | Group 1 | Known | A2 | X | A2 | |
| Methyl alcohol | 67-56-1 | Not listed | |

IARC: (International Agency for Research on Cancer)

IARC: (International Agency for Research on Cancer)

Group 1 - Carcinogenic to Humans

Group 2A - Probably Carcinogenic to Humans Group 2B - Possibly Carcinogenic to Humans

NTP: (National Toxicity Program) Known - Known Carcinogen

Reasonably Anticipated - Reasonably Anticipated to be a Human

Carcinogen

ACGIH: (American Conference of Governmental Industrial

Hygienists)

A1 - Known Human Carcinogen A2 - Suspected Human Carcinogen

A3 - Animal Carcinogen

ACGIH: (American Conference of Governmental Industrial Hygienists)

Mutagenic Effects Mutagenic effects have occurred in humans.

Experiments have shown reproductive toxicity effects on laboratory animals. **Reproductive Effects**

Developmental effects have occurred in experimental animals. Component substance is **Developmental Effects**

listed on California Proposition 65 as a developmental hazard.

Teratogenic effects have occurred in experimental animals. **Teratogenicity**

STOT - single exposure Central nervous system (CNS) STOT - repeated exposure Kidney Liver spleen Blood

No information available **Aspiration hazard**

delayed

Symptoms / effects, both acute and Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling

of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

Endocrine Disruptor Information No information available

See actual entry in RTECS for complete information. Other Adverse Effects

12. Ecological information

Ecotoxicity

| Component | Freshwater Algae | Freshwater Fish | Microtox | Water Flea |
|----------------|------------------|---------------------------|--------------------------|-----------------------|
| Formaldehyde | Not listed | Leuciscus idus: LC50 = 15 | Not listed | EC50 = 20 mg/L 96h |
| | | mg/L 96h | | EC50 = 2 mg/L 48h |
| Methyl alcohol | Not listed | Pimephales promelas: LC50 | EC50 = 39000 mg/L 25 min | EC50 > 10000 mg/L 24h |
| | | > 10000 mg/L 96h | EC50 = 40000 mg/L 15 min | - |
| | | | EC50 = 43000 mg/L 5 min | |

Persistence and Degradability No information available Bioaccumulation/ Accumulation No information available.

Mobility

| Component | log Pow |
|----------------|---------|
| Formaldehyde | -0.35 |
| Methyl alcohol | -0.74 |

13. Disposal considerations

Waste Disposal Methods

Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

| Component | RCRA - U Series Wastes | RCRA - P Series Wastes |
|-----------|------------------------|------------------------|
|-----------|------------------------|------------------------|

Protocol™ 10% Neutral Buffered Formalin

| Formaldehyde - 50-00-0 | U122 | - |
|--------------------------|------|---|
| Methyl alcohol - 67-56-1 | U154 | - |

14. Transport information

DOTNot regulatedTDGNot regulatedIATANot regulatedIMDG/IMONot regulated

15. Regulatory information

International Inventories

| Component | TSCA | DSL | NDSL | EINECS | ELINCS | NLP | PICCS | ENCS | AICS | IECSC | KECL |
|--------------------------------|------|-----|------|-----------|--------|-----|-------|------|------|-------|------|
| Water | Х | Х | - | 231-791-2 | - | | Х | - | Χ | Х | Χ |
| Sodium phosphate, monobasic | Х | Х | - | 231-449-2 | - | | Х | Χ | Х | Х | Х |
| Sodium phosphate dibasic | Х | Х | - | 231-448-7 | - | | Χ | Χ | Х | Х | Χ |
| Formaldehyde | Х | X | - | 200-001-8 | - | | Х | Χ | Х | Х | Χ |
| Methyl alcohol | Х | Х | - | 200-659-6 | - | | Х | Χ | Х | Х | X |

Legend:

- X Listed
- E Indicates a substance that is the subject of a Section 5(e) Consent order under TSCA.
- F Indicates a substance that is the subject of a Section 5(f) Rule under TSCA.
- N Indicates a polymeric substance containing no free-radical initiator in its inventory name but is considered to cover the designated polymer made with any free-radical initiator regardless of the amount used.
- P Indicates a commenced PMN substance
- R Indicates a substance that is the subject of a Section 6 risk management rule under TSCA.
- S Indicates a substance that is identified in a proposed or final Significant New Use Rule
- T Indicates a substance that is the subject of a Section 4 test rule under TSCA.
- XU Indicates a substance exempt from reporting under the Inventory Update Rule, i.e. Partial Updating of the TSCA Inventory Data Base Production and Site Reports (40 CFR 710(B).
- Y1 Indicates an exempt polymer that has a number-average molecular weight of 1,000 or greater.
- Y2 Indicates an exempt polymer that is a polyester and is made only from reactants included in a specified list of low concern reactants that comprises one of the eligibility criteria for the exemption rule.

U.S. Federal Regulations

TSCA 12(b)

Not applicable

SARA 313

| Component | CAS-No | Weight % | SARA 313 - Threshold Values % |
|----------------|---------|-----------|----------------------------------|
| Formaldehyde | 50-00-0 | 3.5 - 4.0 | 0.1 |
| Methyl alcohol | 67-56-1 | 1.0 - 2.0 | 1.0 |

SARA 311/312 Hazardous Categorization

Acute Health HazardYesChronic Health HazardYesFire HazardYesSudden Release of Pressure HazardNoReactive HazardNo

Clean Water Act

| Component | CWA - Hazardous Substances | CWA - Reportable Quantities | CWA - Toxic Pollutants | CWA - Priority Pollutants |
|--------------------------|-------------------------------|--------------------------------|------------------------|---------------------------|
| Sodium phosphate dibasic | X | 5000 lb | - | - |
| Formaldehyde | X | 100 lb | - | - |

Clean Air Act

| Component | HAPS Data | Class 1 Ozone Depletors | Class 2 Ozone Depletors |
|-----------|-------------|--------------------------|--------------------------|
| Component | IIAI O Data | Oldos i Ozolic Depictors | Oldos E Ozolic Depictors |

| Formaldehyde | Х | - |
|----------------|---|---|
| Methyl alcohol | X | - |

OSHA Occupational Safety and Health Administration Not applicable

| Component | Specifically Regulated Chemicals | Highly Hazardous Chemicals |
|--------------|----------------------------------|----------------------------|
| Formaldehyde | 2 ppm STEL | TQ: 1000 lb |
| | 0.5 ppm Action Level | |
| | 0.75 ppm TWA | |

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

| Component | Hazardous Substances RQs | CERCLA EHS RQs |
|--------------------------|--------------------------|----------------|
| Sodium phosphate dibasic | 5000 lb | - |
| Formaldehyde | 100 lb | 100 lb |
| Methyl alcohol | 5000 lb | - |

California Proposition 65

This product contains the following Proposition 65 chemicals:

| Component | CAS-No | California Prop. 65 | Prop 65 NSRL | Category |
|----------------|---------|---------------------|--------------|---------------|
| Formaldehyde | 50-00-0 | Carcinogen | 40 μg/day | Carcinogen |
| Methyl alcohol | 67-56-1 | Developmental | - | Developmental |

State Right-to-Know

| Component | Massachusetts | New Jersey | Pennsylvania | Illinois | Rhode Island |
|--------------------------|---------------|------------|--------------|----------|--------------|
| Water | - | - | X | - | - |
| Sodium phosphate dibasic | Х | Х | Х | - | - |
| Formaldehyde | X | Х | X | Х | Х |
| Methyl alcohol | X | X | X | X | X |

U.S. Department of Transportation

Reportable Quantity (RQ): Y
DOT Marine Pollutant N
DOT Severe Marine Pollutant N

U.S. Department of Homeland Security

This product contains the following DHS chemicals:

| Component | DHS Chemical Facility Anti-Terrorism Standard |
|-----------------------------|---|
| Sodium phosphate, monobasic | 2000 lb STQ |
| Formaldehyde | 11250 lb STQ (solution) |

Other International Regulations


Mexico - Grade Slight risk, Grade 1

Canada

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations (CPR) and the MSDS contains all the information required by the CPR

WHMIS Hazard Class D2A Very toxic materials

E Corrosive material



16. Other information

Prepared By Regulatory Affairs

Thermo Fisher Scientific

Email: EMSDS.RA@thermofisher.com

 Creation Date
 22-Feb-2010

 Revision Date
 30-Mar-2015

 Print Date
 30-Mar-2015

Revision Summary This document has been updated to comply with the US OSHA HazCom 2012 Standard

replacing the current legislation under 29 CFR 1910.1200 to align with the Globally

Harmonized System of Classification and Labeling of Chemicals (GHS)

Disclaimer

The information provided on this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guide for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered as a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other material or in any process, unless specified in the text.

End of SDS