
Product Specifications

	VWR Part Number:	IR1386
	ImmunoReagents, Inc. Part Number:	GtxBo-003-DHRPX
Product:	GOAT X BOVINE IGG HRP 1VL	
Concentration:	1.0 mg/ml	
Amount:	1.0 mg	
Conjugate:	Horseradish Peroxidase	
Form:	Lyophilized	
Purification:	Affinity purified using solid phase Bovine IgG (H&L)	
Purity:	Affinity purified antibody is > 95% based on SDS-PAGE	
Host:	Goat	
Immunogen:	Purified Bovine IgG, whole molecule	
Buffer:	10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 1 % (w/v) BSA, Protease/IgG free	
Storage:	Store freeze-dried powder at 2-8 °C.	
Shelf Life:	Store lyophilized material at 2-8 °C. For long term storage after reconstitution, dilute with 50% glycerol and store at -20 °C as a liquid.	
Specificity:	Based on IEP, this antibody reacts with: · heavy (?) chains on bovine IgG · light chains on all bovine immunoglobulins	
Cross Reactivity:	Based on IEP, no reactivity is observed to: · non-immunoglobulin bovine serum immunoglobulins	
Country of Origin:	Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.	
Applications:	This conjugate is suitable for all immunoassay applications. The optimal working dilution should be determined by the investigator. Suggested starting dilution(?): · 1:500-1:5,000 for Immunohistochemistry · 1:200-1:5000 for ELISA/Western blot	
Disclaimer:	For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.	

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.