

SECTION 1: Identification

1.1. Product Identifier

Trade Name or Designation: Chloridometer Acid Reagent

Product Number: 1970 Other Identifying Product Numbers: 1970-16, 1970-5

1.2. Recommended Use and Restrictions on Use

General Laboratory Reagent

1.3. Details of the Supplier of the Safety Data Sheet

Company: Ricca Chemical Company

Address: 448 West Fork Drive Arlington, TX 76012 USA Telephone: 888-467-4222

1.4. Emergency Telephone Number (24 hr)

CHEMTREC (USA) 800-424-9300 CHEMTREC (International) 1+ 703-527-3887

SECTION 2: Hazard(s) Identification

2.1. Classification of the Substance or Mixture (in accordance with OSHA HCS 29 CFR 1910.1200)

For the full text of the Hazard and Precautionary Statements listed below, see Section 16.

		Hazard	
Hazard Class	Category	Statement	Precautionary Statements
Acute Toxicity - Inhalation	Category 4	H332	P261, P271, P304+P340, P312
Skin Corrosion / Irritation	Category 1	H314	P260, P264, P280, P301+P330+P331,
			P303+P361+P353, P363, P304+P340, P310,
			P321, P305+P351+P338, P405, P501
Eye Damage / Irritation	Category 1	H318	P280, P305+P351+P338, P310
Respiratory Sensitizer	Category 1	H334	P261, P285, P304+P341, P342+P311, P501
Specific Target Organs/Systemic Toxicity Following Single	Category 1	H370	P260, P264, P270, P307+P311, P321, P405,
Exposure			P501
Specific Target Organs/Systemic Toxicity Following Repeated	Category 2	H373	P260, P314, P501
Exposure	-		
Corrosive to Metals	Category 1	H290	P234, P390, P406



2.2. GHS Label Elements





Signal Word: Danger

Hazard Statements:

Hazard Number	Hazard Statement
H290	May be corrosive to metals.
H314	Causes severe skin burns and eye damage.
H318	Causes serious eye damage.
H332	Harmful if inhaled.
H334	May cause allergy or asthma symptoms or breathing difficulties if inhaled.
H370	Causes damage to organs.
H373	May cause damage to organs through prolonged or repeated exposure.

Safety Data Sheet

Precautionary Statements: Precautionary Number Precautionary Statement P234 Keep only in original container. P260 Do not breathe dust, fumes or mist. P261 Avoid breathing dust, fumes or mist. P264 Wash arms, hands and face thoroughly after handling. P270 Do not eat, drink or smoke when using this product. P271 Use only outdoors or in a well-ventilated area. P280 Wear protective gloves and eye protection. P285 In case of inadequate ventilation wear respiratory protection. P301+P330+P331 IF SWALLOWED: rinse mouth. Do NOT induce vomiting. P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water. P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing. P304+P341 IF INHALED: If breathing is difficult, remove person to fresh air and keep comfortable for breathing. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P307+P311 IF exposed: Call a POISON CENTER or physician. P310 Immediately call a POISON CENTER or physician. P312 Call a POISON CENTER or physician if you feel unwell. P314 Get medical attention if you feel unwell. P321 Specific treatment (Wash areas of contact with water immediately). P342+P311 If experiencing respiratory symptoms: Call a POISON CENTER or physician. Wash contaminated clothing before reuse. P363 P390 Absorb spillage to prevent material damage. P405 Store locked up. P406 Store in corrosive resistant container with a resistant inner liner. P501 Dispose of contents in accordance with local, state, federal and international regulations.

2.3. WHMIS Classification

WHMIS classification is not included based on the recommended option (Option 4) found in the Canada Gazette Part II, Vol. 149, No.3, page 458

2.4. Hazards not Otherwise Classified or Covered by GHS

Data not available.

Safety Data Sheet

SECTION 3: Composition / Information on Ingredients

3.1. Components of Substance or Mixture

Chemical Name	Formula	Molecular Weight	CAS Number	Weight%
Water	H₂O	18.01 g/mol	7732-18-5	88.16%
Acetic Acid	CH₃COOH	60.05 g/mol	64-19-7	10.50%
Polyvinyl Alcohol	C_2H_4O	Data not available.	9002-89-5	0.90%
Nitric Acid	HNO_3	63.01 g/mol	7697-37-2	0.44%
Sodium Chloride	NaCl	58.44 g/mol	7647-14-5	0.00%

SECTION 4: First-Aid Measures

4.1. General First Aid Information

- Eye Contact: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Irritant, possibly corrosive to eye tissue. Symptoms include tearing, redness, pain, and impaired vision.
- Inhalation: IF INHALED: If breathing is difficult, remove person to fresh air and keep comfortable for breathing.
- Skin Contact: IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water. May cause irritation, redness, itching and pain, especially on damaged or broken skin.
 - Ingestion: IF SWALLOWED: rinse mouth. Do NOT induce vomiting. Do not induce vomiting. Give large quantity of water. Call a physician immediately.

4.2. Most Important Symptoms and Effects, Acute and Delayed

DANGER! Causes burns. May be harmful if swallowed. Avoid ingestion or contact with skin, eyes, or clothing. If swallowed, do not induce vomiting. Give large quantity of water and call a physician. Wash areas of contact with plenty of water for 15 minutes. For eyes, get medical attention. EYE CONTACT: Irritant, possibly corrosive to eye tissue. Symptoms include tearing, redness, pain, and impaired vision. SKIN CONTACT: May cause irritation, redness, itching and pain, especially on damaged or broken skin. CHRONIC EFFECTS / CARCINOGENICITY: Repeated exposures may cause erosion of exposed front teeth, darkening of skin and chronic inflammation of the nose, throat and bronchial tubes.

4.3. Medical Attention or Special Treatment Needed

Immediately call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately).

SECTION 5: Fire-Fighting Measures

5.1. Extinguishing Media

Water, dry chemical, foam, or carbon dioxide. Water spray may be used to keep fire-exposed containers cool.

5.2. Specific Hazards Arising from the Substance or Mixture

Slight fire hazard when subject to high heat, containers may explode in fire.

5.3. Special Protective Equipment for Firefighters

Use protective clothing and NIOSH-approved breathing equipment appropriate for the surrounding fire.

Safety Data Sheet

SECTION 6: Accidental Release Measures

6.1. Personal Precautions, Protective Equipment and Emergency Procedures

Wear protective gloves and eye protection. In case of inadequate ventilation wear respiratory protection.

6.2. Cleanup and Containment Methods and Materials

Absorb with inert material (vermiculite, sand). Ventilate, if necessary, site of spillage well to evaporate remaining liquid and dispel vapor. Do not flush to sewer. Always comply with local, state, and federal regulations.

SECTION 7: Handling and Storage

7.1. Precautions for Safe Handling and Storage Conditions

Store in corrosive resistant container with a resistant inner liner. As with all chemicals, wash hands thoroughly after handling. Avoid contact with eyes and skin. Protect from freezing and physical damage.

SECTION 8: Exposure Controls / Personal Protection

8.1. Control Parameters

Chemical Name	Limit Type	Country	Exposure Limit	Information Source
Acetic Acid (64-19-7)	TWA	USA	10 ppm TWA	U.S OSHA - Final PELs - Time
			25 mg/m³ TWA	Weighted Averages (TWAs)
Acetic Acid (64-19-7)	TLV-STEL	USA	15 ppm STEL	ACGIH - Threshold Limit Values - Short
				Term Exposure Limits (TLV-STEL)
Acetic Acid (64-19-7)	TLV-TWA	USA	10 ppm TWA	ACGIH - Threshold Limit Values - Time
				Weighted Averages (TLV-TWA)
Nitric Acid (7697-37-2)	TWA	USA	2 ppm TWA	U.S OSHA - Final PELs - Time
			5 mg/m³ TWA	Weighted Averages (TWAs)
Nitric Acid (7697-37-2)	TLV-STEL	USA	4 ppm STEL	ACGIH - Threshold Limit Values - Short
				Term Exposure Limits (TLV-STEL)
Nitric Acid (7697-37-2)	TLV-TWA	USA	2 ppm TWA	ACGIH - Threshold Limit Values - Time
				Weighted Averages (TLV-TWA)

8.2. Exposure Controls

Engineering Controls:	Use only outdoors or in a well-ventilated area. A system of local and/or general exhaust is recommended to keep employee exposures below the Airborne Exposure Limit.
Respiratory Protection:	In case of inadequate ventilation wear respiratory protection. Work with adequate ventilation or wear respirator with acid gas/organic vapor cartridge.
Skin Protection:	Wear protective gloves and eye protection. Chemical resistant gloves.
Eye Protection:	Wear protective gloves and eye protection. Safety glasses or goggles.



8.3. Personal Protective Equipment

Wear protective gloves and eye protection. In case of inadequate ventilation wear respiratory protection. Work with adequate ventilation or wear respirator with acid gas/organic vapor cartridge. Chemical resistant gloves. Safety glasses or goggles.

SECTION 9: Physical and Chemical Properties

9.1. Basic Physical and Chemical Properties

Appearance:	Colorless liquid
Physical State:	Liquid
Odor:	Data not available.
Odor Threshold:	Data not available.
pH:	<1
Melting/Freezing Point:	Approximately 0°C
Initial Boiling Point /Range:	Approximately 100°C - Approximately 100°C
Flash Point:	Data not available.
Evaporation Rate:	Data not available.
Flammability:	Data not available.
Flammability/Explosive Limits:	Data not available.
Vapor Pressure:	Data not available.
Vapor Density:	Data not available.
Relative Density:	Data not available.
Solubility:	Miscible
Partition Coefficient (n-Octanol/Water):	Data not available.
Auto-Ignition Temperature:	Data not available.
Decomposition Temperature:	Data not available.
Viscosity:	Data not available.
ExplosiveProperties:	Data not available.
Oxidizing Properties:	Data not available.

SECTION 10: Stability and Reactivity

10.1. Reactivity and Chemical Stability

Stable under normal conditions of use and storage.

10.2. Possibility of Hazardous Reactions

Data not available.

10.3. Conditions to Avoid and Incompatible Materials

Keep only in original container. Strong bases, strong oxidizers, chromic acid, sodium peroxide, perchloric acid.



10.4. Hazardous Decomposition Products

Will not occur.

SECTION 11: Toxicological Information

11.1. Information on Toxicological Effects

Acute Toxicity - Oral Exposure:

Not applicable.

Acute Toxicity - Dermal Exposure:

Not applicable.

Acute Toxicity - Inhalation Exposure:

Harmful if inhaled. Avoid breathing dust, fumes or mist. Use only outdoors or in a well-ventilated area. IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or physician if you feel unwell.

Acute Toxicity - Other Information:

LD50, Oral, Rat (Acetic Acid): 3310 mg/kg; LD50, Dermal, Rabbit (Acetic Acid): 1.06 L/kg, details of toxic effects not reported other than lethal dose value. LDLo, Oral, Human: 430 mg/kg (Nitric Acid), details of toxic effects not reported other than lethal dose value.

Skin Corrosion and Irritation:

Causes severe skin burns and eye damage. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Wear protective gloves and eye protection. IF SWALLOWED: rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water. Wash contaminated clothing before reuse. IF INHALED: Remove person to fresh air and keep comfortable for breathing. Immediately call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately). IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Serious Eye Damage and Irritation:

Causes serious eye damage. Wear protective gloves and eye protection. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or physician.

Respiratory Sensitization:

May cause allergy or asthma symptoms or breathing difficulties if inhaled. Avoid breathing dust, fumes or mist. In case of inadequate ventilation wear respiratory protection. IF INHALED: If breathing is difficult, remove person to fresh air and keep comfortable for breathing. If experiencing respiratory symptoms: Call a POISON CENTER or physician. Dispose of contents in accordance with local, state, federal and international regulations.

Skin Sensitization:

Not applicable.

Germ Cell Mutagenicity:

Not applicable.

Carcinogenicity:

Not applicable.

Safety Data Sheet

Reproductive Toxicity:

Not applicable.

Specific Target Organ Toxicity from Single Exposure:

Causes damage to organs. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Do not eat, drink or smoke when using this product. IF exposed: Call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately). Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Specific Target Organ Toxicity from Repeated Exposure:

May cause damage to organs through prolonged or repeated exposure. Do not breathe dust, fumes or mist. Get medical attention if you feel unwell. Dispose of contents in accordance with local, state, federal and international regulations.

Aspiration Hazard:

Not applicable.

Additional Toxicology Information:

Data not available.

SECTION 12: Ecological Information

12.1. Ecotoxicity

Not applicable.

12.2. Persistence and Degradability

Data not available.

12.3. Bioaccumulative Potential

Data not available.

12.4. Mobility in Soil

Data not available.

12.5. Other Adverse Ecological Effects

Data not available.

SECTION 13: Disposal Considerations

13.1. Waste Treatment Methods

Data not available.



SECTION 14: Transportation Information

14.1. Transportation by Land - Department of Transportation (DOT, United States of America)

UN Number: UN3265 Proper Shipping Name: Corrosive Liquid, Acidic, Organic, n.o.s., (Acetic Acid) Hazard Class: 8 Packing Group: III Hazard Placard Labels:



UN Number: UN3265 Proper Shipping Name: Corrosive Liquid, Acidic, Organic, n.o.s., (Acetic Acid) Hazard Class: 8 Packing Group: III Hazard Placard Labels:



SECTION 15: Regulatory Information

- 15.1. Occupational Safety and Health Administration (OSHA) Hazards Not listed.
- **15.2. Superfund Amendments and Reauthorization Act (SARA) 302 Extremely Hazardous Substances** Nitric Acid (CAS # 7697-37-2): 1000 lb EPCRA RQ Nitric Acid (CAS # 7697-37-2): 1000 lb TPQ
- **15.3. Superfund Amendments and Reauthorization Act (SARA) 311/312 Hazardous Chemicals** Acetic Acid (CAS # 64-19-7): 5000 lb final RQ; 2270 kg final RQ Nitric Acid (CAS # 7697-37-2): 1000 lb final RQ; 454 kg final RQ
- **15.4. Superfund Amendments and Reauthorization Act (SARA) 313 Toxic Release Inventory (TRI)** Nitric Acid (CAS # 7697-37-2): 1.0 % de minimis concentration



15.5. Massachusetts Right-to-Know Substance List

Acetic Acid (CAS # 64-19-7): Present Nitric Acid (CAS # 7697-37-2): Extraordinarily hazardous

15.6. Pennsylvania Right-to-Know Hazardous Substances

Acetic Acid (CAS # 64-19-7): Environmental hazard Acetic Acid (CAS # 64-19-7): Present Nitric Acid (CAS # 7697-37-2): Environmental hazard Nitric Acid (CAS # 7697-37-2): Present Water (CAS # 7732-18-5): Present

15.7. New Jersey Worker and Community Right-to-Know Components

Acetic Acid (CAS # 64-19-7): corrosive Acetic Acid (CAS # 64-19-7): sn 0004 Nitric Acid (CAS # 7697-37-2): corrosive; reactive - second degree Nitric Acid (CAS # 7697-37-2): sn 1356 Nitric Acid (CAS # 7697-37-2): SN 1356 TPQ: 500 lb Nitric Acid (CAS # 7697-37-2): sn 3722 Nitric Acid (CAS # 7697-37-2): SN 3722 TPQ: 500 lb (water dissociable, Category Code N511)

15.8. California Proposition 65

Not listed.

15.9. Canada Domestic Substances List / Non-Domestic Substances List (DSL/NDSL)

Acetic Acid (CAS # 64-19-7): Present Sodium Chloride (CAS # 7647-14-5): Present Nitric Acid (CAS # 7697-37-2): Present Water (CAS # 7732-18-5): Present Polyvinyl Alcohol (CAS # 9002-89-5): Present

15.10. United States of America Toxic Substances Control Act (TSCA) List

Acetic Acid (CAS # 64-19-7): Present Sodium Chloride (CAS # 7647-14-5): Present Nitric Acid (CAS # 7697-37-2): Present Water (CAS # 7732-18-5): Present Polyvinyl Alcohol (CAS # 9002-89-5): Present [XU]

15.11. European Inventory of Existing Commercial Chemical Substances (EINECS),

European List of Notified Chemical Substances (ELINCS), and No Longer Polymers (NLP)

Not listed.

Safety Data Sheet

SECTION 16: Other Information

16.1. Full Text of Hazard Statements and Precautionary Statements

May be corrosive to metals. Causes severe skin burns and eye damage. Causes serious eye damage. Harmful if inhaled. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Causes damage to organs. May cause damage to organs through prolonged or repeated exposure.

Keep only in original container. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Do not eat, drink or smoke when using this product. Use only outdoors or in a well-ventilated area. Wear protective gloves and eye protection. In case of inadequate ventilation wear respiratory protection.

IF SWALLOWED: rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water. IF INHALED: Remove person to fresh air and keep comfortable for breathing. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. IF exposed: Call a POISON CENTER or physician. Get medical attention if you feel unwell. Specific treatment (Wash areas of contact with water immediately). If experiencing respiratory symptoms: Call a POISON CENTER or physician. Wash contaminated clothing before reuse. Absorb spillage to prevent material damage.

Store locked up. Store in corrosive resistant container with a resistant inner liner.

Dispose of contents in accordance with local, state, federal and international regulations.

16.2. Miscellaneous Hazard Classes

Canadian Carcinogenicity Hazard Class: Not Applicable. Physical Hazards Not Otherwise Classified (PHNOC): Not Applicable. Health Hazards Not Otherwise Classified (HHNOC): Not Applicable. Not Applicable.

16.3. National Fire Protection Association (NFPA) Rating

Health: 2 Flammability: 0 Reactivity: 0 Special Hazard:



16.4. Document Revision

Last Revision Date: 5/1/2015



DISCLAIMER

When handled properly by qualified personnel, the product described herein does not present a significant health or safety hazard. Alteration of its characteristics by concentration, evaporation, addition of other substances, or other means may present hazards not specifically addressed herein and which must be evaluated by the user. The information furnished herein is believed to be accurate and represents the best data currently available to us. No warranty, expressed or implied, is made and RICCA CHEMICAL COMPANY assumes no legal responsibility or liability whatsoever resulting from its use.