
Product Specifications

VWR Part Number: IR2114
ImmunoReagents, Inc. Part Number: GtxOt-070-D650NHSX

Product: GOAT X OT-070-DYLG 650 1MG

Concentration: 1.0 mg/ml (E 1% at 280 nm = 13.0)

Amount: 1.0 mg

Conjugate: DyLight® 650 (Ex = 652 nm; Em = 672 nm)

Form: Lyophilized

Purification: Affinity purified using solid phase biotin

Purity: Affinity purified antibody is > 95% based on SDS-PAGE

Host: Goat

Immunogen: BSA-Biotin, KLH-Biotin

Buffer: 10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 1 % (w/v) BSA, Protease/IgG free

Storage: Store freeze-dried powder at 2-8 °C.

Shelf Life: Product is stable for up to 4 weeks at 2-8°C after rehydration. For extended storage after rehydration, add an equal volume of glycerol and store at -20°C.

Specificity: This antibody reacts with Biotin

Cross Reactivity: This antibody does not react with free BSA or free KLH

Country of Origin: Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.

Applications: This conjugate is suitable for immunomicroscopy and flow cytometry. The optimal working dilution should be determined by the investigator. Suggested starting dilution(?): · 1:20 - 1:2,000 for most applications

Disclaimer: For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.