RICCA CHEMICAL COMPANY®

Safety Data Sheet

SECTION 1: Identification

1.1. Product Identifier

Trade Name or Designation: Potassium Hydroxide, 45% (w/w) FCC

Product Number: R6193000
Other Identifying Product Numbers: R6193000-100A

1.2. Recommended Use and Restrictions on Use

General Laboratory Reagent

1.3. Details of the Supplier of the Safety Data Sheet

Company: Ricca Chemical Company

Address: 448 West Fork Drive
Arlington, TX 76012 USA
Telephone: 888-467-4222

1.4. Emergency Telephone Number (24 hr)

CHEMTREC (USA) 800-424-9300
CHEMTREC (International) 1+ 703-527-3887

SECTION 2: Hazard(s) Identification

2.1. Classification of the Substance or Mixture (in accordance with OSHA HCS 29 CFR 1910.1200)

For the full text of the Hazard and Precautionary Statements listed below, see Section 16.

Hazard Class	Category	Hazard Statement	Precautionary Statements
Acute Toxicity - Oral	Category 3	H301	P264, P270, P301+P310, P321, P330, P405, P501
Skin Corrosion / Irritation	Category 1	H314	P260, P264, P280, P301+P330+P331, P303+P361+P353, P363, P304+P340, P310, P321, P305+P351+P338, P405, P501
Eye Damage / Irritation	Category 1	H318	P280, P305+P351+P338, P310
Specific Target Organs/Systemic Toxicity Following Single Exposure	Category 1	H370	P260, P264, P270, P307+P311, P321, P405, P501
Aspiration Hazard	Category 1	H304	P301+P310, P331, P405, P501
Corrosive to Metals	Category 1	H290	P234, P390, P406
Hazardous to the Aquatic Environment (Acute)	Category 3	H402	P273, P501

Safety Data Sheet

2.2. GHS Label Elements

Pictograms:



Signal Word: **Danger**

Hazard Statements:

Hazard Number	Hazard Statement
H290	May be corrosive to metals.
H301	Toxic if swallowed.
H304	May be fatal if swallowed and enters airways.
H314	Causes severe skin burns and eye damage.
H318	Causes serious eye damage.
H370	Causes damage to organs.
H402	Harmful to aquatic life.

Safety Data Sheet

Precautionary Statements:

Precautionary Number	Precautionary Statement
P234	Keep only in original container.
P260	Do not breathe dust, fumes or mist.
P264	Wash arms, hands and face thoroughly after handling.
P270	Do not eat, drink or smoke when using this product.
P273	Avoid release to the environment.
P280	Wear protective gloves and eye protection.
P301+P310	IF SWALLOWED: Immediately call a POISON CENTER or physician.
P301+P330+P331	IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P303+P361+P353	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P307+P311	IF exposed: Call a POISON CENTER or physician.
P310	Immediately call a POISON CENTER or physician.
P321	Specific treatment (Wash areas of contact with water immediately).
P330	Rinse mouth.
P331	Do NOT induce vomiting.
P363	Wash contaminated clothing before reuse.
P390	Absorb spillage to prevent material damage.
P405	Store locked up.
P406	Store in corrosive resistant container with a resistant inner liner.
P501	Dispose of contents in accordance with local, state, federal and international regulations.

2.3. WHMIS Classification

WHMIS classification is not included based on the recommended option (Option 4) found in the Canada Gazette Part II, Vol. 149, No.3, page 458

2.4. Hazards not Otherwise Classified or Covered by GHS

Data not available.

SECTION 3: Composition / Information on Ingredients

3.1. Components of Substance or Mixture

Chemical Name	Formula	Molecular Weight	CAS Number	Weight%
Potassium Hydroxide	KOH	56.10 g/mol	1310-58-3	52.07%
Water	H_2O	18.01 g/mol	7732-18-5	47.93%

SECTION 4: First-Aid Measures

4.1. General First Aid Information

Eye Contact: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Irritant, possibly corrosive to eye tissue. Symptoms include tearing, redness, pain, and impaired vision.

Inhalation: Not expected to require first aid. If necessary, remove to fresh air.

Skin Contact: IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water. May cause irritation, redness, and pain.

Ingestion: IF SWALLOWED: rinse mouth. Do NOT induce vomiting. Dilute with water or milk. Do not induce vomiting. Call a physician if necessary.

4.2. Most Important Symptoms and Effects, Acute and Delayed

Danger! Corrosive. Causes severe burns. May be fatal if swallowed. Wash areas of contact with plenty of water for at least 15 minutes. If ingested, dilute with a large quantity of water. Do not induce vomiting. Call a physician. EYE CONTACT: Irritant, possibly corrosive to eye tissue. Symptoms include tearing, redness, pain, and impaired vision. SKIN CONTACT: May cause irritation, redness, and pain. CHRONIC EFFECTS / CARCINOGENICITY: Prolonged or repeated exposure may cause dermatitis.

4.3. Medical Attention or Special Treatment Needed

Immediately call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately).

SECTION 5: Fire-Fighting Measures

5.1. Extinguishing Media

Use extinguishing media appropriate for surrounding fire.

5.2. Specific Hazards Arising from the Substance or Mixture

Not combustible. Dissolves in water, releasing heat. If moist, reacts with many common metals to form hydrogen gas. (solid)

5.3. Special Protective Equipment for Firefighters

Wear special protective clothing and positive pressure self-contained breathing apparatus. (solid)

SECTION 6: Accidental Release Measures

6.1. Personal Precautions, Protective Equipment and Emergency Procedures

Wear protective gloves and eye protection.

6.2. Cleanup and Containment Methods and Materials

Keep water away from release. Prompt cleanup and removal are necessary. Control runoff and isolate discharged material for proper disposal. (solid)

Safety Data Sheet

SECTION 7: Handling and Storage

7.1. Precautions for Safe Handling and Storage Conditions

Store in corrosive resistant container with a resistant inner liner. As with all chemicals, wash hands thoroughly after handling. Avoid contact with eyes and skin. Protect from freezing and physical damage. Do not mix with acids.

SECTION 8: Exposure Controls / Personal Protection

8.1. Control Parameters

Chemical Name	Limit Type	Country	Exposure Limit	Information Source
Potassium Hydroxide (1310-58-3)	TLV-Ceiling	USA	2 mg/m³ Ceiling	ACGIH - Threshold Limit Values - Ceilings (TLV-C)

8.2. Exposure Controls

Engineering Controls: No specific controls are needed. Normal room ventilation is adequate.

Respiratory Protection: Normal room ventilation is adequate.

Skin Protection: Wear protective gloves and eye protection. Chemical resistant gloves.

Eye Protection: Wear protective gloves and eye protection. Safety glasses or goggles.

8.3. Personal Protective Equipment

Wear protective gloves and eye protection. Normal room ventilation is adequate. Chemical resistant gloves. Safety glasses or goggles.

Safety Data Sheet

SECTION 9: Physical and Chemical Properties

9.1. Basic Physical and Chemical Properties

Appearance:	Colorless liquid
Physical State:	Liquid
Odor:	Data not available.
Odor Threshold:	Data not available.
pH:	> 13
Melting/Freezing Point:	Data not available.
Initial Boiling Point /Range:	Approximately 100°C - Approximately 100°C
Flash Point:	Data not available.
Evaporation Rate:	Data not available.
Flammability:	Data not available.
Flammability/Explosive Limits:	Data not available.
Vapor Pressure:	Data not available.
Vapor Density:	Data not available.
Relative Density:	1.45
Solubility:	Miscible
Partition Coeffieient (n-Octanol/Water):	Data not available.
Auto-Ignition Temperature:	Data not available.
Decomposition Temperature:	Data not available.
Viscosity:	Data not available.
ExplosiveProperties:	Data not available.
Oxidizing Properties:	Data not available.

SECTION 10: Stability and Reactivity

10.1. Reactivity and Chemical Stability

Stable under normal conditions of use and storage.

10.2. Possibility of Hazardous Reactions

Data not available.

10.3. Conditions to Avoid and Incompatible Materials

Keep only in original container. Strong acids, chlorinated Hydrocarbons, Acetone, metals such as aluminum, tin and zinc.

10.4. Hazardous Decomposition Products

Will not occur.

Safety Data Sheet

SECTION 11: Toxicological Information

11.1. Information on Toxicological Effects

Acute Toxicity - Oral Exposure:

Toxic if swallowed. Wash arms, hands and face thoroughly after handling. Do not eat, drink or smoke when using this product. IF SWALLOWED: Immediately call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately). Rinse mouth. Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Acute Toxicity - Dermal Exposure:

Not applicable.

Acute Toxicity - Inhalation Exposure:

Not applicable.

Acute Toxicity - Other Information:

LD50, Oral, Rat: (Potassium Hydroxide) 273 mg/kg, details of toxic effects not reported other than lethal dose value. Irritation data: skin, rabbit: 50 mg/24H severe; eye, rabbit: 1 mg/24H moderate. Investigated as a mutagen (Potassium Hydroxide).

Skin Corrosion and Irritation:

Causes severe skin burns and eye damage. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Wear protective gloves and eye protection. IF SWALLOWED: rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water. Wash contaminated clothing before reuse. IF INHALED: Remove person to fresh air and keep comfortable for breathing. Immediately call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately). IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Serious Eye Damage and Irritation:

Causes serious eye damage. Wear protective gloves and eye protection. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or physician.

Respiratory Sensitization:

Not applicable.

Skin Sensitization:

Not applicable.

Germ Cell Mutagenicity:

Not applicable.

Carcinogenicity:

Not applicable.

Reproductive Toxicity:

Not applicable.

Specific Target Organ Toxicity from Single Exposure:

Causes damage to organs. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Do not eat, drink or smoke when using this product. IF exposed: Call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately). Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Specific Target Organ Toxicity from Repeated Exposure:

Not applicable.

Aspiration Hazard:

May be fatal if swallowed and enters airways. IF SWALLOWED: Immediately call a POISON CENTER or physician. Do NOT induce vomiting. Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Additional Toxicology Information:

Data not available.

SECTION 12: Ecological Information

12.1. Ecotoxicity

Harmful to aquatic life. Avoid release to the environment. Dispose of contents in accordance with local, state, federal and international regulations.

12.2. Persistence and Degradability

Data not available.

12.3. Bioaccumulative Potential

Data not available.

12.4. Mobility in Soil

Data not available.

12.5. Other Adverse Ecological Effects

Data not available.

SECTION 13: Disposal Considerations

13.1. Waste Treatment Methods

Data not available.

SECTION 14: Transportation Information

14.1. Transportation by Land - Department of Transportation (DOT, United States of America)

UN Number: UN1814

Proper Shipping Name: Potassium Hydroxide, solution

Hazard Class: 8

Packing Group: II

Hazard Placard Labels:



Safety Data Sheet

14.2. Transportation by Air - International Air Transport Association (IATA)

UN Number: UN1814

Proper Shipping Name: Potassium Hydroxide, solution

Hazard Class: 8

Packing Group: II

Hazard Placard Labels:



SECTION 15: Regulatory Information

15.1. Occupational Safety and Health Administration (OSHA) Hazards

Not listed.

15.2. Superfund Amendments and Reauthorization Act (SARA) 302 Extremely Hazardous Substances

Not listed.

15.3. Superfund Amendments and Reauthorization Act (SARA) 311/312 Hazardous Chemicals

Potassium Hydroxide (CAS # 1310-58-3): 1000 lb final RQ; 454 kg final RQ

15.4. Superfund Amendments and Reauthorization Act (SARA) 313 Toxic Release Inventory (TRI)

Not listed.

15.5. Massachusetts Right-to-Know Substance List

Potassium Hydroxide (CAS # 1310-58-3): Present

15.6. Pennsylvania Right-to-Know Hazardous Substances

Potassium Hydroxide (CAS # 1310-58-3): Environmental hazard

Potassium Hydroxide (CAS # 1310-58-3): Present

Water (CAS # 7732-18-5): Present

15.7. New Jersey Worker and Community Right-to-Know Components

Potassium Hydroxide (CAS # 1310-58-3): corrosive

Potassium Hydroxide (CAS # 1310-58-3): sn 1571

15.8. California Proposition 65

Not listed.

15.9. Canada Domestic Substances List / Non-Domestic Substances List (DSL/NDSL)

Potassium Hydroxide (CAS # 1310-58-3): Present

Water (CAS # 7732-18-5): Present

15.10. United States of America Toxic Substances Control Act (TSCA) List

Potassium Hydroxide (CAS # 1310-58-3): Present

Water (CAS # 7732-18-5): Present

15.11. European Inventory of Existing Commercial Chemical Substances (EINECS), European List of Notified Chemical Substances (ELINCS), and No Longer Polymers (NLP)

Not listed.

SECTION 16: Other Information

16.1. Full Text of Hazard Statements and Precautionary Statements

May be corrosive to metals. Toxic if swallowed. Causes severe skin burns and eye damage. Causes serious eye damage. Causes damage to organs. Harmful to aquatic life.

Keep only in original container. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Do not eat, drink or smoke when using this product. Avoid release to the environment. Wear protective gloves and eye protection.

IF SWALLOWED: Immediately call a POISON CENTER or physician. IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water. IF INHALED: Remove person to fresh air and keep comfortable for breathing. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. IF exposed: Call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately). Wash contaminated clothing before reuse. Absorb spillage to prevent material damage.

Store locked up. Store in corrosive resistant container with a resistant inner liner.

Dispose of contents in accordance with local, state, federal and international regulations.

16.2. Miscellaneous Hazard Classes

Canadian Carcinogenicity Hazard Class: Not Applicable.

Physical Hazards Not Otherwise Classified (PHNOC): Not Applicable.


Health Hazards Not Otherwise Classified (HHNOC): Not Applicable.

Not Applicable.

Safety Data Sheet

16.3. National Fire Protection Association (NFPA) Rating

Health: 3
Flammability: 0
Reactivity: 1
Special Hazard:



16.4. Document Revision

Last Revision Date: 5/1/2015

DISCLAIMER

When handled properly by qualified personnel, the product described herein does not present a significant health or safety hazard. Alteration of its characteristics by concentration, evaporation, addition of other substances, or other means may present hazards not specifically addressed herein and which must be evaluated by the user. The information furnished herein is believed to be accurate and represents the best data currently available to us. No warranty, expressed or implied, is made and RICCA CHEMICAL COMPANY assumes no legal responsibility or liability whatsoever resulting from its use.