
Product Specifications

VWR Part Number:	IR1327
ImmunoReagents, Inc. Part Number:	DkxSh-003-FFITC
Product:	DONKEY X SHEEP IGG FITC 1VL
Concentration:	1.0 mg/ml (E 1% at 280 nm = 13.0)
Amount:	1.0 mg
Conjugate:	Fluorescein-5-isothiocyanate (FITC) Amax = 494 nm; Emax = 518 nm
Form:	Clear, fluorescent yellow liquid
Purification:	Affinity purified using solid phase Sheep IgG
Purity:	Affinity purified antibody is > 95% based on SDS-PAGE
Host:	Donkey
Immunogen:	Purified Sheep IgG, whole molecule
Buffer: Protease/IgG free	10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 1 % (w/v) BSA,
Storage:	2-8 °C
Shelf Life:	1 year from date of receipt. Prepare working dilution prior to use and then discard.
Specificity:	Based on IEP, this antibody reacts with: · heavy (?) chains on sheep IgG · light chains on all sheep immunoglobulins
Cross Reactivity:	Based on IEP, no reactivity is observed to: · non-immunoglobulin sheep serum proteins · IgG from human, mouse or rabbit
Country of Origin:	Donkey serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.
Applications:	This conjugate is suitable for immunomicroscopy and flow cytometry. The optimal working dilution should be determined by the investigator. Suggested starting dilution(?): · 1:20 - 1:2,000 for most applications
Disclaimer:	For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.