M

SAFETY DATA SHEET according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

	Revision Date 02/27/2015	Version 1.2
SECTION 1.Identification		
Product identifier		
Product number	803101	
Product name	Decahydronaphthalene (mixture of cis-and trans isomers) for s	synthesis
CAS-No.	91-17-8	
Relevant identified uses of t	he substance or mixture and uses advised against	
Identified uses	Chemical for synthesis	
Details of the supplier of the	e safety data sheet	
Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA (United States of America General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)	
Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week	

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 3, H226 Acute toxicity, Category 3, Inhalation, H331 Skin corrosion, Category 1B, H314 Serious eye damage, Category 1, H318 Aspiration hazard, Category 1, H304 For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word Danger

Hazard Statements H226 Flammable liquid and vapor. H304 May be fatal if swallowed and enters airways.

SAFETY DATA SHEET according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	803101	Version 1.2
Product name	Decahydronaphthalene (mixture of cis-and trans isomers) for synthesis	5

H314 Causes severe skin burns and eye damage.

H331 Toxic if inhaled.

Precautionary Statements

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P233 Keep container tightly closed.

P240 Ground/bond container and receiving equipment.

P241 Use explosion-proof electrical/ ventilating/ lighting/ equipment.

P242 Use only non-sparking tools.

P243 Take precautionary measures against static discharge.

P261 Avoid breathing dust/ fume/ gas/ mist/ vapors/ spray.

P264 Wash skin thoroughly after handling.

P271 Use only outdoors or in a well-ventilated area.

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

P301 + P310 IF SWALLOWED: Immediately call a POISON CENTER or doctor/ physician.

P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

P303 + P361 + P353 IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower.

P304 + P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P310 Immediately call a POISON CENTER or doctor/ physician.

P321 Specific treatment (see supplemental first aid instructions on this label).

P363 Wash contaminated clothing before reuse.

P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.

P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

P403 + P235 Store in a well-ventilated place. Keep cool.

P405 Store locked up.

P501 Dispose of contents/ container to an approved waste disposal plant.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	C₁₀H₁ଃ (Hill)
Molar mass	138.25 g/mol

Hazardous ingredients

Chemical Name (Concentration) CAS-No. Decahydronaphthalene (mixture of cis- and trans isomers) (>= 90 % - <= 100 %) 91-17-8 Exact percentages are being wihtheld as a trade secret.

SECTION 4. First aid measures Description of first-aid measures

Product number	803101	Version 1.2
Product name	Decahydronaphthalene (mixture of cis-and trans isomers) for synth	iesis

General advice

First aider needs to protect himself.

Inhalation

After inhalation: fresh air. Immediately call in physician. If breathing stops: immediately apply artificial respiration, if necessary also oxygen.

Skin contact

In case of skin contact: Take off immediately all contaminated clothing. Rinse skin with water/ shower. Call a physician immediately.

Eye contact

After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

Ingestion

After swallowing: make victim drink water (two glasses at most), avoid vomiting (risk of perforation!). Call a physician immediately. Pulmonary failure possible after aspiration of vomit. Do not attempt to neutralize.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Irritation and corrosion, Cough, Shortness of breath, Dizziness, Unconsciousness, narcosis, agitation, Nausea, Vomiting, Headache, Convulsions Risk of blindness!

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media Foam, Carbon dioxide (CO2), Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible. Vapors are heavier than air and may spread along floors. Forms explosive mixtures with air at elevated temperatures. Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Remove container from danger zone and cool with water. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Product number	803101	Version 1.2
Product name	Decahydronaphthalene (mixture of cis-and trans isomers) for synthe	sis

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Keep away from heat and sources of ignition. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders:

Protective equipment see section 8.

Environmental precautions

Do not let product enter drains. Risk of explosion.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills. Observe possible material restrictions (see sections 7 and 10). Take up carefully with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Work under hood. Do not inhale substance/mixture. Avoid generation of vapors/aerosols.

Observe label precautions.

Advice on protection against fire and explosion Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

Conditions for safe storage, including any incompatibilities

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat and sources of ignition. Keep locked up or in an area accessible only to qualified or authorized persons. Protected from light.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection Tightly fitting safety goggles

Product number	803101	Version 1.2
Product name	Decahydronaphthalene (mixture of cis-and trans isomers) for synthes	sis

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

Flame retardant antistatic protective clothing.

Respiratory protection

Water solubility

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties Physical state liquid Color colorless Odor characteristic Odor Threshold No information available. No information available. pН Melting point -40 °C 372 - 376 °F (189 - 191 °C) Boiling point/boiling range at 1,013 hPa Flash point 135 °F (57 °C) Evaporation rate No information available. Flammability (solid, gas) Not applicable Lower explosion limit 0.7 %(V) Upper explosion limit 4.9 %(V) Vapor pressure 1.3 hPa at 68 °F (20 °C) Relative vapor density 4.2 Density 0.88 g/cm3 at 68 °F (20 °C) Relative density No information available.

0.006 g/l

SAFETY DATA SHEET according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number Product name	803101 Version Decahydronaphthalene (mixture of cis-and trans isomers) for synthesis	1.2
Partition coefficient: n- octanol/water	log Pow: 4.2 (calculated) (Lit.) Potential bioaccumulation	
Autoignition temperature	No information available.	
Decomposition temperature	No information available.	
Viscosity, dynamic	3 mPa.s at 68 °F (20 °C)	
Explosive properties	Not classified as explosive.	
Oxidizing properties	none	
Ignition temperature	491 °F (255 °C) Method: DIN 51794	
Viscosity, kinematic	< 20.5 mm²/s at 77 °F (25 °C)	

SECTION 10. Stability and reactivity

Reactivity

Vapor/air-mixtures are explosive at intense warming.

Chemical stability

Sensitivity to light Reacts with air to form peroxides.

Possibility of hazardous reactions

Violent reactions possible with:

Strong oxidizing agents, Oxygen

Conditions to avoid

Heating. Exposure to light.

Incompatible materials

no information available

Hazardous decomposition products

Peroxides

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure Inhalation, Eye contact, Skin contact

SAFETY DATA SHEET according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	803101	Version 1.2
Product name	Decahydronaphthalene (mixture of cis-and trans isomers) for synthes	sis

Acute oral toxicity LD50 Rat: 4,170 mg/kg (RTECS) Symptoms: If ingested, severe burns of the mouth and throat, as well as a danger of perforation of the esophagus and the stomach.

Acute inhalation toxicity

LC50 Rat: 4.02 mg/l; 4 h (ECHA)

Symptoms: mucosal irritations, Cough, Shortness of breath, Possible damages:, damage of respiratory tract

absorption

Corrosive to respiratory system.

Acute dermal toxicity LD50 Rabbit: 5,192 mg/kg (RTECS)

Skin irritation Rabbit Result: Causes burns. OECD Test Guideline 404

Causes burns.

Eye irritation Causes serious eye damage. Risk of blindness!

Sensitization Sensitization test (Magnusson and Kligman): Result: negative Method: OECD Test Guideline 406

Genotoxicity in vitro Mutagenicity (mammal cell test): Result: negative (Lit.)

Ames test Result: negative (Lit.)

Specific target organ systemic toxicity - single exposure The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Aspiration hazard, Aspiration may cause pulmonary edema and pneumonitis.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or
	equal to 0.1% is identified as probable, possible or confirmed
	human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or

Product number Product name	803101 Decahydronaphthalene (mixture of cis-and trans isomers) for synthesi	Version 1.2 is
	equal to 0.1% is identified as a carcinogen or potential	
	carcinogen by OSHA.	
NTP	No ingredient of this product present at levels greater than or	
	equal to 0.1% is identified as a known or anticipated carcinogen	
	by NTP.	
ACGIH	No ingredient of this product present at levels greater than or	
	equal to 0.1% is identified as a carcinogen or potential	
	carcinogen by ACGIH.	
Further information After absorption: Systemic effects: Dizziness, Headache, Nausea Damage to:	a, Vomiting, Unconsciousness, narcosis, agitation, Convulsions	

Liver, Kidney

_

Other dangerous properties can not be excluded.

This substance should be handled with particular care.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish LC50 Leuciscus idus (Golden orfe): 4.3 mg/l; 48 h DIN 38412 (Lit.) *Toxicity to daphnia and other aquatic invertebrates*

EC50 Daphnia pulex (Water flea): 2.5 mg/l; 48 h (ECOTOX Database)

Toxicity to algae IC50 Desmodesmus subspicatus (green algae): > 2.2 mg/l; 72 h (Lit.)

Persistence and degradability

Biodegradability 3 %; 28 d (Lit.) Not readily biodegradable.

Theoretical oxygen demand (ThOD) 3,362 mg/g (Lit.)

Bioaccumulative potential

Partition coefficient: n-octanol/water log Pow: 4.2 (calculated) (Lit.) Potential bioaccumulation

Mobility in soil

No information available.

Other adverse effects

Product number	803101	Version 1.2
Product name	Decahydronaphthalene (mixture of cis-and trans isomers) for synthe	sis

Henry constant 10740 Pa*m³/mol Method: (experimental) (IUCLID) Distribution preferentially in air.

Additional ecological information Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)	
UN number	UN 1147
Proper shipping name	DECAHYDRONAPHTHALENE
Class	3
Packing group	111
Environmentally hazardous	
Air transport (IATA)	
UN number	UN 1147
Proper shipping name	DECAHYDRONAPHTHALENE
Class	3
Packing group	111
Environmentally hazardous	
Special precautions for user	no
Sea transport (IMDG)	
UN number	UN 1147
Proper shipping name	DECAHYDRONAPHTHALENES
Class	3
Packing group	111
Environmentally hazardous	
Special precautions for user EmS	yes F-E S-D

SECTION 15. Regulatory information United States of America

SARA 313

Product number	803101	Version 1.2
Product name	Decahydronaphthalene (mixture of cis-and trans isomers) for synthesis	

This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311,

Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311,

Table 117.3.

DEA List I Not listed

DEA List II Not listed

US State Regulations

Massachusetts Right To Know

Ingredients Decahydronaphthalene (mixture of cis- and trans isomers)

Pennsylvania Right To Know

Ingredients

Decahydronaphthalene (mixture of cis- and trans isomers)

New Jersey Right To Know

Ingredients Decahydronaphthalene (mixture of cis- and trans isomers)

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status TSCA: All components of the product are listed in the TSCA-inventory. DSL: All components of this product are on the Canadian DSL. KOREA: Not in compliance with the inventory

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Product number	803101	Version 1.2
Product name	Decahydronaphthalene (mixture of cis-and trans isomers) for synthesis	S



Signal Word Danger

Hazard Statements
H226 Flammable liquid and vapor.
H304 May be fatal if swallowed and enters airways.
H314 Causes severe skin burns and eye damage.
H331 Toxic if inhaled.
H411 Toxic to aquatic life with long lasting effects.

Precautionary Statements

Prevention P210 Keep away from heat.

P273 Avoid release to the environment.

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response

P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

P304 + P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P308 + P310 IF exposed or concerned: immediately call a POISON CENTER or doctor/ physician.

Full text of H-Statements referred to under sections 2 and 3.

H226	Flammable liquid and vapor.
H304	May be fatal if swallowed and enters airways.
H314	Causes severe skin burns and eye damage.
H318	Causes serious eye damage.
H331	Toxic if inhaled.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 02/27/2015

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.