ImmunoReagents, Inc.
6003 Chapel Hill Road · Suite # 153 · Raleigh, NC 27607

Product Specifications

VWR Part Number: **IR1328**
ImmunoReagents, Inc. Part Number: DkxSh-003-GFITC

Product: DONKEY X SHEEP IGG FITC 1VL

Concentration: 1.5 mg/ml (E 1% at 280 nm = 13.0)

Amount: 0.5 mg

Conjugate: Fluorescein-5-isothiocyanate (FITC) Amax = 494 nm; Emax = 518 nm

Form: Clear, fluorescent yellow liquid

Purification: Affinity purified using solid phase Sheep IgG

Purity: > 90% based on SDS-PAGE Small amounts of intact IgG may be present.

Host: Donkey

Immunogen: Purified Sheep IgG, whole molecule

Buffer: 10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 1 % (w/v) BSA, Protease/IgG free

Storage: 2-8 °C

Shelf Life: 1 year from date of receipt. Prepare working dilution prior to use and then discard.

Specificity: Based on IEP, this antibody reacts with: · heavy (?) chains on sheep IgG · light chains on all sheep immunoglobulins

Cross Reactivity: Based on IEP, no reactivity is observed to: · non-immunoglobulin sheep serum proteins

Country of Origin: Donkey serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.

Applications: This conjugate is suitable for immunomicroscopy and flow cytometry. The optimal working dilution should be determined by the investigator. Suggested starting dilution(?): · 1:20 - 1:2,000 for most applications

Disclaimer: For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.