

SAFETY DATA SHEET

1. Identification

Product identifier: ARSENIC, 1,000 µg/mL OR 10,00

Other means of identification

Product No.: 6442, 5718, 5704

Recommended use and restriction on use

Recommended use: Not available.

Restrictions on use: Not known.

Manufacturer/Importer/Supplier/Distributor Information

Manufacturer

Company Name: Avantor Performance Materials, Inc.
Address: 3477 Corporate Parkway, Suite 200
Center Valley, PA 18034

Telephone: Customer Service: 855-282-6867

Fax:
Contact Person: Environmental Health & Safety
e-mail: info@avantormaterials.com

Emergency telephone number:

24 Hour Emergency: 908-859-2151

Chemtrec: 800-424-9300

2. Hazard(s) identification

Hazard Classification

Physical Hazards

Corrosive to metals Category 1

Health Hazards

Skin Corrosion/Irritation Category 2

Serious Eye Damage/Eye Irritation Category 2A

Label Elements

Hazard Symbol:



Signal Word: Warning

Hazard Statement: Causes serious eye irritation.
Causes skin irritation.
May be corrosive to metals.

Precautionary Statement

Prevention: Wash hands thoroughly after handling. Wear protective gloves/protective

clothing/eye protection/face protection. Keep only in original container. Do not eat, drink or smoke when using this product.

Response: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention. Absorb spillage to prevent material damage. Take off contaminated clothing and wash it before reuse.

Storage: Store in corrosive resistant container with a resistant inner liner.

Disposal: Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

Other hazards which do not result in GHS classification: None.

3. Composition/information on ingredients

Mixtures

Chemical Identity	Common name and synonyms	CAS number	Content in percent (%)*
NITRIC ACID		7697-37-2	4%
ARSENIC		7440-38-2	0.10 - 1.0%

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

4. First-aid measures

General information: Get medical advice/attention if you feel unwell. Show this safety data sheet to the doctor in attendance.

Ingestion: Rinse mouth thoroughly. Call a POISON CENTER or doctor/physician if you feel unwell.

Inhalation: Move to fresh air. Get medical attention if symptoms persist.

Skin Contact: Wash skin thoroughly with soap and water. Get medical attention if irritation persists after washing. Wash contaminated clothing before reuse.

Eye contact: Flush thoroughly with water. If irritation occurs, get medical assistance.

Most important symptoms/effects, acute and delayed

Symptoms: Irritating to eyes, respiratory system and skin.

Indication of immediate medical attention and special treatment needed

Treatment: Treat symptomatically. Symptoms may be delayed.

5. Fire-fighting measures

General Fire Hazards: In case of fire and/or explosion do not breathe fumes.

Suitable (and unsuitable) extinguishing media

Suitable extinguishing media: Use fire-extinguishing media appropriate for surrounding materials.

Unsuitable extinguishing media: None.

Specific hazards arising from the chemical: During fire, gases hazardous to health may be formed.

Special protective equipment and precautions for firefighters

Special fire fighting procedures: Move containers from fire area if you can do so without risk. Use water spray to keep fire-exposed containers cool. Cool containers exposed to flames with water until well after the fire is out.

Special protective equipment for fire-fighters: Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures: Keep unauthorized personnel away. Use personal protective equipment. See Section 8 of the MSDS for Personal Protective Equipment.

Methods and material for containment and cleaning up: Absorb spill with vermiculite or other inert material, then place in a container for chemical waste. Clean surface thoroughly to remove residual contamination.

Notification Procedures: Inform authorities if large amounts are involved. Prevent runoff from entering drains, sewers, or streams.

Environmental Precautions: Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling: Use personal protective equipment as required. Avoid breathing mist or vapor. Wash hands thoroughly after handling. Avoid contact with eyes, skin, and clothing. Do not taste or swallow. Wear protective gloves/protective clothing/eye protection/face protection. Wash contaminated clothing before reuse.

Conditions for safe storage, including any incompatibilities: Store in corrosive resistant container with a resistant inner liner. Store in a cool, dry place. Store in a well-ventilated place.

8. Exposure controls/personal protection

Control Parameters

Occupational Exposure Limits

Chemical Identity	Type	Exposure Limit Values	Source
NITRIC ACID	STEL	4 ppm	US. ACGIH Threshold Limit Values (2011)
	TWA	2 ppm	US. ACGIH Threshold Limit Values (2011)
	STEL	4 ppm 10 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2010)
	REL	2 ppm 5 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2010)
	PEL	2 ppm 5 mg/m3	US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000) (02 2006)
	STEL	4 ppm 10 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)
	TWA	2 ppm 5 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)

Biological Limit Values

Chemical Identity	Exposure Limit Values	Source
ARSENIC (Inorganic arsenic, plus methylated metabolites, as As: Sampling time: End of work week.)	35 µg/l (Urine)	ACGIH BEL (03 2013)

Appropriate Engineering Controls

No data available.

Individual protection measures, such as personal protective equipment

General information: Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Eye/face protection: Use eye protection.

Skin Protection

Hand Protection: Wear protective gloves.

Other: Wear suitable protective clothing.

Respiratory Protection: In case of inadequate ventilation use suitable respirator.

Hygiene measures: Provide eyewash station and safety shower. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing to remove contaminants. Discard contaminated footwear that cannot be cleaned.

9. Physical and chemical properties

Appearance

Physical state: Liquid
Form: No data available.
Color: Colorless
Odor: Odorless
Odor threshold: No data available.
pH: No data available.

Melting point/freezing point:	No data available.
Initial boiling point and boiling range:	No data available.
Flash Point:	No data available.
Evaporation rate:	No data available.
Flammability (solid, gas):	No data available.
Upper/lower limit on flammability or explosive limits	
Flammability limit - upper (%):	No data available.
Flammability limit - lower (%):	No data available.
Explosive limit - upper (%):	No data available.
Explosive limit - lower (%):	No data available.
Vapor pressure:	No data available.
Vapor density:	No data available.
Relative density:	No data available.
Solubility(ies)	
Solubility in water:	Completely Soluble
Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	No data available.
Auto-ignition temperature:	No data available.
Decomposition temperature:	No data available.
Viscosity:	No data available.

10. Stability and reactivity

Reactivity:	No dangerous reaction known under conditions of normal use.
Chemical Stability:	Material is stable under normal conditions.
Possibility of Hazardous Reactions:	Hazardous polymerization does not occur.
Conditions to Avoid:	Heat, sparks, flames. Contact with incompatible materials.
Incompatible Materials:	Strong oxidizing agents. Bases. Powdered metal. Carbonates. Sulfur oxides. Organic peroxides/hydroperoxides.
Hazardous Decomposition Products:	By heating and fire, toxic vapors/gases may be formed. Nitrogen Oxides

11. Toxicological information

Information on likely routes of exposure

Ingestion:	May cause irritation of the gastrointestinal tract.
Inhalation:	May be harmful if inhaled.
Skin Contact:	Causes skin irritation.
Eye contact:	Causes serious eye irritation.

Information on toxicological effects

Acute toxicity (list all possible routes of exposure)

Oral Product:	No data available.
----------------------	--------------------

Specified substance(s):

ARSENIC
LD 50 (Rat): 763 mg/kg
LD 50 (Mouse): 145 mg/kg

Dermal

Product: No data available.

Inhalation

Product: No data available.

Specified substance(s):

NITRIC ACID
LC 50 (Rat, 1 h): 7 mg/l
LC 50 (Rat, 4 h): 65 ppm
LC 50 (Mouse, 4 h): 67 ppm

Repeated Dose Toxicity

Product: No data available.

Skin Corrosion/Irritation

Product: Causes skin irritation.

Serious Eye Damage/Eye Irritation

Product: Causes serious eye irritation.

Respiratory or Skin Sensitization

Product: Not a skin sensitizer.

Carcinogenicity

Product: This substance has no evidence of carcinogenic properties.

IARC Monographs on the Evaluation of Carcinogenic Risks to Humans:

No carcinogenic components identified

US. National Toxicology Program (NTP) Report on Carcinogens:

No carcinogenic components identified

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050):

No carcinogenic components identified

Germ Cell Mutagenicity

In vitro

Product: No mutagenic components identified

In vivo

Product: No mutagenic components identified

Reproductive Toxicity

Product: No components toxic to reproduction

Specific Target Organ Toxicity - Single Exposure

Product: No data available.

Specific Target Organ Toxicity - Repeated Exposure

Product: No data available.

Aspiration Hazard

Product: Not classified

Other Effects: None known.

12. Ecological information

Ecotoxicity:

Acute hazards to the aquatic environment:

Fish

Product: No data available.

Specified substance(s):

NITRIC ACID LC 50 (Starfish (*Asterias rubens*), 48 h): 100 - 330 mg/l Mortality

Aquatic Invertebrates

Product: No data available.

Specified substance(s):

NITRIC ACID LC 50 (Cockle (*Cerastoderma edule*), 48 h): 330 - 1,000 mg/l Mortality
LC 50 (Green or European shore crab (*Carcinus maenas*), 48 h): 180 mg/l Mortality

Chronic hazards to the aquatic environment:

Fish

Product: No data available.

Aquatic Invertebrates

Product: No data available.

Toxicity to Aquatic Plants

Product: No data available.

Persistence and Degradability

Biodegradation

Product: There are no data on the degradability of this product.

BOD/COD Ratio

Product: No data available.

Bioaccumulative Potential

Bioconcentration Factor (BCF)

Product: No data available on bioaccumulation.

Partition Coefficient n-octanol / water (log Kow)

Product: No data available.

Mobility in Soil: The product is water soluble and may spread in water systems.

Other Adverse Effects: Low acute toxicity to aquatic organisms.

13. Disposal considerations

Disposal instructions: Discharge, treatment, or disposal may be subject to national, state, or local laws. Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

Contaminated Packaging: Since emptied containers retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

UN Number:	UN 3264
UN Proper Shipping Name:	Corrosive liquid, acidic, inorganic, n.o.s.(NITRIC ACID)
Transport Hazard Class(es)	
Class(es):	8
Label(s):	8
Packing Group:	III
Marine Pollutant:	No

IMDG

UN Number:	UN 3264
UN Proper Shipping Name:	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S.(NITRIC ACID)
Transport Hazard Class(es)	
Class(es):	8
Label(s):	8
EmS No.:	F-A, S-B
Packing Group:	III
Marine Pollutant:	No

IATA

UN Number:	UN 3264
Proper Shipping Name:	Corrosive liquid, acidic, inorganic, n.o.s.(NITRIC ACID)
Transport Hazard Class(es):	
Class(es):	8
Label(s):	8
Marine Pollutant:	No
Packing Group:	III

15. Regulatory information

US Federal Regulations

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

None present or none present in regulated quantities.

CERCLA Hazardous Substance List (40 CFR 302.4):

NITRIC ACID Reportable quantity: 1000 lbs.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories

☒ Acute (Immediate) ☒ Chronic (Delayed) ☐ Fire ☐ Reactive ☐ Pressure Generating

SARA 302 Extremely Hazardous Substance

Chemical Identity	RQ	Threshold Planning Quantity
NITRIC ACID	1000 lbs.	1000 lbs.

SARA 304 Emergency Release Notification

Chemical Identity	RQ
NITRIC ACID	1000 lbs.

SARA 311/312 Hazardous Chemical

Chemical Identity	Threshold Planning Quantity
NITRIC ACID	500lbs

SARA 313 (TRI Reporting)

Chemical Identity	Reporting threshold for other users	Reporting threshold for manufacturing and processing
NITRIC ACID	10000 lbs	25000 lbs.

Clean Water Act Section 311 Hazardous Substances (40 CFR 117.3)

NITRIC ACID	Reportable quantity: 1000 lbs.
-------------	--------------------------------

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130):

NITRIC ACID	Threshold quantity: 15000 lbs
-------------	-------------------------------

US State Regulations

US. California Proposition 65

No ingredient regulated by CA Prop 65 present.

US. New Jersey Worker and Community Right-to-Know Act

NITRIC ACID	Listed
-------------	--------

US. Massachusetts RTK - Substance List

NITRIC ACID	Listed
-------------	--------

US. Pennsylvania RTK - Hazardous Substances

NITRIC ACID	Listed
-------------	--------

US. Rhode Island RTK


NITRIC ACID	Listed
-------------	--------

Inventory Status:

Australia AICS:	On or in compliance with the inventory
Canada DSL Inventory List:	On or in compliance with the inventory
EINECS, ELINCS or NLP:	On or in compliance with the inventory
Japan (ENCS) List:	Not in compliance with the inventory.
China Inv. Existing Chemical Substances:	On or in compliance with the inventory
Korea Existing Chemicals Inv. (KECI):	On or in compliance with the inventory
Canada NDSL Inventory:	Not in compliance with the inventory.
Philippines PICCS:	On or in compliance with the inventory
US TSCA Inventory:	On or in compliance with the inventory
New Zealand Inventory of Chemicals:	Not in compliance with the inventory.
Japan ISHL Listing:	Not in compliance with the inventory.
Japan Pharmacopoeia Listing:	Not in compliance with the inventory.

16. Other information, including date of preparation or last revision

NFPA Hazard ID



Red	Flammability
Blue	Health
Yellow	Reactivity
White	Special hazard.

Hazard rating: 0 - Minimal; 1 - Slight; 2 - Moderate; 3 - Serious; 4 - Severe

SDS_US - SDSMIX000907

Issue Date: 12-16-2014

Revision Date: No data available.

Version #: 1.0

Further Information: No data available.

Disclaimer: THE INFORMATION PRESENTED IN THIS MATERIAL SAFETY DATA SHEET (MSDS/SDS) WAS PREPARED BY TECHNICAL PERSONNEL BASED ON DATA THAT THEY BELIEVE IN THEIR GOOD FAITH JUDGMENT IS ACCURATE. HOWEVER, THE INFORMATION PROVIDED HEREIN IS PROVIDED "AS IS," AND AVANTOR PERFORMANCE MATERIALS MAKES AND GIVES NO REPRESENTATIONS OR WARRANTIES WHATSOEVER, AND EXPRESSLY DISCLAIMS ALL WARRANTIES REGARDING SUCH INFORMATION AND THE PRODUCT TO WHICH IT RELATES, WHETHER EXPRESS, IMPLIED, OR STATUTORY, INCLUDING WITHOUT LIMITATION<(>,<)> WARRANTIES OF ACCURACY, COMPLETENESS, MERCHANTABILITY, NON-INFRINGEMENT, PERFORMANCE, SAFETY, SUITABILITY, STABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, AND ANY WARRANTIES ARISING FROM COURSE OF DEALING, COURSE OF PERFORMANCE, OR USAGE OF TRADE. THIS MSDS/SDS IS INTENDED ONLY AS A GUIDE TO THE APPROPRIATE PRECAUTIONARY HANDLING OF THE MATERIAL BY A PROPERLY TRAINED PERSON USING THIS PRODUCT, AND IS NOT INTENDED TO BE COMPREHENSIVE AS TO THE MANNER AND CONDITIONS OF USE, HANDLING, STORAGE, OR DISPOSAL OF THE PRODUCT. INDIVIDUALS RECEIVING THIS MSDS/SDS MUST ALWAYS EXERCISE THEIR OWN INDEPENDENT JUDGMENT IN DETERMINING THE APPROPRIATENESS OF SUCH ISSUES. ACCORDINGLY, AVANTOR PERFORMANCE MATERIALS ASSUMES NO LIABILITY WHATSOEVER FOR THE USE OF OR RELIANCE UPON THIS INFORMATION. NO SUGGESTIONS FOR USE ARE INTENDED AS, AND NOTHING HEREIN SHALL BE CONSTRUED AS, A RECOMMENDATION TO INFRINGE ANY EXISTING PATENTS OR TO VIOLATE ANY FEDERAL, STATE, LOCAL, OR FOREIGN LAWS. AVANTOR PERFORMANCE MATERIALS REMINDS YOU THAT IT IS YOUR LEGAL DUTY TO MAKE ALL INFORMATION IN THIS MSDS/SDS AVAILABLE TO YOUR EMPLOYEES.