

Safety Data Sheet
according to OSHA HCS

Printing date 02/07/2016

Reviewed on 07/23/2015

1 Identification

- **Product name**
- **Trade name:** Hafnium powder (99.6%, Zr-3.1%)
- **Item number:** 93-7225
- **CAS Number:**
7440-58-6
- **EC number:**
231-166-4
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Strem Chemicals, Inc.
7 Mulliken Way
NEWBURYPORT, MA 01950
USA
info@strem.com
- **Information department:** Technical Department
- **Emergency telephone number:**
EMERGENCY: CHEMTREC: + 1 (800) 424-9300
During normal opening times: +1 (978) 499-1600

2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS02 Flame

Flam. Sol. 1 H228 Flammable solid.

Self-heat. 1 H251 Self-heating: may catch fire.



GHS08 Health hazard

STOT RE 2 H373 May cause damage to organs through prolonged or repeated exposure.



GHS07

Acute Tox. 4 H302 Harmful if swallowed.

Acute Tox. 4 H312 Harmful in contact with skin.

Acute Tox. 4 H332 Harmful if inhaled.

- **Label elements**

- **GHS label elements**

The substance is classified and labeled according to the Globally Harmonized System (GHS).

- **Hazard pictograms**



GHS02



GHS07



GHS08

- **Signal word** *Danger*

(Contd. on page 2)

US

Safety Data Sheet according to OSHA HCS

Printing date 02/07/2016

Reviewed on 07/23/2015

Trade name: Hafnium powder (99.6%, Zr-3.1%)

(Contd. of page 1)

· **Hazard statements**

- H228 *Flammable solid.*
- H251 *Self-heating: may catch fire.*
- H302+H312+H332 *Harmful if swallowed, in contact with skin or if inhaled.*
- H373 *May cause damage to organs through prolonged or repeated exposure.*

· **Precautionary statements**

- P231 *Handle under inert gas.*
- P301+P310 *IF SWALLOWED: Immediately call a POISON CENTER/ doctor.*
- P305+P351+P338 *If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.*
- P403+P233 *Store in a well-ventilated place. Keep container tightly closed.*
- P422 *Store contents under inert gas.*
- P501 *Dispose of contents/container in accordance with local/regional/national/international regulations.*

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



· **HMIS-ratings (scale 0 - 4)**

HEALTH	2	Health = 2
FIRE	0	Fire = 0
REACTIVITY	0	Reactivity = 0

· **Other hazards**

· **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

3 Composition/information on ingredients

· **Chemical characterization: Substances**

· **CAS No. Description**

7440-58-6 Hafnium powder (99.6%, Zr-3.1%)

· **Identification number(s)**

· **EC number:** 231-166-4

· **Dangerous components:** not applicable

4 First-aid measures

· **Description of first aid measures**

· **General information:**

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

· **After inhalation:**

Supply fresh air. If required, provide artificial respiration. Keep patient warm. Consult doctor if symptoms persist.

In case of unconsciousness place patient stably in side position for transportation.

· **After skin contact:** Immediately rinse with water.

· **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.

(Contd. on page 3)

Safety Data Sheet according to OSHA HCS

Printing date 02/07/2016

Reviewed on 07/23/2015

Trade name: *Hafnium powder (99.6%, Zr-3.1%)*

(Contd. of page 2)

- **After swallowing:** *Immediately call a doctor.*
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** *No further relevant information available.*
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** *Special powder for metal fires. Do not use water.*
- **For safety reasons unsuitable extinguishing agents:** *Water*
- **Special hazards arising from the substance or mixture**
During heating or in case of fire poisonous gases are produced.
- **Advice for firefighters**
- **Protective equipment:** *Mouth respiratory protective device.*

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**
Mount respiratory protective device.
Wear protective equipment. Keep unprotected persons away.
- **Environmental precautions:** *No special measures required.*
- **Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
Do not flush with water or aqueous cleansing agents
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

7 Handling and storage

- **Handling:**
- **Precautions for safe handling**
Thorough dedusting.
Ensure good ventilation/exhaustion at the workplace.
Open and handle receptacle with care.
- **Information about protection against explosions and fires:**
Keep ignition sources away - Do not smoke.
Protect against electrostatic charges.
Keep respiratory protective device available.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** *No special requirements.*
- **Information about storage in one common storage facility:** *Not required.*
- **Further information about storage conditions:** *Keep receptacle tightly sealed.*
- **Specific end use(s)** *No further relevant information available.*

US

(Contd. on page 4)

Safety Data Sheet according to OSHA HCS

Printing date 02/07/2016

Reviewed on 07/23/2015

Trade name: Hafnium powder (99.6%, Zr-3.1%)

(Contd. of page 3)

8 Exposure controls/personal protection

· **Additional information about design of technical systems:** No further data; see item 7.

· **Control parameters**

· **Components with limit values that require monitoring at the workplace:**

7440-58-6 Hafnium powder (99.6%, Zr-3.1%)

PEL Long-term value: 0.5 mg/m³
as Hf

REL Long-term value: 0.5 mg/m³
as Hf

TLV Long-term value: 0.5 mg/m³
as Hf

· **Additional information:** The lists that were valid during the creation were used as basis.

· **Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Wash hands before breaks and at the end of work.

Store protective clothing separately.

Avoid contact with the eyes and skin.

· **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

(Contd. on page 5)

Safety Data Sheet according to OSHA HCS

Printing date 02/07/2016

Reviewed on 07/23/2015

Trade name: Hafnium powder (99.6%, Zr-3.1%)

(Contd. of page 4)

9 Physical and chemical properties

· Information on basic physical and chemical properties	
· General Information	
· Appearance:	
Form:	Powder
Color:	Grey
· Odor:	Odorless
· Odor threshold:	Not determined.
· pH-value:	Not applicable.
· Change in condition	
Melting point/Melting range:	2227 °C (4041 °F)
Boiling point/Boiling range:	4602 °C (8316 °F)
· Flash point:	Not applicable.
· Flammability (solid, gaseous):	Product is not flammable.
· Ignition temperature:	
Decomposition temperature:	Not determined.
· Auto igniting:	Not determined.
· Danger of explosion:	Not determined.
· Explosion limits:	
Lower:	Not determined.
Upper:	Not determined.
· Vapor pressure at 20 °C (68 °F):	no data hPa
· Density at 20 °C (68 °F):	13.31 g/cm ³ (111.072 lbs/gal)
· Relative density	Not determined.
· Vapor density	Not applicable.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with	
Water:	Insoluble.
· Partition coefficient (n-octanol/water):	
Not determined.	
· Viscosity:	
Dynamic:	Not applicable.
Kinematic:	Not applicable.
· Solvent content:	
Organic solvents:	0.0 %
VOC content:	0.0 g/l / 0.00 lb/gal
Solids content:	100.0 %
· Other information	No further relevant information available.

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.

(Contd. on page 6)

Printing date 02/07/2016

Reviewed on 07/23/2015

Trade name: *Hafnium powder (99.6%, Zr-3.1%)*

(Contd. of page 5)

- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**

- **Carcinogenic categories**

- **IARC (International Agency for Research on Cancer)**

Substance is not listed.

- **NTP (National Toxicology Program)**

Substance is not listed.

- **OSHA-Ca (Occupational Safety & Health Administration)**

Substance is not listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:** Not known to be hazardous to water.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

US

(Contd. on page 7)

Safety Data Sheet
according to OSHA HCS

Printing date 02/07/2016

Reviewed on 07/23/2015

Trade name: Hafnium powder (99.6%, Zr-3.1%)

(Contd. of page 6)

14 Transport information

· **UN-Number**

· **DOT, IMDG, IATA**

UN2545

· **UN proper shipping name**

· **DOT, IATA**

· **IMDG**

Hafnium powder, dry

HAFNIUM POWDER, DRY

· **Transport hazard class(es)**

· **DOT**



· **Class**

4.2 Substances liable to spontaneous combustion

· **Label**

4.2

· **IMDG**



· **Class**

4

· **Label**

4.2

· **IATA**



· **Class**

4.2 Substances liable to spontaneous combustion

· **Label**

4.2

· **Packing group**

· **DOT, IMDG, IATA**

II

· **Environmental hazards:**

· **Marine pollutant:**

No

· **Special precautions for user**

Not applicable.

· **EMS Number:**

F-G,S-M

· **Segregation groups**

Powdered metals

· **Stowage Category**

D

· **Handling Code**

H1 Keep as dry as reasonably practicable

· **Segregation Code**

SG26 In addition: from goods of classes 2.1 and 3 when stowed on deck of a containership a minimum distance of two container spaces athwartship shall be maintained, when stowed on ro-ro ships a distance of 6 m athwartship shall be maintained.

· **Transport in bulk according to Annex II of**

MARPOL73/78 and the IBC Code

Not applicable.

(Contd. on page 8)

Safety Data Sheet
according to OSHA HCS

Printing date 02/07/2016

Reviewed on 07/23/2015

Trade name: *Hafnium powder (99.6%, Zr-3.1%)*

(Contd. of page 7)

· **Transport/Additional information:**

· **DOT**

· **Quantity limitations**

On passenger aircraft/rail: 15 kg

On cargo aircraft only: 50 kg

· **UN "Model Regulation":**

UN 2545 HAFNIUM POWDER, DRY, 4.2, II

15 Regulatory information

· **Safety, health and environmental regulations/legislation specific for the substance or mixture**

· **Sara**

· **Section 355 (extremely hazardous substances):**

Substance is not listed.

· **Section 313 (Specific toxic chemical listings):**

Substance is not listed.

· **TSCA (Toxic Substances Control Act):**

Substance is listed.

· **Proposition 65**

· **Chemicals known to cause cancer:**

Substance is not listed.

· **Chemicals known to cause reproductive toxicity for females:**

Substance is not listed.

· **Chemicals known to cause reproductive toxicity for males:**

Substance is not listed.

· **Chemicals known to cause developmental toxicity:**

Substance is not listed.

· **Carcinogenic categories**

· **EPA (Environmental Protection Agency)**

Substance is not listed.

· **TLV (Threshold Limit Value established by ACGIH)**

Substance is not listed.

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

Substance is not listed.

· **GHS label elements**

The substance is classified and labeled according to the Globally Harmonized System (GHS).

· **Hazard pictograms**



GHS02

GHS07

GHS08

· **Signal word** *Danger*

· **Hazard statements**

H228

Flammable solid.

H251

Self-heating: may catch fire.

(Contd. on page 9)

Safety Data Sheet according to OSHA HCS

Printing date 02/07/2016

Reviewed on 07/23/2015

Trade name: Hafnium powder (99.6%, Zr-3.1%)

(Contd. of page 8)

H302+H312+H332 Harmful if swallowed, in contact with skin or if inhaled.

H373 May cause damage to organs through prolonged or repeated exposure.

· Precautionary statements

P231 Handle under inert gas.

P301+P310 IF SWALLOWED: Immediately call a POISON CENTER/ doctor.

P305+P351+P338 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P403+P233 Store in a well-ventilated place. Keep container tightly closed.

P422 Store contents under inert gas.

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

· Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Department issuing SDS: Technical Department.

· Contact: Technical Director

· Date of preparation / last revision 02/07/2016 / -

· Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit

Flam. Sol. 1: Flammable solids, Hazard Category 1

Self-heat. 1: Self-Heating Substances and Mixtures, Hazard Category 1

Acute Tox. 4: Acute toxicity, Hazard Category 4

STOT RE 2: Specific target organ toxicity - Repeated exposure, Hazard Category 2