

The following list contains the Material Safety Data Sheets you requested. Please scroll down to view the requested MSDS(s).

Product	MSDS	Distributor	Format	Language	Quantity
2122326	N/A	Hach Company	ROWGHS	English	1

Total Enclosures: 1

World Headquarters
Hach Company
P.O.Box 389
Loveland, CO USA 80539
(970) 669-3050

MSDS No: M00379

SAFETY DATA SHEET

1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

Product Name: Alkaline Cyanide Reagent

Catalog Number: 2122326

Hach Company
P.O.Box 389
Loveland, CO USA 80539
(970) 669-3050

Emergency Telephone Numbers:
(Medical and Transportation)
(303) 623-5716 24 Hour Service
(515)232-2533 8am - 4pm CST

MSDS Number: M00379

Chemical Name: Not applicable

CAS Number: Not applicable

Additional CAS No. (for hydrated forms): Not applicable

Chemical Formula: Not applicable

Chemical Family: Not applicable

Intended Use: Laboratory Reagent Determination of manganese

2. HAZARDS IDENTIFICATION

GHS Classification:

Hazard categories: Acute Toxicity: Acute Tox. 3-Orl Acute Toxicity: Acute Tox. 2-Derm Acute Toxicity: Acute Tox. 3-Inh Skin Corrosion/Irritation: Skin Corr. 1A Hazardous to the Aquatic Environment: Aquatic Chronic 1

GHS Label Elements:

DANGER



Hazard statements: Toxic if swallowed. Fatal in contact with skin. Toxic if inhaled. Causes severe skin burns and eye damage. Very toxic to aquatic life with long lasting effects.

Contact with acids liberates very toxic gas.

Precautionary statements: Do not breathe dust/fume/gas/mist/vapours/spray. Use only outdoors or in a well-ventilated area. Do not get in eyes, on skin, or on clothing. Do not eat, drink or smoke when using this product. Wear protective gloves / protective clothing / eye protection / face protection. IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. IF INHALED: Remove victim/person to fresh air and keep at rest in a position comfortable for breathing. IF SWALLOWED: rinse mouth. Do NOT induce vomiting. Immediately call a POISON CENTER or doctor/physician.

HMIS:

Health: 3

Flammability: 0

Reactivity: 0

Protective Equipment: X - See protective equipment, Section 8.

NFPA:

Health: 3

Flammability: 0

Reactivity: 0

Symbol: Not applicable

WHMIS Hazard Classification: Class E - Corrosive material Class D, Division 1, Subdivision B - Toxic material (immediate effects)

WHMIS Symbols: Corrosive Acute Poison

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Components according to GHS:

Sodium Cyanide

CAS Number: 143-33-9

Chemical Formula: NaCN

GHS Classification: Acute Tox. 1 –Orl, H300; Acute Tox. 1 – Derm, H310; Acute Tox. 2 - Inh, H330; Aquatic acute 1, H400; Aquatic Chronic 1, H410; EUH032

Percent Range (Trade Secret): 5.0 - 15.0

Percent Range Units: weight / weight

PEL: 5 mg/m³ (skin)

TLV: 5 mg/m³ (skin)

WHMIS Symbols: Acute Poison

Sodium Hydroxide

CAS Number: 1310-73-2

Chemical Formula: NaOH

GHS Classification: Met. Corr.1, H290; Skin Corr. 1A, H314; Aquatic Acute 3, H402

Percent Range (Trade Secret): 1.0 - 5.0

Percent Range Units: weight / weight

PEL: 2 mg/m³

TLV: Not established

WHMIS Symbols: Acute Poison Corrosive

Hazardous Components according to GHS: No

Demineralized Water

CAS Number: 7732-18-5

Chemical Formula: H₂O

GHS Classification: Not a dangerous substance according to GHS.

Percent Range (Trade Secret): > 90.0

Percent Range Units: weight / weight

PEL: Not established

TLV: Not established

WHMIS Symbols: Not applicable

4. FIRST AID MEASURES

General Information: In the event of exposure, show this Material Safety Data Sheet and label (where possible) to a doctor. Have a cyanide first aid kit available. Emergency response to cyanide exposure should be planned and practiced prior to work with cyanides. First responders should start treatment and get medical attention immediately.

Advice to doctor: Break an amyl nitrite pearl in cloth and hold lightly under nose for 15 seconds. Repeat 5 times at 15 second intervals. Transport to hospital immediately. If patient has not responded to amyl nitrite, inject intravenously 10 mL of a 3% solution of sodium nitrite at a rate not greater than 2.5 - 5 mL/min. Follow directly with 50 mL of a 25 % solution of sodium thiosulfate at the same rate by the same route. Keep patient under observation. If signs of poisoning persist or reappear, repeat nitrite and thiosulfate injections 1 hour later in one-half the original doses.

Emergency response to cyanide exposure should be planned and practiced prior to work with cyanides. First responders should start treatment and get medical attention immediately. Antidote: break an amyl nitrite pearl in cloth and hold lightly under nose for 15 seconds. Repeat 5 times at 15 second intervals. Transport to hospital immediately. Note to Physician: Have a cyanide first aid kit available. If patient has not responded to amyl nitrite, inject intravenously 10 mL of a 3% solution of sodium nitrite at a rate not greater than 2.5 - 5 mL/min. Follow directly with 50 mL of a 25 % solution of sodium thiosulfate at the same rate by the same route. Keep patient under observation. If signs of poisoning persist or reappear, repeat nitrite and thiosulfate injections 1 hour later in one-half the original doses.

Eye Contact: Immediately flush eyes with water for 15 minutes. Call physician.

Skin Contact (First Aid): Remove contaminated clothing. Wash skin with plenty of water for 15 minutes. Call physician immediately.

Inhalation: Remove to fresh air. Call physician.

Ingestion (First Aid): Never give anything by mouth to an unconscious person. Call physician immediately.

5. FIRE FIGHTING MEASURES

Flammable Properties: During a fire, irritating and highly toxic gases may be generated by thermal decomposition.

Fire Fighting Instruction: As in any fire, wear self-contained breathing apparatus pressure-demand and full protective gear.

Extinguishing Media: Use media appropriate to surrounding fire conditions

Extinguishing Media NOT To Be Used: Not applicable

Fire / Explosion Hazards: May react violently with: strong acids

Hazardous Combustion Products: Toxic fumes of: cyanide compounds sodium monoxide

6. ACCIDENTAL RELEASE MEASURES

Spill Response Notice:

Only persons properly qualified to respond to an emergency involving hazardous substances may respond to a spill according to federal regulations (OSHA 29 CFR 1910.120(a)(v)) and per your company's emergency response plan and guidelines/procedures. See Section 13, Special Instructions for disposal assistance. Outside of the US, only persons properly qualified according to state or local regulations should respond to a spill involving chemicals.

Containment Technique: Releases of this material may contaminate the environment. Stop spilled material from being released to the environment. Absorb spilled liquid with non-reactive sorbent material.

Clean-up Technique: If permitted by regulation, Cover spilled material with an alkali, such as soda ash or sodium bicarbonate. Carefully mist spill with bleach until saturated. Scoop up slurry into a large beaker. Oxidize spilled material with a 50% excess of bleach containing at least 5% sodium hypochlorite. Allow to react for 24 hours in a fume hood. Flush reacted material to the drain with a large excess of water. Decontaminate area with bleach solution. Otherwise, Pick up spill for disposal and place in a closed container. Dispose of in accordance with local, state and federal regulations or laws.

Evacuation Procedure: Evacuate general area (50 foot radius or as directed by your facility's emergency response plan) when: any quantity is spilled. Deny access to unnecessary and unprotected personnel. If conditions warrant, increase the size of the evacuation.

DOT Emergency Response Guide Number: 154

7. HANDLING AND STORAGE

Handling: Avoid contact with eyes skin clothing Do not breathe mist or vapors. Wash thoroughly after handling. Maintain general industrial hygiene practices when using this product.

Storage: Keep away from: acids / acid fumes. Protect from: heat freezing

Flammability Class: Not applicable

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Engineering Controls: Use a fume hood to avoid exposure to dust, mist or vapor. Maintain general industrial hygiene practices when using this product.

Personal Protective Equipment:

Eye Protection: chemical splash goggles

Skin Protection: neoprene latex gloves In the EU, the selected gloves must satisfy the specifications of EU Directive 89/686/EEC and standard EN 374 derived from it. lab coat

Inhalation Protection: laboratory fume hood

Precautionary Measures: Avoid contact with: eyes skin clothing Do not breathe: mist/vapor Wash thoroughly after handling. Keep away from: acids/acid fumes Protect from: heat freezing

TLV: Cyanide 5 mg/m³ (skin)

PEL: Cyanide 5 mg/m³ (skin)

For Occupational Exposure Limits (OEL) for ingredients, see section 3 - Composition/Information on Ingredients.:

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance: Clear, colorless liquid

Physical State: Liquid
Molecular Weight: Not applicable
Odor: None
Odor Threshold: Odorless
pH: 12.3
Metal Corrosivity:
Corrosivity Classification: Not classified as corrosive to metals according to GHS criteria.
Steel: Not determined
Aluminum: Not determined
Specific Gravity/ Relative Density (water = 1; air =1): 1.112
Viscosity: Not determined
Solubility:
Water: Miscible
Acid: Produces HCN
Other: Not determined
Partition Coefficient (n-octanol / water): Not applicable
Coefficient of Water / Oil: Not applicable
Melting Point: Not available
Decomposition Temperature: Not determined
Boiling Point: 92 C
Vapor Pressure: Not available
Vapor Density (air = 1): Not available
Evaporation Rate (water = 1): 0.57
Volatile Organic Compounds Content: Not applicable
Flammable Properties: During a fire, irritating and highly toxic gases may be generated by thermal decomposition.
Flash Point: Not applicable
Method: Not applicable
Flammability Limits:
Lower Explosion Limits: Not applicable
Upper Explosion Limits: Not applicable
Autoignition Temperature: Not available
Explosive Properties:
Not classified according to GHS criteria.
Oxidizing Properties:
Not classified according to GHS criteria.
Reactivity Properties:
Not classified as self-reactive, pyrophoric, self-heating or emitting flammable gases in contact with water according to GHS criteria.
Gas under Pressure:
Not classified according to GHS criteria.
Not determined

10. STABILITY AND REACTIVITY

Chemical Stability: Stable when stored under proper conditions.
Mechanical Impact: None reported
Static Discharge: None reported.
Reactivity / Incompatibility: Incompatible with: acids
Hazardous Decomposition: Contact with acids/acid fumes releases toxic cyanide gas.
Conditions to Avoid: Extreme temperatures

11. TOXICOLOGICAL INFORMATION

Toxicokinetics, Metabolism and Distribution: No information available for mixture.
Toxicologically Synergistic Products: None reported
Acute Toxicity: Toxicological Testing and/or Acute Toxicity Estimate (ATE) - Calculated from Ingredient Toxicity Data
Testing data Oral Rat LD50 = 69 mg/kg; ATE oral LD50 = 64 mg/kg
Testing data Dermal rabbit LD50 Between 200 mg/kg and 500 mg/kg; ATE dermal LD50 = 103 mg/kg;
ATE inhalation Rat LC50 = 2.4 mg/l
Specific Target Organ Toxicity - Single Exposure (STOT-SE): Based on classification principles, the classification criteria are not met.

Specific Target Organ Toxicity - Repeat Exposure (STOT-RE): Based on classification principles, the classification criteria are not met.

Skin Corrosion/Irritation: Corrosive to skin.

Testing data: 1 Hour exposure - Severe erythema 1 hour after exposure. Slight edema 1 hour after exposure. Moderate eschar with pale areas 1 hour after exposure.

Eye Damage: Corrosive to eyes.

Sensitization: Based on classification principles, the classification criteria are not met.

CMR Effects/Properties (carcinogenic, mutagenic or toxic to reproduction): No germ cell mutagenicity, carcinogenicity or reproductive toxicity data found.

This product does NOT contain any IARC listed chemicals.

This product does NOT contain any NTP listed chemicals.

This product does NOT contain any OSHA listed carcinogens.

Symptoms/Effects:

Ingestion: Toxic May be rapidly fatal. Causes: cyanosis (a reduction of the blood's ability to carry oxygen, giving a bluish discoloration) burns of the mouth and esophagus May cause: anxiety headache confusion irregular heartbeat convulsions coma death

Inhalation: Toxic Effects similar to those of ingestion.

Skin Absorption: Toxic Will be absorbed through the skin. Effects similar to those of ingestion

Chronic Effects: Chronic overexposure may cause central nervous system effects irritation skin irritation

Medical Conditions Aggravated: Pre-existing: Skin conditions

12. ECOLOGICAL INFORMATION

Product Ecological Information: --

No ecological data available for this product.

Ingredient Ecological Information: sodium cyanide: Lepomis macrochirus 96hr LC50 = 0.083 mg/l; Asellus communis 96hr EC50 = 2.33 mg/l

CEPA statement: Sodium Hydroxide: Persistent, Not bioaccumulative or inherently toxic to aquatic organisms; Sodium Cyanide: Persistent, Inherently toxic to aquatic organisms, Not bioaccumulative.

13. DISPOSAL CONSIDERATIONS

EPA Waste ID Number: D003

Special Instructions (Disposal): Dispose of material in an E.P.A. approved hazardous waste facility.

Empty Containers: Rinse three times with an appropriate solvent. In the US, rinsate from empty containers is classified as hazardous waste and should be disposed of at an E.P. A. approved facility.

NOTICE (Disposal): These disposal guidelines are based on federal regulations and may be superseded by more stringent state or local requirements. Please consult your local environmental regulators for more information. In Europe: Chemical and analysis solutions must be disposed of in compliance with the respective national regulations. Product packaging must be disposed of in compliance with the country-specific regulations or must be passed to a packaging return system.

14. TRANSPORT INFORMATION

D.O.T.:

D.O.T. Proper Shipping Name: Corrosive Liquid, Toxic, N.O.S.

(Sodium Hydroxide/Sodium Cyanide Solution)

Hazard Class: 8

Subsidiary Risk: 6.1

ID Number: UN2922

Packing Group: II

T.D.G.:

Proper Shipping Name: Corrosive Liquid, Toxic, N.O.S.

(Sodium Hydroxide/Sodium Cyanide Solution)

Hazard Class: 8

Subsidiary Risk: 6.1

UN Number/PIN: 2922

Packing Group: II

I.C.A.O.:

I.C.A.O. Proper Shipping Name: Corrosive Liquid, Toxic, N.O.S.

(Sodium Hydroxide/Sodium Cyanide Solution)

Hazard Class: 8

Subsidiary Risk: 6.1
ID Number: UN2922
Packing Group: II

I.M.O.:

Proper Shipping Name: Corrosive Liquid, Toxic, N.O.S.
(Sodium Hydroxide/Sodium Cyanide Solution)

Hazard Class: 8

Subsidiary Risk: 6.1

ID Number: UN2922

Packing Group: II

Additional Information: There is a possibility that this product could be contained in a reagent set or kit composed of various compatible dangerous goods. If the item is NOT in a set or kit, the classification given above applies. If the item IS part of a set or kit, the classification would change to the following: UN3316 Chemical Kit, Class 9, PG II or III. If the item is not regulated, the Chemical Kit classification does not apply.

15. REGULATORY INFORMATION

U.S. Federal Regulations:

O.S.H.A.: This product meets the criteria for a hazardous substance as defined in the Hazard Communication Standard. (29 CFR 1910.1200)

E.P.A.:

S.A.R.A. Title III Section 311/312 Categorization (40 CFR 370): Immediate (Acute) Health Hazard

S.A.R.A. Title III Section 313 (40 CFR 372): This product contains a chemical(s) subject to the reporting requirements of Section 313 of Title III of SARA.

Cyanide compounds

302 (EHS) TPQ (40 CFR 355): Sodium Cyanide 100 lbs.

304 CERCLA RQ (40 CFR 302.4): Sodium Hydroxide 1000 lbs. Sodium Cyanide 10 lbs.

304 EHS RQ (40 CFR 355): Sodium Cyanide - RQ 10 lbs

Clean Water Act (40 CFR 116.4): Sodium Hydroxide - RQ = 1000 lbs. (454 kgs.) Sodium cyanide - RQ 10 lbs.

RCRA: Contains RCRA regulated substances. See Section 13, EPA Waste ID Number.

State Regulations:

California Prop. 65: No Prop. 65 listed chemicals are present in this product.

Identification of Prop. 65 Ingredient(s): None

California Perchlorate Rule CCR Title 22 Chap 33: Not applicable

Trade Secret Registry: Not applicable

National Inventories:

U.S. Inventory Status: All ingredients in this product are listed on the TSCA 8(b) Inventory (40 CFR 710).

CAS Number: Not applicable

Canadian Inventory Status: All ingredients of this product are DSL Listed.

EEC Inventory Status: All ingredients used to make this product are listed on EINECS / ELINCS.

Australian Inventory (AICS) Status: All ingredients are listed.

New Zealand Inventory (NZIoC) Status: All components either listed or exempt.

Korean Inventory (KECI) Status: All components of this product are either listed, listed as the anhydrous compound or exempt.

Japan (ENCs) Inventory Status: All components either listed or exempt.

China (PRC) Inventory (MEP) Status: All components either listed or exempt.

16. OTHER INFORMATION

References: 29 CFR 1900 - 1910 (Code of Federal Regulations - Labor). Air Contaminants, Federal Register, Vol. 54, No. 12. Thursday, January 19, 1989. pp. 2332-2983. TLV's Threshold Limit Values and Biological Exposure Indices for 1992-1993. American Conference of Governmental Industrial Hygienists, 1992. CCINFO RTECS. Canadian Centre for Occupational Health and Safety. Hamilton, Ontario Canada: 30 June 1993. Gosselin, R. E. et al. Clinical Toxicology of Commercial Products, 5th Ed. Baltimore: The Williams and Wilkins Co., 1984. Outside Testing. In-house information. Technical Judgment. List of Dangerous Substances Classified in Annex I of the EEC Directive (67/548) - Classification, Packaging and Labeling of Dangerous Substances, Amended July 1992.

Complete Text of H phrases referred to in Section 3: H290 May be corrosive to metals. H300 Fatal if swallowed. H310 Fatal in contact with skin. H314 Causes severe skin burns and eye damage. H318 Causes serious eye damage. H330 Fatal if inhaled. H400 Very toxic to aquatic life. . H410 Very toxic to aquatic life with long lasting effects.

Revision Summary: . . Substantial revision to comply with EU Reg 1272/2008, Reg 1907/2006 and UN GHS (ST/SG/AC.10/36/Add.3).

Date of MSDS Preparation:

Day: 30

Month: July

Year: 2014

MSDS Prepared: MSDS prepared by Product Compliance Department extension 3350

CCOHS Evaluation Note: It is offered under exemption from WHMIS labeling as specified in the Controlled Products Regulation (CPR) Section 17. It is offered under the interim policy that was established by Health Canada permitting use of GHS-formatted safety data sheets in Canada prior to revision of CPR to GHS. This product has been classified and labeled in accordance with the requirements of GHS (ST/SG/AC.10/36/Add.3). This SDS has been prepared in accordance with the requirements of GHS (ST/SG/AC.10/36/Add.3).

Legend:

NA - Not Applicable

ND - Not Determined

NV - Not Available

w/w - weight/weight

w/v - weight/volume

v/v - volume/volume

USER RESPONSIBILITY: Each user should read and understand this information and incorporate it in individual site safety programs in accordance with applicable hazard communication standards and regulations.

**THE INFORMATION CONTAINED HEREIN IS BASED ON DATA CONSIDERED TO BE ACCURATE.
HOWEVER, NO WARRANTY IS EXPRESSED OR IMPLIED REGARDING THE ACCURACY OF THESE DATA
OR THE RESULTS TO BE OBTAINED FROM THE USE THEREOF.**

HACH COMPANY ©2015