

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** Red Mineral Liquid
- **CAS Number:**
8052-41-3
- **EC number:**
232-489-3
- **Index number:**
649-345-00-4
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** Organic solvent
- **1.3 Details of the supplier of the Safety Data Sheet**
- **Manufacturer/Supplier:**
H-B Instrument – A Division of Bel-Art Products
102 West Seventh Avenue
Trappe, PA 19426 USA
Phone: (610) 489-5500
- **1.4 Emergency telephone number:**
ChemTel Inc.
(800)255-3924, +1 (813)248-0585

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



flame

Flam. Liq. 3 H226 Flammable liquid and vapour.



health hazard

Muta. 1B H340 May cause genetic defects.

Carc. 1B H350 May cause cancer.

Asp. Tox. 1 H304 May be fatal if swallowed and enters airways.

- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC**



T; Toxic

Carc. Cat. 2, Muta. Cat. 2

R45-46: May cause cancer. May cause heritable genetic damage.



Xn; Harmful

(Contd. on page 2)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

(Contd. of page 1)

R65: Harmful: may cause lung damage if swallowed.

R10: Flammable.

- **Information concerning particular hazards for human and environment:**
Heightened danger of slipping when the product is spilled on the floor.

- **2.2 Label elements**

- **Labelling according to Regulation (EC) No 1272/2008**

The substance is classified and labelled according to the CLP regulation.

- **Hazard pictograms**



GHS02 GHS08

- **Signal word** Danger

- **Hazard-determining components of labelling:**

Stoddard solvent

- **Hazard statements**

H304: May be fatal if swallowed and enters airways.

H226 Flammable liquid and vapour.

H340 May cause genetic defects.

H350 May cause cancer.

- **Precautionary statements**

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P281 Use personal protective equipment as required.

P233 Keep container tightly closed.

P202 Do not handle until all safety precautions have been read and understood.

P303+P361+P353 IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower.

P308+P313 IF exposed or concerned: Get medical advice/attention.

P370+P378 In case of fire: Use for extinction: CO₂, powder or water spray.

P403+P235 Store in a well-ventilated place. Keep cool.

- **Additional information:**

Restricted to professional users.

- **Hazard description:**

- **WHMIS-symbols:**

B3 - Combustible liquid

D2A - Very toxic material causing other toxic effects



- **NFPA ratings (scale 0 - 4)**



Health = 0

Fire = 2

Reactivity = 0

(Contd. on page 3)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

(Contd. of page 2)

· HMIS-ratings (scale 0 - 4)

HEALTH	0	Health = *0
FIRE	2	Fire = 2
REACTIVITY	0	Reactivity = 0

* - Indicates a long term health hazard from repeated or prolonged exposures.

· HMIS Long Term Health Hazard Substances

8052-41-3	Stoddard solvent
-----------	------------------

· 2.3 Other hazards

· Results of PBT and vPvB assessment

· PBT: Not applicable.

· vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

· 3.1 Substances

· CAS No. Description

8052-41-3 Stoddard solvent

· Identification number(s)

· EC number: 232-489-3

· Index number: 649-345-00-4

· Impurities and stabilising additives:

CAS: 100-41-4 EINECS: 202-849-4 Index number: 601-023-00-4	ethylbenzene Xn R20; F R11 Flam. Liq. 2, H225 Carc. 2, H351 Acute Tox. 4, H332 Aquatic Chronic 3, H412
CAS: 91-20-3 EINECS: 202-049-5 Index number: 601-052-00-2	naphthalene Xn R22-40; N R50/53 Carc. Cat. 3 Carc. 2, H351 Aquatic Acute 1, H400; Aquatic Chronic 1, H410 Acute Tox. 4, H302
CAS: 111-84-2 EINECS: 203-913-4	nonane R10 Flam. Liq. 3, H226

(Contd. on page 4)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

(Contd. of page 3)

CAS: 95-63-6

EINECS: 202-436-9

Index number: 601-043-00-3

1,2,4-trimethylbenzene

 Xn R20; Xi R36/37/38; N R51/53

R10

 Flam. Liq. 3, H226 Aquatic Chronic 2, H411 Acute Tox. 4, H332; Skin Irrit. 2, H315; Eye Irrit. 2, H319; STOT SE 3, H335

SECTION 4: First aid measures

4.1 Description of first aid measures

General information:

Immediately remove any clothing soiled by the product.

Take affected persons out into the fresh air.

After inhalation:

Supply fresh air; consult doctor in case of complaints.

Provide oxygen treatment if affected person has difficulty breathing.

In case of unconsciousness place patient stably in side position for transportation.

After skin contact:

Immediately wash with water and soap and rinse thoroughly.

If skin irritation continues, consult a doctor.

After eye contact:

Remove contact lenses if worn.

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

After swallowing:

Rinse out mouth and then drink plenty of water.

Do not induce vomiting; call for medical help immediately.

A person vomiting while laying on their back should be turned onto their side.

4.2 Most important symptoms and effects, both acute and delayed

Coughing

Breathing difficulty

Gastric or intestinal disorders when ingested.

Slight irritant effect on skin and mucous membranes.

Slight irritant effect on eyes.

Hazards

Danger of pulmonary oedema.

Danger of impaired breathing.

Carcinogenic.

Possible risk of irreversible effects.

4.3 Indication of any immediate medical attention and special treatment needed

If swallowed, gastric irrigation with added, activated carbon.

If swallowed or in case of vomiting, danger of entering the lungs.

If necessary oxygen respiration treatment.

(Contd. on page 5)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

(Contd. of page 4)

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, sand, extinguishing powder. Do not use water.
Foam
- **For safety reasons unsuitable extinguishing agents:** Water
- **5.2 Special hazards arising from the substance or mixture**
Formation of toxic gases is possible during heating or in case of fire.
- **5.3 Advice for firefighters**
- **Protective equipment:**
Wear self-contained respiratory protective device.
Wear fully protective suit.
- **Additional information** Eliminate all ignition sources if safe to do so.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Use respiratory protective device against the effects of fumes/dust/aerosol.
Wear protective equipment. Keep unprotected persons away.
Ensure adequate ventilation
Keep away from ignition sources.
Protect from heat.
Particular danger of slipping on leaked/spilled product.
- **6.2 Environmental precautions:**
Do not allow to enter sewers/ surface or ground water.
Prevent from spreading (e.g. by damming-in or oil barriers).
Inform respective authorities in case of seepage into water course or sewage system.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with non-combustible liquid-binding material (sand, diatomite, acid binders, universal binders).
Pick up mechanically.
Dispose contaminated material as waste according to item 13.
Do not flush with water or aqueous cleansing agents
Used rags or other cleaning materials should be soaked with water and placed in a sealed container.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**
Prevent formation of aerosols.
Avoid splashes or spray in enclosed areas.
Use only in well ventilated areas.

(Contd. on page 6)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

(Contd. of page 5)

Rags, metal wools / cuttings / shavings and waste papers soaked with product must be placed in a sealed metal container rated for flammable waste.

· **Information about fire - and explosion protection:**

Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

Emergency cooling must be available in case of nearby fire.

Flammable gas-air mixtures may form in empty receptacles.

· **7.2 Conditions for safe storage, including any incompatibilities**

· **Storage:**

· **Requirements to be met by storerooms and receptacles:**

Provide ventilation for receptacles.

Avoid storage near extreme heat, ignition sources or open flame.

· **Information about storage in one common storage facility:**

Store away from foodstuffs.

Store away from oxidizing agents.

· **Further information about storage conditions:** Store in cool, dry conditions in well sealed receptacles.

· **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

· **Additional information about design of technical facilities:** No further data; see item 7.

· **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

8052-41-3 Stoddard solvent

PEL (USA)	Long-term value: 2900 mg/m ³ , 500 ppm
REL (USA)	Long-term value: 350 mg/m ³
	Ceiling limit: 1800* mg/m ³
	*15-min
TLV (USA)	Long-term value: 525 mg/m ³ , 100 ppm
EL (Canada)	Short-term value: 580 mg/m ³
	Long-term value: 290 mg/m ³
EV (Canada)	Long-term value: 525 mg/m ³

· **DNELs** No further relevant information available.

· **PNECs** No further relevant information available.

· **Additional information:** The lists valid during the making were used as basis.

· **8.2 Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.

Keep away from foodstuffs, beverages and feed.

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

Avoid contact with the eyes.

Avoid close or long term contact with the skin.

(Contd. on page 7)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

(Contd. of page 6)

Do not carry product impregnated cleaning cloths in trouser pockets.

· **Respiratory protection:**

Not required under normal conditions of use.

Use suitable respiratory protective device when aerosol or mist is formed.

Use suitable respiratory protective device when high concentrations are present.

For spills, respiratory protection may be advisable.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation.

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Safety glasses

· **Body protection:**

Not required under normal conditions of use.

Protection may be required for spills.

· **Limitation and supervision of exposure into the environment**

No further relevant information available.

· **Risk management measures**

See Section 7 for additional information.

No further relevant information available.

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form:

Liquid

Colour:

Black

· **Odour:**

Petroleum-like

· **Odour threshold:**

Not determined.

· **pH-value:**

Not determined.

· **Change in condition**

Melting point/Melting range:

+ 1 °F / - 17 °C

(Contd. on page 8)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

Boiling point/Boiling range:	Boiling Point Range: 318 - 388 ° F / 159 - 198 °C.
· Flash point:	111 °F / 44 °C
· Flammability (solid, gaseous):	Not applicable.
· Auto/Self-ignition temperature:	500 °F / 260 °C (Approximate)
· Decomposition temperature:	Not determined.
· Self-igniting:	Not determined.
· Danger of explosion:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· Explosion limits:	
Lower:	2,1 Vol %
Upper:	13,3 Vol %
· Oxidizing properties	Non-oxidising.
· Vapour pressure at 20 °C:	2,93 hPa (2.2 mmHg)
· Density at 15,6 °C:	0,8 g/cm ³
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate at 20 °C	0,17 (Butyl Acetate = 1.0)
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient (n-octanol/water) at 20 °C:	>3,0 log POW (Estimate)
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· 9.2 Other information	No further relevant information available.

(Contd. of page 7)

SECTION 10: Stability and reactivity

- **10.1 Reactivity**
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used and stored according to specifications.
- **10.3 Possibility of hazardous reactions**
Reacts with strong acids.
Flammable.
Used empty containers may contain product gases which form explosive mixtures with air.
Can form explosive mixtures in air if heated above flash point and/or when sprayed or atomised.
Reacts violently with oxidizing agents.
Toxic fumes may be released if heated above the decomposition point.
- **10.4 Conditions to avoid**
Keep ignition sources away - Do not smoke.
Store away from oxidizing agents.

(Contd. on page 9)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

(Contd. of page 8)

- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** Carbon monoxide and carbon dioxide

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** Slight irritant effect on skin and mucous membranes.
- **on the eye:** Slight irritant effect on eyes.
- **Sensitization:** No sensitizing effects known.
- **Subacute to chronic toxicity:**
Inhalation of concentrated vapours as well as oral intake will lead to anaesthesia-like conditions and headache, dizziness, etc.
- **Additional toxicological information:**
The product shows the following dangers according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version:
May cause genetic defects.
May cause cancer.
- **Repeated dose toxicity:** May cause damage to organs through prolonged or repeated exposure.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction):**
Muta. 1B, Carc. 1B

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** The product contains materials that are harmful to the environment.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:**
Harmful to fish
The product is oxygen-consuming. The declared action may be partly caused by lack of oxygen.
Due to mechanical actions of the product (e.g. agglutinations) damages may occur.
- **Additional ecological information:**
- **General notes:**
This statement was deduced from the properties of the single components.
The product contains materials that are harmful to the environment.
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Danger to drinking water if even small quantities leak into the ground.
Harmful to aquatic organisms
Avoid transfer into the environment.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

(Contd. on page 10)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

(Contd. of page 9)

- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

· 13.1 Waste treatment methods

· Recommendation

Must not be disposed together with household garbage. Do not allow product to reach sewage system. Can be burned with household garbage after consulting with the waste disposal facility operator and the pertinent authorities and adhering to the necessary technical regulations.

Contact waste processors for recycling information.

The user of this material has the responsibility to dispose of unused material, residues and containers in compliance with all relevant local, state and federal laws and regulations regarding treatment, storage and disposal for hazardous and nonhazardous wastes. Residual materials should be treated as hazardous.

· Uncleaned packaging:

· **Recommendation:** Disposal must be made according to official regulations.

· **Recommended cleansing agents:** Solvent naphtha

SECTION 14: Transport information

· 14.1 UN-Number

· DOT

Not Regulated

Classified as combustible under US DOT regulations. Labeling required for single packages ≥ 119 US gal / 450 L to include Combustible symbol and Proper Shipping Name.

UN1268

· ADR, IMDG, IATA

· 14.2 UN proper shipping name

· DOT

Not Regulated

· ADR

1268 PETROLEUM DISTILLATES, N.O.S.

· IMDG, IATA

PETROLEUM DISTILLATES, N.O.S.

· 14.3 Transport hazard class(es)

· DOT

· Class

Not Regulated

· ADR



· Class

3 (F1) Flammable liquids.

(Contd. on page 11)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

(Contd. of page 10)

· Label

3

· IMDG, IATA



· Class

3 Flammable liquids.

· Label

3

· 14.4 Packing group

· DOT

Not Regulated

· ADR, IMDG, IATA

III

· 14.5 Environmental hazards:

· Marine pollutant:

No

· 14.6 Special precautions for user

Warning: Flammable liquids.

· Danger code (Kemler):

30

· EMS Number:

F-E,S-E

· 14.7 Transport in bulk according to Annex II of
MARPOL73/78 and the IBC Code

Not applicable.

· Transport/Additional information:

· ADR

· Limited quantities (LQ)

5L

· Excepted quantities (EQ)

Code: E1

Maximum net quantity per inner packaging: 30 ml

Maximum net quantity per outer packaging: 1000 ml

· Transport category

3

· Tunnel restriction code

D/E

· IMDG

· Limited quantities (LQ)

5L

· Excepted quantities (EQ)

Code: E1

Maximum net quantity per inner packaging: 30 ml

Maximum net quantity per outer packaging: 1000 ml

· DOT

· Remarks:

A flammable liquid offered for transport domestically by highway or rail ONLY, with a flash point at or above 38 °C (100°F) may be reclassified as a combustible liquid.

· UN "Model Regulation":

UN1268, PETROLEUM DISTILLATES, N.O.S., 3, III

SECTION 15: Regulatory information

· 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

· United States (USA)

· SARA

· Section 355 (extremely hazardous substances):

Substance is not listed.

(Contd. on page 12)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

(Contd. of page 11)

· **Section 313 (Specific toxic chemical listings):**

Substance is not listed.

· **TSCA (Toxic Substances Control Act):**

Substance is listed.

· **Proposition 65 (California):**

· **Chemicals known to cause cancer:**

100-41-4 ethylbenzene

91-20-3 naphthalene

· **Chemicals known to cause reproductive toxicity for females:**

Substance is not listed.

· **Chemicals known to cause reproductive toxicity for males:**

Substance is not listed.

· **Chemicals known to cause developmental toxicity:**

Substance is not listed.

· **Carcinogenic Categories**

· **EPA (Environmental Protection Agency)**

Substance is not listed.

· **IARC (International Agency for Research on Cancer)**

Substance is not listed.

· **TLV (Threshold Limit Value established by ACGIH)**

Substance is not listed.

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

Substance is not listed.

· **Canada**

· **Canadian Domestic Substances List (DSL)**

Some components are listed on the NDSL.

Substance is listed.

· **Canadian Ingredient Disclosure list (limit 0.1%)**

95-63-6 1,2,4-trimethylbenzene

· **Canadian Ingredient Disclosure list (limit 1%)**

Substance is listed.

· **Information about limitation of use:**

Workers are not allowed to be exposed to this hazardous material. Exceptions can be made by the authorities in certain cases.

· **Other regulations, limitations and prohibitive regulations**

This product has been classified in accordance with hazard criteria of the Controlled Products Regulations and the SDS contains all the information required by the Controlled Products Regulations.

· **Substances of very high concern (SVHC) according to REACH, Article 57**

Substance is not listed.

(Contd. on page 13)

Safety Data Sheet
according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 15.08.2014

Revision: 15.08.2014

Trade name: Red Mineral Liquid

(Contd. of page 12)

· **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
DOT: US Department of Transportation
IATA: International Air Transport Association
GHS: Globally Harmonized System of Classification and Labelling of Chemicals
ACGIH: American Conference of Governmental Industrial Hygienists
EINECS: European Inventory of Existing Commercial Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
NFPA: National Fire Protection Association (USA)
HMIS: Hazardous Materials Identification System (USA)
WHMIS: Workplace Hazardous Materials Information System (Canada)
DNEL: Derived No-Effect Level (REACH)
PNEC: Predicted No-Effect Concentration (REACH)
Flam. Liq. 3: Flammable liquids, Hazard Category 3
Muta. 1B: Germ cell mutagenicity, Hazard Category 1B
Carc. 1B: Carcinogenicity, Hazard Category 1B
Asp. Tox. 1: Aspiration hazard, Hazard Category 1

· **Sources**

SDS Prepared by:

ChemTel Inc.

1305 North Florida Avenue

Tampa, Florida USA 33602-2902

Toll Free North America 1-888-255-3924 Intl. +01 813-248-0573

Website: www.chemtelinc.com