

Procalcitonin Antibody

CATALOG NO:	6640-30T 30 µg (Trial size) 6640-100 100 µg
ALTERNATE NAME:	Procalcitonin, calcitonin, CALCA; CALC1; CGRP; CGRP-I; CGRP1; CT; KC; MGC126648
CONCENTRATION:	0.5 mg/ml
IMMUNOGEN:	Recombinant Human Procalcitonin 26-141 aa (Cat. No. 4009-10)
INTERNAL ID:	BV- M55
HOST:	Rabbit
SPECIES REACTIVITY:	Human, Mouse, Rat
PURIFICATION:	Affinity purified rabbit IgG
FORMULATION:	Supplied in PBS, 0.01 % BSA, 0.01 % thimerosal, and 50 % glycerol, pH7.2
STORAGE CONDITIONS:	Store at -20°C. For long term storage, aliquot and freeze at -70°C. Avoid repeated freeze/thaw cycles.
DESCRIPTION:	Procalcitonin is a peptide hormone mainly produced by the C cells of the thyroid and certain endocrine cells of the lung. Under normal expression conditions, procalcitonin is immediately cleaved into three specific fragments, an N terminal residue, calcitonin and katacalcin. Levels of unprocessed procalcitonin rises significantly after bacterial infection, trauma or shock.
APPLICATION:	Western blot: 1:200 Note: This information is only intended as a guide. The optimal dilutions must be determined by the user.



Western blot of IL-10 antibody

Lane 1: Procalcitonin 10 ng.
Lane 2: Procalcitonin 50 ng.

RELATED PRODUCTS:

Apoptosis Detection Kits & Reagents

- Annexin V Kits & Bulk Reagents
- Caspase Assay Kits & Reagents
- Mitochondrial Apoptosis Kits & Reagents
- Nuclear Apoptosis Kits & Reagents
- Apoptosis Inducers and Set
- Apoptosis siRNA Vectors

Cell Fractionation System

- Mitochondria/Cytosol Fractionation Kit
- Nuclear/Cytosol Fractionation Kit
- Membrane Protein Extraction Kit
- Cytosol/Particulate Rapid Separation Kit
- Mammalian Cell Extraction Kit
- FractionPREP Fractionation System

Cell Proliferation & Senescence

- Quick Cell Proliferation Assay Kit
- Senescence Detection Kit
- High Throughput Apoptosis/Cell Viability Assay Kits
- LDH-Cytotoxicity Assay Kit
- Bioluminescence Cytotoxicity Assay Kit
- Live/Dead Cell Staining Kit

Cell Damage & Repair

- HDAC Fluorometric & Colorimetric Assays & Drug Discovery Kits
- HAT Colorimetric Assay Kit & Reagents
- DNA Damage Quantification Kit
- Glutathione & Nitric Oxide Fluorometric & Colorimetric Assay Kits

Signal Transduction

- cAMP & cGMP Assay Kits
- Akt & JNK Activity Assay Kits
- Beta-Secretase Activity Assay Kit

Adipocyte & Lipid Transfer

- Recombinant Adiponectin, Survivin, & Leptin
- CETP Activity Assay & Drug Discovery Kits
- PLTP Activity Assay & Drug Discovery Kits
- Total Cholesterol Quantification Kit

Molecular Biology & Reporter Assays

- siRNA Vectors
- Cloning Insert Quick Screening Kit
- Mitochondrial & Genomic DNA Isolation Kits
- 5 Minutes DNA Ligation Kit
- 20 Minutes Gel Staining/Destaining Kit
- β-Galactosidase Staining Kit & Luciferase Reporter Assay Kit

Growth Factors and Cytokines

Monoclonal and Polyclonal Antibodies

FOR RESEARCH USE ONLY! Not to be used on humans.