QuickSlide™

Safety Data Sheet

1. Product And Company Identification

1.1. **Product identifiers**

Product Name: **Decolorizer**

Other Common Names: None

Catalog Number: **AGS-SK-2000C, AGS-BD-10, MGS-SK-6000C**

1.2. **Recommended use**

Used in the gram stain procedure; alcohol/acetone.

1.3. **Details of the supplier of this Safety Data Sheet**

Company: Hardy Diagnostics
1430 West McCoy Lane
Santa Maria, CA 93455

Telephone: (805) 346-2766
(800) 266-2222

Emergency Phone: (800) 424-9300 ChemTrec (24hr service)

2. Hazards Identification

2.1. **Classification of substance or mixture**

GHS Classification in Accordance with 29 CFR 1910 (OSHA HCS)

Flammable Liquid (Category 2), H225

Eye Irritant (Category 2A), H319

Specific Target Organ Toxicity, Single Exposure (Category 1), H370

2.2. **GHS Label elements, including precautionary statements**

Pictogram:	
Signal Word:	**Danger**
Hazard Statements:	
H225	Highly flammable liquid and vapor
H319	Causes serious eye irritation
H370	Causes damage to organs
Precautionary Statements:	
P210	Keep away from heat, hot surfaces, sparks, open flames, and other ignition sources. No smoking.
P233	Keep container tightly closed.
P240	Ground and bond container and receiving equipment.
P241	Use explosion-proof equipment.
P242	Use non-sparking tools.
P243	Take action to prevent static discharges.
P260	Do not breathe fumes, mists, or vapors.
P264	Wash hands thoroughly after handling.
P270	Do not eat, drink, or smoke when using this product.
P280	Wear eye protection.

P303+P361+P353	IF ON SKIN: Take off immediately all contaminated clothing. Rinse skin with water.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308+P311	If exposed or concerned, call a POISON CENTER.
P321	Specific treatment (see supplemental first aid instructions on this label).
P337+P313	If eye irritation persists: Get medical attention.
P370+P378	In case of fire, use water spray, carbon dioxide, dry chemical powder, or appropriate foam to extinguish.
P403+P235	Store in well ventilated place. Keep cool.
P405	Store locked up.
P501	Dispose of contents or container at an approved waste disposal facility, according to applicable regulations.

2.3. **Hazards not otherwise classified or not covered by GHS**

No data available.

3. Composition/Information on Ingredients

3.1. **Mixtures**

Hazardous components:

Substance:	**Concentration:**	**Hazard Information:**
Acetone (CAS# 67-64-1)	Proprietary	Eye Irritant 2A, Flammable Liquid 2
Ethanol (CAS # 64-17-5)	Proprietary	Flammable Liquid 2
Isopropanol (CAS # 67-63-0)	Proprietary	Eye Irritant 2A, Flammable Liquid 2
Methanol (CAS # 67-56-1)	Proprietary	Specific Target Organ Toxicity Single Exposure 1, Flammable Liquid 2

4. First Aid Measures

4.1. **Description of first aid measures**

Inhalation:	If inhaled, remove to fresh air. If not breathing, give artificial respiration and immediately seek medical attention.
Ingestion:	Do not induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Seek medical advice.
Skin Contact:	Immediately wash thoroughly with soap and water. If irritation persists, consult a physician. Avoid touching contaminated clothing.
Eye Contact:	Immediately flush eyes with plenty of water for at least 15 minutes, keeping eyelids open. If irritation persists, consult a physician.

4.2. **Most important symptoms and effects, both acute and delayed**

The most important known symptoms and effects are described in the labeling (see section 2.2) and/or in section 11.

4.3. **Indication of any immediate medical attention and special treatment needed**

No data available.

5. Firefighting Measures

5.1. **Extinguishing media**
Water spray, carbon dioxide, dry chemical powder, or appropriate foam.

5.2. **Special hazards arising from the substance or mixture**
No data available.

5.3. **Advice for firefighters**
In the event of a fire, wear protective clothing and NIOSH-approved breathing apparatus necessary to prevent any possible irritation.

5.4. **Further information**
No data available.

6. Accidental Release Measures

6.1. **Personal precautions, protective equipment and emergency procedures**
Wear protective equipment: chemical resistant gloves. Keep unprotected persons away.
Environmental precautions
No data available.

6.2. **Methods and materials for containment and cleaning up**
Ventilate area of leak or spill. Remove all sources of ignition. Contain and recover liquid when possible. Use non-sparking tools and equipment.

6.3. **Reference to other sections**
For disposal, see section 13.

7. Handling and Storage

7.1. **Precautions for safe handling**
Wear appropriate personal protective equipment.

7.2. **Conditions for safe storage, including any incompatibilities**
Keep container tightly closed. Store in a cool dry place in accordance with specified storage conditions.

7.3. **Specific end uses**
Apart from uses mentioned in section 1.2, not other specific uses are stipulated.

8. Exposure Controls/Personal Protection

8.1. **Control parameters**
No data available.

8.2. **Appropriate engineering controls**
Safety shower and eye bath.

8.3. **Personal protective equipment**

Eye/Face:	Safety goggles
Skin:	Chemical resistant gloves. Wash thoroughly after handling.
Respiratory:	None for normal use
Thermal Hazards:	No data available

9. Physical and Chemical Properties

9.1. **Information on basic physical and chemical properties**

Appearance:	Physical State: Liquid Color: Clear and colorless
Odor:	Alcohol smell
Odor Threshold:	Not Determined
pH:	Not Determined
Melting/Freezing Point:	Not Determined
Boiling Point:	60-63°C
Flash Point:	-2°C (28°F) TCC
Evaporation Rate:	Not Determined
Flammability:	Not Determined
Explosion Limits:	Not Determined
Vapor Pressure:	184 mm Hg at 25°C
Vapor Density:	Not Determined
Relative Density:	Not Determined
Water Solubility:	Soluble
Partition coefficient (n-octanol/water):	Not Determined
Auto-ignition Temperature:	Not Determined
Decomposition Temperature:	Not Determined
Viscosity:	Not Determined
Explosive Properties:	Not Determined
Oxidizing Properties:	Not Determined

9.2. **Other safety information**

No data available.

10. Stability and Reactivity

Reactivity	No data available.
Chemical stability	This product is stable under ordinary conditions of use and storage.
Possibility of hazardous reactions	No data available.
Conditions to avoid	Heat, flames
Incompatible materials	Ignition sources
Hazardous decomposition products	No dangerous decomposition products known.

11. Toxicological Information

11.1. **Information on toxicological effects**

Acute toxicity	No data available
Skin corrosion/irritation	No data available
Serious eye damage/eye irritation	Causes eye irritation
Respiratory or skin sensitization	No data available
Germ cell mutagenicity	No data available
Carcinogenicity	No data available
Reproductive toxicity	No data available
Specific target organ toxicity – single exposure	Liver, kidneys
Specific target organ toxicity – repeated exposure	No data available
Aspiration Hazard	No data available
Additional information	Harmful, irritant

12. Ecological Information

Toxicity	No data available
Persistence and degradability	No data available
Bioaccumulative potential	No data available
Mobility in soil	No data available
Results of PBT and vPvB assessment	No data available
Other adverse effects	No data available

13. Disposal Considerations

13.1. **Waste disposal**

Dispose of in accordance with applicable state and federal regulations.
Disposal must be in accordance with regulations 40 CFR 261.

14. Transport Information

DOT hazard class	Flammable liquid
Shipping name	Ethyl Alcohol Solution
Identification number	UN1170
Packing group	II

15. Regulations

Carcinogenicity	**Yes/No**
NTP:	No
IARC:	Yes, Isopropanol Category 3
OSHA:	No
California Prop 65:	Yes, Methanol
IATA:	No

16. Other Information

The above information, to the best of our knowledge, is accurate. Hardy Diagnostics assumes no liability whatsoever for the accuracy or completeness of the information stated above. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards may be described, we cannot guarantee that these are the only hazards that exist.

QUICKSLIDE™, a division of Hardy Diagnostics
1430 West McCoy Lane, Santa Maria, CA 93455, USA
Phone: (940) 692-3135
Fax: (940) 692-3040
Website: www.quickslide.com
Email: info@quickslide.com