

Product code	Description
A7122	Cell Lysis Solution (CLA), 150ml 150ml

Components:

A712	Cell Lysis Solution (CLA)
------	---------------------------

Safety Data Sheet
acc. to OSHA HCS

Printing date 02/03/2016

Reviewed on 02/02/2016

1: Identification**1.1 Product identifier****Trade name:** Cell Lysis Solution (CLA)**Article number:** A712**Application of the substance / the mixture** Laboratory chemicals**1.3 Details of the supplier of the safety data sheet****Manufacturer/Supplier:**

Promega Corporation
2800 Woods Hollow Road
Madison, WI 53711
U.S.A.

1-800-356-9526 or (608)-274-4330

Information department: SDS author: Regulatory.Affairs@promega.com**1.4 Emergency telephone number:**

For Chemical Emergency Spill, Leak, Fire, Exposure, or Accident Call CHEMTREC Day or Night Within USA
and Canada: 1-800-424-9300

Outside USA and Canada: +1 703-527-3887 (collect calls accepted)

2: Hazard(s) identification**2.1 Classification of the substance or mixture****Classification according to the Hazard Communication Standard (HCS)**

Skin Irrit. 2 H315 Causes skin irritation.

Eye Irrit. 2 H319 Causes serious eye irritation.

2.2 Label elements**Labelling according to Regulation (EC) No 1272/2008**

The product is classified and labeled according to the CLP regulation.

Hazard pictograms GHS07**Signal word** Warning**Hazard-determining components of labeling:**

sodium hydroxide

Hazard statements

H315 Causes skin irritation.

H319 Causes serious eye irritation.

Precautionary statements

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P305+P351+P338 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P321 Specific treatment (see on this label).

P362 Take off contaminated clothing.

P332+P313 If skin irritation occurs: Get medical advice/attention.

(Contd. on page 2)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/03/2016

Reviewed on 02/02/2016

Trade name: Cell Lysis Solution (CLA)

(Contd. of page 1)

*P337+P313 If eye irritation persists: Get medical advice/attention.***Classification system:****NFPA ratings (scale 0 - 4)**

Health = 2

Fire = 0

Reactivity = 0

HMIS-ratings (scale 0 - 4)

Health = 2

Fire = 0

Reactivity = 0

OSHA Hazard Overview (Criteria according to 29CFR1910.1200):

Toxic

Irritant

Primary route(s) of entry:

Dermal

Oral

Target Organ(s): Not applicable or unknown**2.3 Other hazards**

This mixture has not been tested to determine the overall health hazard; therefore in accordance with 29CFR1910.1200, the data reported above pertains to the hazardous ingredients of this mixture.

Results of PBT and vPvB assessment**PBT:** Not applicable.**vPvB:** Not applicable.

3: Composition/information on ingredients

3.2 Chemical characterization: Mixtures**Description:**

The product is a mixture of the hazardous substances listed below along with unlisted nonhazardous substances. The exact concentration percentages of the hazardous substances are withheld as a Promega Corp. trade secret.

Dangerous components:

151-21-3	sodium dodecyl sulphate	<2.00%
Flam. Sol. 1, H228; STOT SE 2, H371; Eye Dam. 1, H318; Aquatic Chronic 2, H411; Acute Tox. 4, H302; Acute Tox. 4, H332; Skin Irrit. 2, H315		

Additional information: For the wording of the listed risk phrases refer to section 15.

4: First-aid measures

4.1 Description of first aid measures

After inhalation: If the patient feels unwell or is concerned, obtain medical advice.

After skin contact:

Immediately wash with water and soap and rinse thoroughly.

If skin irritation continues, consult a doctor.

After eye contact:

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

After swallowing: If the patient feels unwell or is concerned, obtain medical advice.

4.2 Most important symptoms and effects, both acute and delayed None**4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

US
(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/03/2016

Reviewed on 02/02/2016

Trade name: Cell Lysis Solution (CLA)

(Contd. of page 2)

5: Fire-fighting measures

5.1 Extinguishing media

Suitable extinguishing agents:

CO₂, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

5.2 Special hazards arising from the substance or mixture

None known

5.3 Advice for firefighters

No special advice

6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Remove persons from danger area.

Wear protective clothing.

6.2 Environmental precautions:

Dilute with plenty of water.

Do not allow to enter sewers/ surface or ground water.

6.3 Methods and material for containment and cleaning up:

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Ensure adequate ventilation.

6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 13 for disposal information.

7: Handling and storage

7.1 Precautions for safe handling

Ensure good ventilation/exhaustion at the workplace.

Prevent formation of aerosols.

Information about protection against explosions and fires: The product is not flammable.

7.2 Conditions for safe storage, including any incompatibilities

Storage:

Requirements to be met by storerooms and receptacles: No special requirements.

Information about storage in one common storage facility: Not required.

Further information about storage conditions: Keep receptacle tightly sealed.

7.3 Specific end use(s)

No further relevant information available.

8: Exposure controls/personal protection

8.1 Control parameters

Components with limit values that require monitoring at the workplace:

1310-73-2 sodium hydroxide

PEL Long-term value: 2 mg/m³

REL Ceiling limit value: 2 mg/m³

TLV Ceiling limit value: 2 mg/m³

Additional information: The lists that were valid during the creation were used as basis.

(Contd. on page 4)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/03/2016

Reviewed on 02/02/2016

Trade name: Cell Lysis Solution (CLA)

(Contd. of page 3)

8.2 Exposure controls**Personal protective equipment:****General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing.

Wash hands before breaks and at the end of work.

Avoid contact with the eyes and skin.

Do not eat or drink while working.

Clean skin thoroughly immediately after handling the product.

Breathing equipment:

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

Protection of hands:

Protective gloves

Select the glove material considering penetration time, rate of diffusion and degradation time.

It is recommended that the selected protective gloves be tested and approved under NIOSH or EU Directive 89/686/EEC and the standard EN 374 derived from it.

Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

Eye protection:

Safety glasses

Use equipment for eye protection tested and approved under government NIOSH standards.

9: Physical and chemical properties

9.1 Information on basic physical and chemical properties**General Information****Appearance:**

Form:	Fluid
Color:	Colorless
Odor:	Not determined
Odor threshold:	Not determined.

pH-value at 20 °C (68 °F): 13

Change in condition

Melting point/Melting range:	0 °C (32 °F)
Boiling point/Boiling range:	100 °C (212 °F)
Flash point:	Not applicable.

Flammability (solid, gaseous): Not applicable.

Ignition temperature:

Decomposition temperature: Not determined.

Auto igniting: Product is not selfigniting.

Danger of explosion: Product does not present an explosion hazard.

Explosion limits:

Lower:	Not determined.
Upper:	Not determined.
Vapor pressure:	Not determined.

(Contd. on page 5)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/03/2016

Reviewed on 02/02/2016

Trade name: Cell Lysis Solution (CLA)

(Contd. of page 4)

Density at 20 °C (68 °F):	1.00304 g/cm ³ (8.37 lbs/gal)
Relative density	Not determined.
Vapor density	Not determined.
Evaporation rate	Not determined.
Solubility in / Miscibility with	
Water:	Fully miscible.
Partition coefficient (n-octanol/water):	Not determined.
Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
Organic solvents:	0.0 %
Water:	98.2 %
Solids content:	1.8 %
9.2 Other information	No further relevant information available.

10: Stability and reactivity

10.1 Reactivity No further relevant information available.

10.2 Chemical stability

Thermal decomposition / conditions to be avoided: No decomposition if used according to specifications.

10.3 Possibility of hazardous reactions No dangerous reactions known.

10.4 Conditions to avoid No further relevant information available.

10.5 Incompatible materials: No further relevant information available.

10.6 Hazardous decomposition products: No dangerous decomposition products known.

11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity: Based on available data, the classification criteria are not met.

LD/LC50 values that are relevant for classification: No data available

Primary irritant effect:

on the skin:

Causes skin irritation.

on the eye:

Causes serious eye irritation.

Sensitization: Based on available data, the classification criteria are not met.

Additional toxicological information:

Carcinogenic categories

IARC (International Agency for Research on Cancer)

None of the ingredients are listed.

NTP (National Toxicology Program)

None of the ingredients are listed.

OSHA-Ca (Occupational Safety & Health Administration)

None of the ingredients are listed.

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/03/2016

Reviewed on 02/02/2016

Trade name: Cell Lysis Solution (CLA)

(Contd. of page 5)

12: Ecological information

12.1 Toxicity

Aquatic toxicity: Not harmful to the aquatic environment

12.2 Persistence and degradability Not available

12.3 Bioaccumulative potential Not known

12.4 Mobility in soil No further relevant information available.

Ecotoxicological effects:

Remark: Not available

Additional ecological information:

General notes:

Water hazard class 1 (Self-assessment): slightly hazardous for water

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

Rinse off of bigger amounts into drains or the aquatic environment may lead to increased pH-values. A high pH-value harms aquatic organisms. In the dilution of the use-level the pH-value is considerably reduced, so that after the use of the product the aqueous waste, emptied into drains, is only low water-dangerous.

12.5 Results of PBT and vPvB assessment

PBT: Not applicable.

vPvB: Not applicable.

12.6 Other adverse effects No further relevant information available.

13: Disposal considerations

13.1 Waste treatment methods

Recommendation:

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Refer to Section 7: Handling and Storage and Section 8: Exposure Control/Personal Protection for additional handling information and protection of employees.

Uncleaned packagings:

Recommendation: Disposal must be made according to official regulations.

Recommended cleansing agent: Water, if necessary with cleansing agents.

14: Transport information

14.1 UN-Number Not hazardous for transportation

DOT, ADR, ADN, IMDG, IATA Void

14.2 UN proper shipping name None

DOT, ADR, ADN, IMDG, IATA Void

14.3 Transport hazard class(es) None

DOT, ADR, ADN, IMDG, IATA

Class Void

14.4 Packing group None

DOT, ADR, IMDG, IATA Void

14.5 Environmental hazards:

Marine pollutant: No

14.6 Special precautions for user Not applicable.

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/03/2016

Reviewed on 02/02/2016

Trade name: Cell Lysis Solution (CLA)

(Contd. of page 6)

14.7 Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code Not applicable.

UN "Model Regulation": Void

15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
Sara

Section 355 (extremely hazardous substances):

None of the ingredients are listed.

Section 313 (Specific toxic chemical listings):

None of the ingredients are listed.

TSCA (Toxic Substances Control Act):

All ingredients are listed.

Proposition 65

Chemicals known to cause cancer:

None of the ingredients are listed.

Chemicals known to cause reproductive toxicity for females:

None of the ingredients are listed.

Chemicals known to cause reproductive toxicity for males:

None of the ingredients are listed.

Chemicals known to cause developmental toxicity:

None of the ingredients are listed.

Carcinogen categories

EPA (Environmental Protection Agency)

None of the ingredients are listed.

TLV (Threshold Limit Value established by ACGIH)

None of the ingredients are listed.

NIOSH-Ca (National Institute for Occupational Safety and Health)

None of the ingredients are listed.

National regulations:

Water hazard class: Water hazard class 1 (Self-assessment): slightly hazardous for water.

15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

Department issuing SDS:

(Contd. on page 8)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 02/03/2016

Reviewed on 02/02/2016

Trade name: Cell Lysis Solution (CLA)

(Contd. of page 7)

Promega Corporation
 Environmental Health and Safety Department
 2800 Woods Hollow Road
 Madison, WI
 Ph: (608) 274-4330

Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
 IMDG: International Maritime Code for Dangerous Goods
 DOT: US Department of Transportation
 IATA: International Air Transport Association
 GHS: Globally Harmonized System of Classification and Labeling of Chemicals
 ACGIH: American Conference of Governmental Industrial Hygienists
 EINECS: European Inventory of Existing Commercial Chemical Substances
 ELINCS: European List of Notified Chemical Substances
 CAS: Chemical Abstracts Service (division of the American Chemical Society)
 NFPA: National Fire Protection Association (USA)
 HMIS: Hazardous Materials Identification System (USA)
 LC50: Lethal concentration, 50 percent
 LD50: Lethal dose, 50 percent
 PBT: Persistent, Bioaccumulative and Toxic
 vPvB: very Persistent and very Bioaccumulative
 NIOSH: National Institute for Occupational Safety
 OSHA: Occupational Safety & Health
 TLV: Threshold Limit Value
 PEL: Permissible Exposure Limit
 REL: Recommended Exposure Limit
 Flam. Sol. 1: Flammable solids, Hazard Category 1
 Acute Tox. 4: Acute toxicity, Hazard Category 4
 Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2
 Eye Dam. 1: Serious eye damage/eye irritation, Hazard Category 1
 Eye Irrit. 2: Serious eye damage/eye irritation, Hazard Category 2
 STOT SE 2: Specific target organ toxicity - Single exposure, Hazard Category 2
 Aquatic Chronic 2: Hazardous to the aquatic environment - Chronic Hazard, Category 2

*** Data compared to the previous version altered.**

US