



SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 10/24/2014

Version 1.2

SECTION 1. Identification

Product identifier

Product number	100079
Product name	Bolton Broth Selective Supplement acc. to ISO 10272-1

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Use restricted under TSCA to research and development or as analytical reagent. Uses regulated under FDA or FIFRA are not affected. Biochemical research/analysis
-----------------	--

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS-Labeling

Not a dangerous substance according to GHS.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Chemical nature	Lyophilisate.
-----------------	---------------

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

Vancomycin hydrochloride ($\geq 1\%$ - $< 5\%$)

1404-93-9

Exact percentages are being withheld as a trade secret.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

100079

Version 1.2

Product name

Bolton Broth Selective Supplement acc. to ISO 10272-1

amphotericin B (>= 1 % - < 5 %)

1397-89-3

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

In case of skin contact: Take off immediately all contaminated clothing. Rinse skin with water/shower.

Eye contact

After eye contact: rinse out with plenty of water.

Ingestion

After swallowing: make victim drink water (two glasses at most). Consult doctor if feeling unwell.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Diarrhea, Nausea, Vomiting

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Water, Foam, Carbon dioxide (CO₂), Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.

Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters

In the event of fire, wear self-contained breathing apparatus.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid inhalation of dusts. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders:

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

100079

Version 1.2

Product name

Bolton Broth Selective Supplement acc. to ISO 10272-1

Protective equipment see section 8.

Environmental precautions

Do not let product enter drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills. Observe possible material restrictions (see sections 7 and 10). Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry.

Store at +2°C to +8°C (+36°F to +46°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Change contaminated clothing. Wash hands after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Respiratory protection

required when dusts are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state

Lyophilisate

Color

light yellow

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

100079

Version 1.2

Product name

Bolton Broth Selective Supplement acc. to ISO 10272-1

Odor	odorless
Odor Threshold	No information available.
pH	No information available.
Melting point	No information available.
Boiling point	No information available.
Flash point	No information available.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Density	No information available.
Relative density	No information available.
Water solubility	No information available.
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.
Oxidizing properties	none

SECTION 10. Stability and reactivity

Reactivity

The following applies in general to flammable organic substances and mixtures: in correspondingly fine distribution, when whirled up a dust explosion potential may generally be assumed.

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

100079

Version 1.2

Product name

Bolton Broth Selective Supplement acc. to ISO 10272-1

Possibility of hazardous reactions

Violent reactions possible with:

Strong oxidizing agents, Strong acids, strong alkalis

Conditions to avoid

no information available

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact, Ingestion

Target Organs

Skin

Heart

Blood

Kidney

Digestive organs

Gastro-intestinal system

ears

Cardio-vascular system

Eyes

head

Musculo-skeletal system

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC

No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

100079

Version 1.2

Product name

Bolton Broth Selective Supplement acc. to ISO 10272-1

by NTP.

ACGIH

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Handle in accordance with good industrial hygiene and safety practice.

Ingredients

Vancomycin hydrochloride

Acute oral toxicity

LD50 Rat: > 10,000 mg/kg (RTECS)

amphotericin B

Acute oral toxicity

LD50 Rat: > 5,000 mg/kg (Lit.)

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Additional ecological information

Discharge into the environment must be avoided.

Ingredients

Vancomycin hydrochloride

No information available.

amphotericin B

No information available.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

100079

Version 1.2

Product name

Bolton Broth Selective Supplement acc. to ISO 10272-1

SECTION 14. Transport information

Land transport (DOT)

Not classified as dangerous in the meaning of transport regulations.

Air transport (IATA)

Not classified as dangerous in the meaning of transport regulations.

Sea transport (IMDG)

Not classified as dangerous in the meaning of transport regulations.

SECTION 15. Regulatory information

United States of America

SARA 313

This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

100079

Version 1.2

Product name

Bolton Broth Selective Supplement acc. to ISO 10272-1

Notification status

TSCA:

Not Listed on TSCA inventory. For Research and Development Use only. Not For Manufacturing or Commercial Purposes.

DSL:

This product contains one or several components that are not on the Canadian DSL nor NDSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 10/24/2014

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.