# **BioVision**

## **Recombinant Human FGF-9**

**CATALOG #**: 4056-20 20 μg

4056-1000 1 mg

LOT#:

SOURCE: E. coli

**PURITY:** >95% by SDS-PAGE and HPLC

Endotoxin level is <0.1 ng per μg of FGF-9.

MOL. WEIGHT: 23.4 kDa

**FORM:** Lyophilized from 10 mM Tris, pH 7.8 + Ammmonium

Sulfate.

#### RECONSTITUTION:

Centrifuge the vial prior to opening. Reconstitute in 10 mM Tris (pH 8.0) to a concentration of 0.1-1.0 mg/ml. This solution can be diluted into other aqueous buffers and store at 4°C for 1 week or stored at -20°C for future use.

#### STORAGE CONDITIONS:

The lyophilized FGF-9 is best-stored desiccated below 0°C. Reconstituted FGF-9 should be stored at 4°C or lyophilized at working aliquots. Repeated freeze/thaw cycles will result in some loss of activity.

#### **DESCRIPTION:**

FGF-9 (also known as Glial Activating Factor) is a heparin binding growth factor that stimulates the proliferation and activation of glial cells and other cells that express FGF receptors. The human FGF-9 is a 23.4 kDa protein containing 207 amino acid residues.

### **BIOLOGICAL ACTIVITY:**

The ED<sub>50</sub> as determined by the dose-dependent stimulation of thymidine uptake by BaF3 cells expressing FGF receptors is  $\leq$ 0.5 ng/ml, corresponding to a specific activity of  $\geq$ 2 x 10<sup>6</sup> units/mg.

FOR RESEARCH USE ONLY! Not to be used on humans.

#### **RELATED PRODUCTS:**

rev.07/07

Apoptosis Detection Kits & Reagents

- Annexin V Kits & Bulk Reagents
- Caspase Assay Kits & Reagents
- Mitochondrial Apoptosis Kits & Reagents
- Nuclear Apoptosis Kits & Reagents
- Apoptosis Inducers and Set
- Apoptosis siRNA Vectors

## Cell Fractionation System

- Mitochondria/Cytosol Fractionation Kit
- Nuclear/Cytosol Fractionation Kit
- Membrane Protein Extraction Kit
- Cytosol/Particulate Rapid Separation Kit
- Mammalian Cell Extraction Kit
- FractionPREP Fractionation System

## Cell Proliferation & Senescence

- Quick Cell Proliferation Assay Kit
- Senescence Detection Kit
- High Throughput Apoptosis/Cell Viability Assay Kits
- LDH-Cytotoxicity Assay Kit
- Bioluminescence Cytotoxicity Assay Kit
- Live/Dead Cell Staining Kit

### Cell Damage & Repair

- HDAC Fluorometric & Colorimetric Assavs & Drug Discovery Kits
- HAT Colorimetric Assay Kit & Reagents
- DNA Damage Quantification Kit
- Glutathione & Nitric Oxide Fluorometric & Colorimetric Assay Kits

## Signal Transduction

- cAMP & cGMP Assay Kits
- Akt & JNK Activity Assay Kits
- Beta-Secretase Activity Assay Kit

## Adipocyte & Lipid Transfer

- Recombinant Adiponectin, Survivin, & Leptin
- CETP Activity Assay & Drug Discovery Kits
- PLTP Activity Assay & Drug Discovery Kits
- Total Cholesterol Quantification Kit

## Molecular Biology & Reporter Assays

- siRNA Vectors
- Cloning Insert Quick Screening Kit
- Mitochondrial & Genomic DNA Isolation Kits
- 5 Minutes DNA Ligation Kit
- 20 Minutes Gel Staining/Destaining Kit
- β -Galactosidase Staining Kit & Luciferase Reporter Assay Kit

Growth Factors and Cytokines

Monoclonal and Polyclonal Antibodies