

Recombinant Human Interleukin-17A (IL-17A)

CATALOG #:	4176-25	25 µg
	4176-1000	1 mg
LOT #:		
SOURCE:	<i>E. coli</i>	
PURITY:	>98% by SDS-PAGE and HPLC analyses Endotoxin level is <0.1 ng per µg of IL-17A.	
FORMULATION:	Sterile filtered and lyophilized with no additives	

RECONSTITUTION:

Centrifuge the vial prior to opening. Reconstitute in water to a concentration of 0.1-1.0 mg/ml. The solution can then be diluted into other aqueous buffers and stored at 4°C for 1 week or – 20°C for future use.

STORAGE CONDITIONS:

The lyophilized human IL-17 should be stored desiccated below 0°C. Reconstituted IL-17 should be stored at working aliquots at -20°C.

DESCRIPTION:

The original described IL-17 protein, now known as IL-17A, was identified from a CD4+ T cells DNA library. IL-17 can be induced from primary peripheral blood CD4+ T cells upon stimulation. Supernatant from cells transfected with IL-17 induced IL-16 and IL-18 production and enhanced the surface expression of the intracellular adhesion molecule-1 (ICAM-1) in human fibroblasts. Recombinant IL-17 is a 31 kDa disulfide-linked homodimer of two 136 amino acid polypeptide chains.

BIOLOGICAL ACTIVITY:

The ED₅₀ as determined by the dose-dependent induction of IL-6 in primary human foreskin fibroblasts is ≤ 2 ng/ml, corresponding to a specific activity of > 5 x 10⁵ units/mg.

FOR RESEARCH USE ONLY! Not to be used in humans.

RELATED PRODUCTS:

Apoptosis Detection Kits & Reagents

- Annexin V Kits & Bulk Reagents
- Caspase Assay Kits & Reagents
- Mitochondrial Apoptosis Kits & Reagents
- Nuclear Apoptosis Kits & Reagents
- Apoptosis Inducers and Set
- Apoptosis siRNA Vectors

Cell Fractionation System

- Mitochondria/Cytosol Fractionation Kit
- Nuclear/Cytosol Fractionation Kit
- Membrane Protein Extraction Kit
- Cytosol/Particulate Rapid Separation Kit
- Mammalian Cell Extraction Kit
- FractionPREP Fractionation System

Cell Proliferation & Senescence

- Quick Cell Proliferation Assay Kit
- Senescence Detection Kit
- High Throughput Apoptosis/Cell Viability Assay Kits
- LDH-Cytotoxicity Assay Kit
- Bioluminescence Cytotoxicity Assay Kit
- Live/Dead Cell Staining Kit

Cell Damage & Repair

- HDAC Fluorometric & Colorimetric Assays & Drug Discovery Kits
- HAT Colorimetric Assay Kit & Reagents
- DNA Damage Quantification Kit
- Glutathione & Nitric Oxide Fluorometric & Colorimetric Assay Kits

Signal Transduction

- cAMP & cGMP Assay Kits
- Akt & JNK Activity Assay Kits
- Beta-Secretase Activity Assay Kit

Adipocyte & Lipid Transfer

- Recombinant Adiponectin, Survivin, & Leptin
- CETP Activity Assay & Drug Discovery Kits
- PLTP Activity Assay & Drug Discovery Kits
- Total Cholesterol Quantification Kit

Molecular Biology & Reporter Assays

- siRNA Vectors
- Cloning Insert Quick Screening Kit
- Mitochondrial & Genomic DNA Isolation Kits
- 5 Minutes DNA Ligation Kit
- 20 Minutes Gel Staining/Destaining Kit
- β -Galactosidase Staining Kit & Luciferase Reporter Assay Kit

Growth Factors and Cytokines

Monoclonal and Polyclonal Antibodies