

Recombinant Human IL-29

CATALOG #:	4981-20	20 µg
	4981-100	100 µg
	4981-1000	1 mg

SYNONYMS: Interleukin-29, IL 29, IFN-Lambda 1, Interferon-Lambda 1, Cytokine ZCYTO21, IL29, IFNL1, ZCYTO21.

SOURCE: *E. coli*

PURITY: >90% by SDS-PAGE and HPLC analyses
Endotoxin level is <0.1 ng/µg of human IL-29.

MOLECULAR WT: 20 kDa

FORM: Lyophilized without additives

RECONSTITUTION:

Centrifuge the vial prior to opening. Reconstitute in sterile dH₂O not less than 100 µg/ml. This solution can then be diluted into other aqueous buffers and stored at 4°C for 1 week or -20°C for future use.

STORAGE CONDITIONS:

The lyophilized human IL-29 is best-stored desiccated below 0°C. Reconstituted IL-29 should be stored in working aliquots at -20°C. For long term storage it is recommended to add a carrier protein (0.1% HSA or BSA).

DESCRIPTION:

IL-29 is distantly related to type I interferons and the IL-10 family. Expression of IL-29 is induced by viral infection which interacts with a heterodimeric class II cytokine receptor that consists of interleukin 10 receptor beta (IL10RB) and interleukin 28 receptor alpha. IL-29 exhibits common features with type I IFNs such as antiviral activity, antiproliferative activity and in vivo antitumour activity. IL-29 acts similarly to IFNs, but is less effective generally and has activity in a more limited range of cell lines. IL-29 produced in response to viral infection, activates both monocytes and macrophages producing a restricted panel of cytokines and therefore is an important factor in activating innate immune responses at the site of viral infection. IFN-Lambda 1 antiviral and antiproliferative activity requires Interferon-Lambda 2 receptor tyrosine residues. Recombinant human IL-29 produced in E.Coli is a single, non-glycosylated, polypeptide chain containing 181 amino acids and having a molecular mass of 20 kDa.

FOR RESEARCH USE ONLY! Not to be used on humans.

RELATED PRODUCTS:

Apoptosis Detection Kits & Reagents

- Annexin V Kits & Bulk Reagents
- Caspase Assay Kits & Reagents
- Mitochondrial Apoptosis Kits & Reagents
- Nuclear Apoptosis Kits & Reagents
- Apoptosis Inducers and Set
- Apoptosis siRNA Vectors

Cell Fractionation System

- Mitochondria/Cytosol Fractionation Kit
- Nuclear/Cytosol Fractionation Kit
- Membrane Protein Extraction Kit
- Cytosol/Particulate Rapid Separation Kit
- Mammalian Cell Extraction Kit
- FractionPREP Fractionation System

Cell Proliferation & Senescence

- Quick Cell Proliferation Assay Kit
- Senescence Detection Kit
- High Throughput Apoptosis/Cell Viability Assay Kits
- LDH-Cytotoxicity Assay Kit
- Bioluminescence Cytotoxicity Assay Kit
- Live/Dead Cell Staining Kit

Cell Damage & Repair

- HDAC Fluorometric & Colorimetric Assays & Drug Discovery Kits
- HAT Colorimetric Assay Kit & Reagents
- DNA Damage Quantification Kit
- Glutathione & Nitric Oxide Fluorometric & Colorimetric Assay Kits

Signal Transduction

- cAMP & cGMP Assay Kits
- Akt & JNK Activity Assay Kits
- Beta-Secretase Activity Assay Kit

Adipocyte & Lipid Transfer

- Recombinant Adiponectin, Survivin, & Leptin
- CETP Activity Assay & Drug Discovery Kits
- PLTP Activity Assay & Drug Discovery Kits
- Total Cholesterol Quantification Kit

Molecular Biology & Reporter Assays

- siRNA Vectors
- Cloning Insert Quick Screening Kit
- Mitochondrial & Genomic DNA Isolation Kits
- 5 Minutes DNA Ligation Kit
- 20 Minutes Gel Staining/Destaining Kit
- β -Galactosidase Staining Kit & Luciferase Reporter Assay Kit

Growth Factors and Cytokines

Monoclonal and Polyclonal Antibodies