



Transferrin Antibody

CATALOG NUMBER: 54-194

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	Transferrin antibody can be used at 1:1000 to 1:5000 for both ELISA and immunoblot testing.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Transferrin antibody is human specific.
IMMUNOGEN:	Human transferrin mix peptides (aa30-41, aa292-303, aa431-422) as combined immunogens.
HOST SPECIES:	Chicken

Properties

PURIFICATION:	Total IgY purified from egg yolk
PHYSICAL STATE:	Liquid
BUFFER:	PBS Buffer containing 0.02% sodium azide.
STORAGE CONDITIONS:	2-8°C for one week and -20°C as an undiluted liquid for up to two years.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	Serotransferrin, Beta-1 metal-binding globulin, Transferrin, TFQTL1, PRO1557, PRO2086
ACCESSION NO.:	P02787
PROTEIN GI NO.:	313104271
OFFICIAL SYMBOL:	TF
GENE ID:	7018

Background

FOR RESEARCH USE ONLY

December 13, 2016