



NBS1 Antibody [1D7]

CATALOG NUMBER: 47-175

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IP, WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
POSITIVE CONTROL:	1) Cat. No. 1201 - HeLa Cell Lysate 2) Cat. No. 1219 - MCF7 Cell Lysate 3) Cat. No. 1207 - Raji Cell Lysate
IMMUNOGEN:	Fusion protein containing the complete coding region of human p95/nibrin expressed in E. coli.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein G-purified
PHYSICAL STATE:	Liquid
BUFFER:	PBS
STORAGE CONDITIONS:	NBS1 monoclonal antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	Retinoblastoma, phospho-Retinoblastoma, phospho-Rb, pS249/pT252, Retinoblastoma-associated protein, p105-Rb, Rb, RB, pRb, OSRC, pp110
ACCESSION NO.:	AAO62758.1
PROTEIN GI NO.:	29123599
OFFICIAL SYMBOL:	RB1
GENE ID:	5925

Background

FOR RESEARCH USE ONLY

December 13, 2016