



Estrogen Receptor alpha Antibody [1F3]

CATALOG NUMBER: 47-122

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IP, WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	6-His fusion protein containing the region encoding aa 1-190 of human estrogen receptor- α (ER- α) expressed in E. coli.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein G-purified
PHYSICAL STATE:	Liquid
BUFFER:	PBS
STORAGE CONDITIONS:	Estrogen Receptor alpha monoclonal antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1/kappa
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	P53, Cellular tumor antigen p53, Antigen NY-CO-13, BCC7, LFS1, TRP53
ACCESSION NO.:	NP_000537.3
PROTEIN GI NO.:	120407068
OFFICIAL SYMBOL:	TP53
GENE ID:	7157

Background

FOR RESEARCH USE ONLY

December 13, 2016